

Other Salt Mixtures

Component	A 3551 [1X] g/L	G 9779 [1X] g/L	K 4002 g/L	K 3753 g/L	P 2917 [1X] g/L	T 2145 g/L	T 2397 [1X] g/L
Inorganic Salts							
Calcium Chloride	—	0.2251	—	—	—	—	—
Calcium Chloride•2H ₂ O	—	—	—	—	—	0.265	0.265
Citric Acid•3Na•2H ₂ O	8	—	—	—	—	—	—
Citric Acid•H ₂ O	0.55	—	—	—	—	—	—
Magnesium Chloride•6 H ₂ O	—	0.21	0.1	—	—	0.214	0.214
Magnesium Sulfate (anhydrous)	—	0.0342	—	0.141	—	—	—
Potassium Chloride	—	0.37	0.34	0.35	0.4	0.2	0.2
Potassium Phosphate Monobasic (anhydrous)	—	0.03	—	0.16	—	—	—
Sodium Bicarbonate	—	2.27	—	—	0.35	—	1
Sodium Chloride	4.2	7	7	6.9	8	8	8
Sodium Phosphate Dibasic (anhydrous)	—	0.1196	0.1	—	—	—	—
Sodium Phosphate Monobasic (anhydrous)	—	—	0.18	—	—	0.05	0.05
Other							
D-Glucose	20.5	1	1.8	2	1	1	1
Phenol Red (sodium)	—	0.0106	—	—	0.005	—	—
Add							
Sodium Bicarbonate	—	—	1.26	2.1	—	1	—