



QUALITY CONTROL RANGES

MILLIPLEX[®] MAP Mouse MMP Magnetic Bead Panel 1
Kit Catalog # MMMP1MAG-79

MILLIPLEX[®] MAP Mouse MMP Magnetic Bead Panel 2
Kit Catalog # MMMP2MAG-79

MILLIPLEX[®] MAP Mouse MMP Magnetic Bead Panel 3
Kit Catalog # MMMP3MAG-79

Control Catalog # MMMP-6079
Lot# MMMP-107A and MMMP-207A

<u>Analyte</u>	<u>QC Level</u>	<u>Expected Range</u>	<u>Units</u>
MMMP2	Control 1	672 - 1396	pg/mL
	Control 2	6929 - 14391	pg/mL
MMMP3	Control 1	35 - 72	pg/mL
	Control 2	367 - 762	pg/mL
MMMP8	Control 1	172 - 357	pg/mL
	Control 2	1766 - 3668	pg/mL
MMMP9	Control 1	599 - 1244	pg/mL
	Control 2	6466 - 13428	pg/mL
MMMP12	Control 1	65 - 135	pg/mL
	Control 2	630 - 1308	pg/mL

Note: The Quality Control Ranges are generated with overnight assay format.

MMMP-6079: MMMP-107A.207A (21 July 2021)

EMD MILLIPORE • 1-800-645-5476 • 1-800-645-5439 (FAX) www.emdmillipore.com

The M logo is a trademark of Merck KGaA, Darmstadt, Germany.

© 2013 EMD Millipore Corporation, Billerica, MA 01821 USA.