

# Material Safety Data Sheet

OSHA "Hazard Communication" (29 CFR 1910.1200)

## Trypsin-EDTA Solution 1X

0.25% trypsin, 0.1% EDTA, trypsin gamma irradiated by SER-TAIN™ Process,  
in Hanks' Balanced Salt Solution  
CATALOG NO. 59429

### Section I – Product Identification

**Product Name:**

Trypsin-EDTA Solution 1X , 0.25% trypsin, 0.1% EDTA, trypsin gamma irradiated by SER-TAIN™ Process,  
in Hanks' Balanced Salt Solution

**Product Number:**

59429

**Product Classification:**

Liquid Media

**Synonyms:**

Parenzyme, Tryptar

### Section II – Physical Data

**Appearance:**

Clear red solution

**pH:**

7.2 - 8.0

### Section III – Hazardous Ingredients

Porcine Trypsin Enzyme CAS Number: 9002-07-7. Ethylenediaminetetraacetic Acid, Disodium, Dihydrate CAS Number: 6381-92-6.

### Section IV – First Aid

In case of contact with eyes, flush thoroughly with water and contact a physician. In case of accidental swallowing, rinse the mouth with fresh water, provided the person is conscious. Contact a physician. If inhaled remove to fresh air. Give oxygen if breathing becomes difficult. If not breathing, give artificial respiration. Contact a physician. In case of contact with skin, wash the affected area with copious quantities of soap and water. Should irritation occur, contact a physician. Remove contaminated clothing and footwear.

### Section V – Fire and Explosion Hazard Data

**Extinguishing Media:**

Water spray, dry chemical powder or appropriate foam. Wear self-contained breathing apparatus and protective clothing. Avoid contact with skin or eyes.

---

**United States**

SAFC Biosciences, Inc.  
13804 W. 107th Street  
Lenexa, Kansas 66215  
USA  
Phone +1 913-469-5580  
Toll free-USA 1 800-255-6032  
Fax +1 913-469-5584  
E-mail info-na@sial.com

**Europe**

SAFC Biosciences Ltd.  
Smeaton Road, West Portway  
Andover, Hampshire SP10 3LF  
UNITED KINGDOM  
Phone +44 (0)1264-333311  
Fax +44 (0)1264-332412  
E-mail info-eu@sial.com

**Asia Pacific**

SAFC Biosciences Pty. Ltd.  
18-20 Export Drive  
Brooklyn, Victoria 3025  
AUSTRALIA  
Phone +61 (0)3-9362-4500  
Toll free-AUS 1 800-200-404  
Fax +61 (0)3-9315-1656  
E-mail info-ap@sial.com

## Section VI – Health (Toxicological) Hazard Data

This product is a potential irritant to eyes, respiratory system and skin. This product may also be harmful if ingested. Prolonged or repeated exposure may result in allergic reactions in sensitive individuals. Complete toxicological properties have yet to be determined.

## Section VII – Stability and Reactivity

Stable. Hazardous Polymerization will not occur.

## Section VIII – Special Protection Information

### Eye Protection:

Safety glasses or goggles required.

### Protective Gloves:

Chemical-resistant gloves required.

### Respiratory Protection:

Respirator or protective mask required.

### Ventilation:

Mechanical (general) or local exhaust.

### Other Protection Equipment:

Safety shower and eye bath. Wear protective clothing.

## Section IX – Handling and Storage Precautions/Comments

### Store at:

-10 to -40 C.

### Intended Use:

For further manufacturing use. THIS PRODUCT IS NOT INTENDED FOR HUMAN OR THERAPEUTIC USE.

## Section X – Spill or Leak Procedures

### Spill:

Wear respirator, safety glasses or goggles, protective clothing and chemical-resistant gloves. Absorb liquid on sand, vermiculite or other absorbent material. Place in a closed container and hold for waste disposal. Ventilate area. Wash area thoroughly after clean-up is complete.

### Waste Disposal:

Follow all Federal, state and local regulations for chemical waste disposal.

## Section XI – Disclaimer

The information, data and recommendations contained herein are believed to be accurate but may not be all-inclusive and should only be used as a guide. SAFC Biosciences makes no warranty of any kind whatsoever with respect thereto and disclaims all liability from reliance thereon. We reserve the right to revise this MSDS periodically as new information becomes available.

### Warranty, Limitation of Remedies

SAFC Biosciences warrants to the purchaser for a period of one year from date of delivery that this product conforms to its specifications. Other terms and conditions of this warranty are contained in SAFC Biosciences' written warranty, a copy of which is available upon request. ALL OTHER WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING THE IMPLIED WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. In no case will SAFC Biosciences be liable for any special, incidental, or consequential damages arising out of this product or the use of this product by the customer or any third party based upon breach of warranty, breach of contract, negligence, strict tort, or any other legal theory. SAFC Biosciences expressly disclaims any warranty against claims by any third party by way of infringement or the like. THIS PRODUCT IS INTENDED FOR PURPOSES DESCRIBED ONLY AND IS NOT INTENDED FOR ANY HUMAN OR THERAPEUTIC USE.

Additional Terms and Conditions are contained in the product Catalog, a copy of which is available upon request.

SER-TAIN™ is a trademark of SAFC Biosciences, Inc.

© 2006 SAFC Biosciences, Inc.

Issued April 2006 M59429  
0103 0905 1005

### United States

SAFC Biosciences, Inc.  
13804 W. 107th Street  
Lenexa, Kansas 66215  
USA  
Phone +1 913-469-5580  
Toll free-USA 1 800-255-6032  
Fax +1 913-469-5584  
E-mail info-na@sial.com

### Europe

SAFC Biosciences Ltd.  
Smeaton Road, West Portway  
Andover, Hampshire SP10 3LF  
UNITED KINGDOM  
Phone +44 (0)1264-333311  
Fax +44 (0)1264-332412  
E-mail info-eu@sial.com

### Asia Pacific

SAFC Biosciences Pty. Ltd.  
18-20 Export Drive  
Brooklyn, Victoria 3025  
AUSTRALIA  
Phone +61 (0)3-9362-4500  
Toll free-AUS 1 800-200-404  
Fax +61 (0)3-9315-1656  
E-mail info-ap@sial.com