



Eppendorf 5702 / R **Z606936 and Z618942**

(* A-4-38 / 5702 720 003 is supplied with round suspensions 5702 722 006 ** includes 30 x 5702 707 007 adapters ***includes 10 x 5702 707 007 adapters)



ml / mm	Tubes per rotor	RCF	Rotor Cat. No. / model / Supplier ref. No.	Swing out or fixed	Suspensions Cat. No. / model	Suspension lid Cat. No. / model	Suspensions needed per rotor	Adapters Cat. No. / model	No. of adapters per rotor
2-7 100 x 12	20	2,850	Z606944 / A-4-38 / 5702 720 003*	S	5702 722 006*	5702 721 000	4	Z643319 / 5702 737 003	4
2.6-7 100 x 13	16	2,850	Z606944 / A-4-38 / 5702 720 003*	S	5702 722 006*	5702 721 000	4	Z643327 / 5702 719 005	4
4-10 100 x 16	16	2,850	Z606944 / A-4-38 / 5702 720 003*	S	5702 722 006*	5702 721 000	4	Z642827 / 5702 735 000	4
5-7 100 x 13	40	2,750	A-4-38 / 5702 720 004	S	Z618705 / 5702 709 000	-	4	570 710 008	10
9 100 x 14	24	2,750	A-4-38 / 5702 720 004	S	Z618705 / 5702 709 000	-	4	Z618829 / 5702 711 004	4
9-15 100 x 17	16	2,800	Z606944 / A-4-38 / 5702 720 003*	S	5702 722 006*	5702 721 000	4	Z618721 / 5702 724 009	4
15 115 X 18	30	2,750	Z606960 / F-35-30-17 / 5702 704 008**	F	-	-	-	Z618519 / 5702 707 007	30



ml / mm	Tubes per rotor	RCF	Rotor Cat. No. / model / Supplier ref. No.	Swing out or fixed	Suspensions Cat. No. / model	Suspension lid Cat. No. / model	Suspensions needed per rotor	Adapters Cat. No. / model	No. of adapters per rotor
15 100 X 17	24	2,750	A-4-38 / 5702 720 004	S	Z618705 / 5702 709 000	-	4	Z618837 / 5702 712 000	4
20 100 X 22	16	2,750	A-4-38 / 5702 720 004	S	Z618705 / 5702 709 000	-	4	Z618845 / 5702 713 007	4
20 100 X 25	8	2,750	A-4-38 / 5702 720 004	S	Z618705 / 5702 709 000	-	4	Z618853 / 5702 716 006	4
25 100 x 25	4	2,900	Z606944 / A-4-38 / 5702 720 003*	S	5702 722 006*	5702 721 000	4	5702 717 002	4
85 106 x 38	4	2,900	Z606944 / A-4-38 / 5702 720 003*	S	5702 722 006*	5702 721 000	4	5702 718 009	4
15 120 x 17	4	3,000	Z606944 / A-4-38 / 5702 720 003*	S	5702 722 006*	5702 721 000	4	5702 732 001	1
15 121 x 17	8	3,000	Z606944 / A-4-38 / 5702 720 003*	S	5702 722 006*	-	4	Z606952 / 5702 723 002	2
50 115 x 30	4	2,900	Z606944 / A-4-38 / 5702 720 003*	S	5702 722 006*	5702 721 000	4	Z618985 / 5702 734 004	1
15 120/135 x 18	20	2,750	F-35-30-17 / 5702 704 004 ***	F	-	-	-	Z618519 / 5702 707 007	10 + 10