

QUALITY CONTROL RANGES
MILLIPLEX[®] MAP Mouse Bone Magnetic Bead Panel
Kit Catalog # MBNMAG-41K
Control Catalog # MBN-6041



<u>Analyte</u>	<u>QC Level</u>	<u>Lot #</u>	<u>Expected Range</u>	<u>Units</u>
ACTH	Control 1	MBN-106	75 - 155	pg/mL
	Control 2	MBN-206	425 - 883	pg/mL
IL-6	Control 1	MBN-106	147 - 343	pg/mL
	Control 2	MBN-206	946 - 1964	pg/mL
OPG	Control 1	MBN-106	337 - 832	pg/mL
	Control 2	MBN-206	2118 - 4399	pg/mL
Insulin	Control 1	MBN-106	827 - 1719	pg/mL
	Control 2	MBN-206	5124 - 10643	pg/mL
Leptin	Control 1	MBN-106	211 - 490	pg/mL
	Control 2	MBN-206	1331 - 2765	pg/mL
DKK1	Control 1	MBN-106	263 - 654	pg/mL
	Control 2	MBN-206	1741 - 3617	pg/mL
SOST	Control 1	MBN-106	61 - 133	pg/mL
	Control 2	MBN-206	358 - 743	pg/mL
TNF α	Control 1	MBN-106	58 - 139	pg/mL
	Control 2	MBN-206	369 - 766	pg/mL
FGF23	Control 1	MBN-106	139 - 430	pg/mL
	Control 2	MBN-206	919 - 1908	pg/mL

Note: The Quality Control Ranges are generated with overnight assay format using serum matrix provided in the kit. Quality Control values in culture media are not tested.

MBN-6041: MBN-106.206 (28 May 2020)

EMD MILLIPORE • 1-800-645-5476 • 1-800-645-5439 (FAX) www.emdmillipore.com

The M logo is a trademark of Merck KGaA, Darmstadt, Germany.

© 2013 EMD Millipore Corporation, Billerica, MA 01821 USA.