



Product Information

SIGMA QUALITY CONTROL TEST PROCEDURE

Enzymatic Assay of α -GLUCOSIDASE

(EC 3.2.1.20)

p-Nitrophenyl α -D-Glucoside as Substrate

Product Nos. G-5003, G-6136, G-7256, G-8889, G0660, and G-3651

PRINCIPLE:

p-Nitrophenyl α -D-Glucoside $\xrightarrow{\alpha\text{-Glucosidase}}$ α -D-Glucose + p-Nitrophenol

CONDITIONS: T = 37°C, pH = 6.8, A_{400nm}, Light path = 1 cm

METHOD: Spectrophotometric Stop Rate Determination

REAGENTS:

- A. 67 mM Potassium Phosphate Buffer, pH 6.8 at 37°C
(Prepare 100 ml in deionized water using Potassium Phosphate, Monobasic, Anhydrous, Sigma Prod. No P-5379. Adjust to pH 6.8 at 37°C with 1 M NaOH. **PREPARE FRESH.**)
- B. 3 mM Glutathione, Reduced Solution (GSH)
(Prepare 10 ml in deionized water using Glutathione, Free Acid, Reduced Form, Sigma Prod. No. G-4251. **PREPARE FRESH.**)
- C. 10 mM p-Nitrophenyl α -D-Glucoside Solution (PNP-Gluc)
(Prepare 10 ml in deionized water using p-Nitrophenyl α -D-Glucopyranoside, Sigma Prod. No. N-1377.)
- D. 100 mM Sodium Carbonate Solution, (NaCarb)
(Prepare 50 ml in deionized water using Sodium Carbonate, Anhydrous, Sigma Prod. No. S-2127.)
- E. α -Glucosidase Enzyme Solution
(Immediately before use, prepare a solution containing 0.15 - 0.3 unit/ml of α -Glucosidase in cold deionized water.)

PROCEDURE:

Pipette (in milliliters) the following reagents into suitable containers:

	<u>Test</u>	<u>Blank</u>
Deionized Water	-----	0.20
Reagent A (Buffer)	5.00	5.00
Reagent B (GSH)	0.20	0.20
Reagent E (Enzyme Solution)	0.20	-----

Mix by inversion and equilibrate to 37°C. Then add:

Reagent C (PNP-Gluc)	0.50	0.50
----------------------	------	------

Immediately mix by inversion and incubate for exactly 20 minutes at 37°C.

Pipette (in milliliters) the following reagents into suitable containers:

Test Solution	2.00	-----
Blank Solution	-----	2.00
Reagent D (NaCarb)	8.00	8.00

Mix by inversion and transfer the solutions to suitable cuvettes. Record the A_{400nm} for both the Test and Blank using a suitable spectrophotometer.

CALCULATIONS:

$$\text{Units/ml enzyme} = \frac{(A_{400nm} \text{ Test} - A_{400nm} \text{ Blank})(10)(5.9)(df)}{(18.3)(20)(2)(0.2)}$$

5.9 = Volume (in milliliters) of reaction mixture

df = Dilution factor

18.3 = Millimolar extinction coefficient of p-Nitrophenol at 400 nm

20 = Time (in minutes) of the assay

10 = Volume (in milliliters) of Colorimetric Determination

2 = Volume (in milliliters) of reaction mix used in the colorimetric determination

CALCULATIONS:

$$\text{Units/mg solid} = \frac{\text{units/ml enzyme}}{\text{mg solid/ml enzyme}}$$

$$\text{Units/mg protein} = \frac{\text{units/ml enzyme}}{\text{mg protein/ml enzyme}}$$

UNIT DEFINITION:

One unit will liberate 1.0 μ mole of D-glucose from p-nitrophenyl α -D-glucoside per minute at pH 6.8 at 37°C.

FINAL ASSAY CONCENTRATIONS:

In a 5.90 ml reaction mix, the final concentrations are 57 mM potassium phosphate, 0.1 mM glutathione, 0.85 mM p-nitrophenyl α -D-glucoside and 0.03 - 0.06 unit α -glucosidase.

NOTES:

1. All product and stock numbers, unless otherwise indicated, are Sigma product and stock numbers.

Sigma warrants that the above procedure information is currently utilized at Sigma and that Sigma products conform to the information in Sigma publications. Purchaser must determine the suitability of the information and products for its particular use. Upon purchase of Sigma products, see reverse side of invoice or packing slip for additional terms and conditions of sale.