



SIGMA QUALITY CONTROL TEST PROCEDURE

Product Information

Enzymatic Assay of GLUTATHIONE REDUCTASE (EC 1.6.4.2)

PRINCIPLE:



Abbreviations used:

β -NADPH = β -Nicotinamide Adenine Dinucleotide Phosphate, Reduced Form

β -NADP = β -Nicotinamide Adenine Dinucleotide Phosphate, Oxidized Form

GSSG = Glutathione, Oxidized Form

GSH = Glutathione, Reduced Form

CONDITIONS: T = 25°C, pH = 7.6, $A_{340\text{nm}}$, Light Path = 1 cm

METHOD: Continuous Spectrophotometric Rate Determination

REAGENTS:

- A. 100 mM Potassium Phosphate Buffer with 3.4 mM Ethylenediaminetetraacetic Acid (EDTA), pH 7.6 at 25°C
(Prepare 200 ml in deionized water using Potassium Phosphate, Monobasic, Anhydrous, Sigma Prod. No. P-5379 and Ethylenediaminetetraacetic Acid, Dipotassium Salt, Sigma Stock No. ED2P. Adjust to pH 7.6 at 25°C with 1 M KOH.)
- B. 30 mM Glutathione Substrate Solution (GSSG)
(Prepare 5 ml in deionized water using Glutathione, Oxidized Form, Disodium Salt, Sigma Prod. No. G-4626.)
- C. 0.8 mM β -Nicotinamide Adenine Dinucleotide Phosphate, Reduced Form Solution (β -NADPH)
(Prepare 5 ml in cold Reagent A using β -Nicotinamide Adenine Dinucleotide Phosphate, Tetrasodium Salt, Sigma Prod. No. N-1630.)
- D. 1.0% (w/v) Bovine Serum Albumin (BSA)
(Prepare 100 ml in Reagent A using Albumin, Bovine, Sigma Prod. No. A-4503. This solution should be kept cold.)

**Enzymatic Assay of GLUTATHIONE REDUCTASE
(EC 1.6.4.2)**

REAGENTS: (continued)

- E. Glutathione Reductase Enzyme Solution
(Immediately before use, prepare a solution containing 0.30 - 0.60 unit/ml of Glutathione Reductase in cold Reagent D.)

PROCEDURE:

Pipette (in milliliters) the following reagents into suitable cuvettes:

	<u>Test</u>	<u>Blank</u>
Deionized Water	0.65	0.65
Reagent A (Buffer)	1.50	1.50
Reagent B (GSSG)	0.10	0.10
Reagent C (β-NADPH)	0.35	0.35
Reagent D (BSA)	0.30	0.40

Mix by inversion and equilibrate to 25°C. Monitor the $A_{340\text{nm}}$ until constant, using a suitably thermostatted spectrophotometer. Then add:

Reagent E (Enzyme Solution)	0.10	-----
-----------------------------	------	-------

Immediately mix by inversion and record the decrease in the $A_{340\text{nm}}$ for approximately 5 minutes. Obtain the $\Delta A_{340\text{nm}}/\text{minute}$ using the maximum linear rate for both the Test and Blank.

CALCULATIONS:

$$\text{Units/ml enzyme} = \frac{(\Delta A_{340\text{nm}}/\text{min Test} - \Delta A_{340\text{nm}}/\text{min Blank})(3)(\text{df})}{(6.22)(0.1)}$$

3 = Total volume (in milliliters) of assay

df = Dilution factor

6.22 = Millimolar extinction coefficient of β-NADPH at 340 nm

0.1 = Volume (in milliliters) of enzyme used

$$\text{Units/mg solid} = \frac{\text{units/ml enzyme}}{\text{mg solid/ml enzyme}}$$

**Enzymatic Assay of GLUTATHIONE REDUCTASE
(EC 1.6.4.2)**

CALCULATIONS: (continued)

$$\text{Units/mg protein} = \frac{\text{units/ml enzyme}}{\text{mg protein/ml enzyme}}$$

UNIT DEFINITION:

One unit will reduce 1.0 μ mole of oxidized glutathione per minute at pH 7.6 at 25°C.

FINAL ASSAY CONCENTRATION:

In a 3.00 ml reaction mix, the final concentrations are 75 mM potassium phosphate, 2.6 mM ethylenediaminetetraacetic acid, 1 mM glutathione, 0.09 mM β -nicotinamide adenine dinucleotide phosphate, reduced form, 0.13% (w/v) bovine serum albumin, and 0.03 - 0.06 unit of glutathione reductase.

REFERENCE:

Mavis, R.D. and Stellwagen, E. (1968) *Journal of Biological Chemistry* **243**, 809-814

NOTES:

1. This assay is based on the cited reference.
2. Where Sigma Product or Stock numbers are specified, equivalent reagents may be substituted.

Sigma warrants that the above procedure information is currently utilized at Sigma and that Sigma products conform to the information in Sigma publications. Purchaser must determine the suitability of the information and products for its particular use. Upon purchase of Sigma products, see reverse side of invoice or packing slip for additional terms and conditions of sale.