VELP SCIENTIFICA

MSL 50 Digital

High Volume Magnetic Stirrer

Be Assured. Choose MSL Series



Safety, Resistance and Reliability.

- Clear digital display to accurately set up the desired working conditions
- Gentle start and low speed stirring (20rpm) to protect your sample
- Brushless motor ensures premium power and long life span for up to 50L volume
- Resistant stainless steel cover allowing easy visualization of particles and color changes
- Constant stirring from 20 to 1000 rpm with SpeedServo technology
- MSL 50 Digital remains cold during continuous stirring
- Integral timer and programmable auto-reverse of the stirring direction
- Safety Lock avoids possible unintentional changes
- Control panel is shielded from liquid spills
- The intermittent mode option enhances programming capabilities to match any application requirement

3 YEARS WARRANTY

INSTRUMENT - CODE

MSL 50 Digital	100-240V/50-60Hz	**F203A0512**

TECHNICAL DATA

USER INTERFACE	Digital
MOTOR	Brushless Motor
PLATE MATERIAL	Stainless steel
STIRRING VOLUME (H2O)	Up to 50 L
STIRRING SPEED RANGE	20-1000 rpm
SPEED ACCURACY	10 rpm
SPEED CONTROL	Digital
TORQUE COMPENSATION	SpeedServo™
TIMER	Yes
AUTO-REVERSE	Yes
LOCK FUNCTION	Yes
INTERMITTENT MODE	Yes
AUTOMATIC SHUT DOWN	Yes, after 10 sec
DIMENSION (WXHXD)	354x77x369 mm
PERMISSIBLE AMBIENT TEMPERATURE	5-40°C
POWER INPUT	10 W
WEIGHT	4 Kg

We reserve the right to make technical alterations
We do not assume liability for errors in printing, typing or transmission

VELP Official Partner

DESIGNED AND MANUFACTURED IN ITALY

VELP SCIENTIFICA

ITALY – HQ
Via Stazione 16
20865 Usmate (MB) Italy
Tel. +39 039 628811
velpitalia@velp.com

INDIA
velpindia@velp.com

USA
155 Keyland Court, Bohemia
NY 11716 - U.S.
Tel. +1 631 573 6002
velpusa@velp.com

CHINA
Xinlong Rd Building 28, Lane 1333
Shanghai city - China
Tel. +86 18616509163
velpchina@velp.com

Rev 1 11.2019