



LIPIDOMIX[®] Quantitative Mass Spec Standards

Exclusively available from MilliporeSigma*

- Single-use vials
- Ready-to-use concentrations
- Concentrations verified using quantitative NMR
- Certificate of analysis for every batch
- Reduce standard preparation time with high-purity LC/MS grade solvents formulated with trustworthy Avanti[®] purity

Deuterated Ceramide LIPIDOMIX[®] Quantitative Mass Spec Internal Standard

Product Number 330713X-1EA

Deuterated version of 4 ceramide compounds found to be relevant in determining CVD risk. Each ampoule contains 1 mL of 1:1 DCM:MeOH solution with a mixture of four lipid standards. Concentrations are verified for use as a quantitative standard.

Mixture Component	MW	µg/mL	µM
C16 Ceramide-d7 (d18:1-d7/16:0)	544.944	21.8	40
C18 Ceramide-d7 (d18:1-d7/18:0)	572.997	11.5	20
C24 Ceramide-d7 (d18:1-d7/24:0)	650.113	26.3	40
C24:1 Ceramide-d7 (d18:1-d7/24:1(15Z))	655.141	13.1	20

Odd-Chained LIPIDOMIX[®] Quantitative Mass Spec Internal Standard

Product Number 330711X-1EA

Odd-chained lipids for use as internal standards in lipidomic analysis. Each sealed ampoule contains 1 mL 1:1 DCM:MeOH solution with a mixture of 16 lipid standards. Concentrations are verified for use as a quantitative standard.

Mixture Component	MW	µg/mL	µM
17:1 Lyso PG (Na Salt)	518.56	13	25
17:1 Lyso PA (NH ₄ Salt)	439.524	15	36
17:1 Lyso PI (NH ₄ Salt)	601.664	13	22
17:1 Lyso PS (Na Salt)	531.552	13	25
17:1 Lyso PC	507.641	575	1125
17:1 Lyso PE	465.568	12	25
17:0-17:0 DAG	596.978	300	500
17:0-17:0-17:0 TAG	849.42	1500	1750
12:0 SM (d18:1/12:0)	646.922	650	1000
17:0-14:1 PC	717.996	3775	5250
17:0-14:1 PS (NH ₄ Salt)	736.957	180	250
17:0-14:1 PG (NH ₄ Salt)	723.958	90	125
17:0-14:1 PA (NH ₄ Salt)	649.879	15	25
17:0-14:1 PE	675.917	120	175
17:0-14:1 PI (NH ₄ Salt)	812.02	200	250
17:0 Chol Ester	639.089	8475	13250

* MilliporeSigma is the exclusive supplier of Avanti[®] Polar Lipids to customers in Canada.

More than Lipids

Browse [Sigma-Aldrich.com/Avanti](https://www.sigmaaldrich.com/Avanti) to explore more than **2,000 Avanti® Polar Lipids** products with **99% purity**. All products are manufactured by Avanti® Polar Lipids and backed by the same quality standards and informed techniques. Because they're available from MilliporeSigma, ordering is easy, inventory is reliable, and support is always within reach.

- Storage and Handling of Lipids
- Fatty Acid Distribution
- Phase Transition Temperatures
- Miscibility of Phospholipid Binary Mixtures
- Ionization Constants of Phospholipids
- Critical Micelle Concentrations (CMCs)

SPLASH® LIPIDOMIX® Quantitative Mass Spec Internal Standard

Product Number 330707-1EA

Deuterated lipid internal standards in amounts relative to human plasma lipid concentrations. Each sealed ampoule contains 1 mL methanol solution containing 14 lipid classes. Concentrations are verified for use as a quantitative standard.

Mixture Component	MW	µg/mL	µM
15:0-18:1(d7) PC	753.11	160	210
15:0-18:1(d7) PE	711.03	5	7
15:0-18:1(d7) PS (Na Salt)	777.02	5	7
15:0-18:1(d7) PG (Na Salt)	764.02	30	40
15:0-18:1(d7) PI (NH4 Salt)	847.13	10	12
15:0-18:1(d7) PA (Na Salt)	689.94	7	10
18:1(d7) Lyso PC	528.72	25	45
18:1(d7) Lyso PE	486.64	5	10
18:1(d7) Chol Ester	658.16	350	530
18:1(d7) MAG	363.59	2	5
15:0-18:1(d7) DAG	587.98	10	16
15:0-18:1(d7)-15:0 TAG	812.37	55	70
d18:1-18:1(d9) SM	738.12	30	40
Cholesterol (d7)	393.71	100	250

Ceramide LIPIDOMIX® Quantitative Mass Spec Standard

Product Number 330712X-1EA

Calibration mixture of 4 compounds found to be relevant in determining CVD risk. Each ampoule contains 1 mL of 1:1 DCM:MEOH solution with a mixture of four lipid standards. Concentrations are verified for use as a quantitative standard.

Mixture Component	MW	µg/mL	µM
C16 Ceramide (d18:1/16:0)	537.901	16.1	30
C18 Ceramide (d18:1/18:0)	565.954	8.5	15
C24 Ceramide (d18:1/24:0)	650.113	48.8	75
C24:1 Ceramide (d18:1/24:1(15Z))	648.097	24.3	37.5

SPLASH® II LIPIDOMIX® Quantitative Mass Spec Internal Standard

Product Number 330709W-1EA

Deuterated lipid internal standards in amounts relative to human plasma lipid concentration now includes plasmalogen species. Each sealed ampoule contains 1 mL methanol solution with a mixture of 12 lipid standards. Concentrations are verified for use as a quantitative standard.

Mixture Component	MW	µg/mL	µM
15:0-18:1(d7) PC	753.11	160	210
15:0-18:1(d7) PE	711.03	5	7
15:0-18:1(d7) PS (Na Salt)	777.02	8	10
15:0-18:1(d7) PI (NH4 Salt)	847.13	8	10
18:1(d7) Lyso PC	528.72	25	45
18:1(d7) Lyso PE	486.64	0.5	1
18:1(d7) Chol Ester	658.16	350	530
C18(Plasm)-18:1(d9) PC	781.19	8	10
15:0-18:1(d7) DAG	587.98	12	20
15:0-18:1(d7)-15:0 TAG	812.37	55	70
d18:1-18:1(d9) SM	738.12	30	40
C18(Plasm)-18:1(d9) PE	739.11	0.07	0.1

The life science business of Merck KGaA, Darmstadt, Germany operates as MilliporeSigma in the U.S. and Canada.

© 2018 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved. MilliporeSigma and the vibrant M are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. All other trademarks are the property of their respective owners. Detailed information on trademarks is available via publicly accessible resources.

Lit. Code: MS_FL2653EN

Polar Bear photo provided by: Kyriakos Kaziras

MilliporeSigma
400 Summit Drive
Burlington, MA 018030

[SigmaAldrich.com/Avanti](https://www.sigmaaldrich.com/Avanti)

