



- World's first glass Carboy with 83B and 120mm caps
- Sizes range from 5 L - 50 L
- Large, visible writing surface on bottle for additional labeling; white graduations for identification of approximate volume; retrace code for identification
- Borosil® 3.3 Borosilicate Glass is mechanically strong, chemically resistant, and withstands thermal shock
- Bottle, VersaCap®, and Pouring Ring are autoclavable and comply with USP-VI standards

The PUREGRIP® Glass Carboy encompasses the latest offering in Foxx's collaboration with Borosil®. Combining the quality of Borosil® glassware with Foxx's innovative, user-focused designs, PUREGRIP® Carboys are the first ever 83mm Glass Carboy on the market. This product line features the largest writing surfaces and visible graduations on a glass carboy, while including our patented VersaCap® made from Class VI, Animal Free, Polypropylene.


A platinum-cured silicone O-ring ensures our leak-proof seal while the large handles with finger grips allow for easy tightening and opening. Our Open VersaCap® technology, sold separately, is also compatible with a variety of adapter inserts, enabling users to quickly change top connections to match their application needs. This product line is autoclavable and sterilizable.



- 1 Frosted surface on top of cap for convenient labeling
- 2 Patented VersaCap® is leak-proof, has replaceable platinum-cured silicone gaskets, and provides the ultimate in top-connection flexibility
- 3 USP Class VI, Animal-Free Polypropylene VersaCap® and Platinum Cured Silicone Gasket for leakproof, drip-free experience
- 4 Sloped shoulders for smooth, natural pouring motion
- 5 Largest enamel in the industry for additional labeling; white graduations for identification of approximate volume; retrace code for identification
- 6 Easy to read graduation marks



PUREGRIP® is a registered trademark of Foxx Life Sciences.



	Part Number	Description	Material	Cap Size (mm)	Autoclavable	Qty/Pack
PUREGRIP® Carboys	1551033-FLS	PUREGRIP® Glass Carboys, Round, Clear, 5L	BORO	83	Yes	1
	1551038-FLS	PUREGRIP® Glass Carboys, Round, Clear, 10L	BORO	83	Yes	1
	1551040-FLS	PUREGRIP® Glass Carboys, Round, Clear, 20L	BORO	120	Yes	1
	15R-E121-FLS	PUREGRIP® Glass Carboys, Round, Clear, 50L	BORO	120	Yes	1
Versacap® 83B	205-1003-RLS	Versacap®, Closed	PP	83	Yes	1
	205-1004-RLS	Versacap®, Open with closed adapter	PP	83	Yes	1
	205-1007-RLS	Versacap®, Open with adapter, 1/4" HB x 2 and Vent	PP	83	Yes	1
	205-1008-RLS	Versacap®, Open with adapter, 1/2" HB x 2 and Vent	PP	83	Yes	1
	205-3001-RLS	Adapter, Closed	PP	83	Yes	1
	205-3002-RLS	Adapter, Quick Connect, 1/4" HB x 2	PP	83	Yes	1
	205-3003-RLS	Adapter, Quick Connect, 3/8" HB x 2	PP	83	Yes	1
	205-3004-RLS	Adapter, Quick Connect, 1/4" HB x 3	PP	83	Yes	1
	205-3005-RLS	Adapter, Quick Connect, 3/8" HB x 3	PP	83	Yes	1
	205-3006-RLS	Adapter, Quick Connect, 1/4" HB x 4	PP	83	Yes	1
	205-3007-RLS	Adapter, Quick Connect, 3/8" HB x 4	PP	83	Yes	1
	205-5001-RLS	Adapter, Molded, 1/4" HB x 2 and Vent	PP	83	Yes	1
	205-5002-RLS	Adapter, Molded, 1/2" HB x 2 and Vent	PP	83	Yes	1
	205-3001-RLS	Adapter, Closed Clearview®	PC	83	Yes	1

* EZBio® Cap Assemblies are compatible with the 83B VersaCap® and can be purchased separately.