

2025-26

Analyte Quarterly



Beyond Biomarkers

Keep your focus on the next stage. Our rigorously tested and limitation-lifting immunoassay platforms provide you with all the AssayAbilities to take your biomarker research further.




MilliporeSigma is the U.S. and Canada Life Science business of Merck KGaA, Darmstadt, Germany.

Millipore®

Preparation, Separation,
Filtration & Testing Products

Beyond Biomarkers

We are committed to delivering the best possible immunoassays for your research needs. Whether you are using our industry-leading MILLIPLEX® multiplex panels to broadly survey multiple analytes, performing femtogram/mL biomarker analysis using the FemtoQuest™ ultrasensitive immunoassay platform, or examining single proteins with our tried-and-true ELISAs and RIAs, you can confidently expect reliable measurements, a simplified user experience, and knowledgeable scientific partners to help drive your biomarker project from hypothesis to publication.



Designed Reliability

Our Conferma® ELISAs are engineered for endogenous detection and lot-to-lot consistency of routine-use biomarkers to keep your data reproducible, run after run.



Genuine Flexability

Our industry-leading MILLIPLEX® multiplex assays for the Luminex® platform give you the FlexAbility to select your combination of biomarkers to simultaneously analyze with ease.




Next-Level Detectability

Our ultrasensitive SMC® kits for the FemtoQuest™ platform take your research to the next level by detecting biomarkers down to fg/mL levels.



Complete Compareability

Our Belysa® Immunoassay Curve Fitting Software helps you quickly compare your standard and sample curves with ease, confirming that your methods and plates ran consistently.



Expert Customability

Our Custom Assay Development & Innovation (CADI) team of experienced scientists partner with you to develop custom immunoassays for your biomarker(s) of interest, accelerating your projects from discovery to clinical trials.



Keep your focus on the next stage.



Immunoassays at a Glance

		MILLIPLEX® Multiplex Assays		SMC® Assays	ELISAs
		Qualified Assays	Screening Assays		
Species	Human	•	•	•	•
	Mouse	•		•	•
	Rat	•		•	•
	Non-Human Primate	•		•	•
	Canine	•			•
	Feline	•			•
	Bovine	•			•
	Chicken	•			
	Equine	•			•
	Ovine	•			•
	Porcine	•			•
	Multi-Species	•		•	•
Analytes	Human	>620	115	>40	>1,000
	Mouse	>280		3	>300
	Rat	>170		3	>190
	Non-Human Primate	>65		1	>70
	Canine	>40		1	>30
	Feline	>15			>20
	Bovine	>15			>20
	Chicken	>10			
	Equine	>25			>20
	Ovine	>15			>5
	Porcine	>15			>30
	Multi-Species	>5		1	>5
Research Areas	Immunology/Inflammation	•	•	•	•
	Immune Response	•	•	•	•
	Virology	•		•	•
	Metabolism/Endocrinology	•	•	•	•
	Cardiovascular Disease	•	•	•	•
	Bone	•	•		•
	Cancer	•	•	•	•
	Neuroscience	•	•	•	•
	Toxicity	•	•		•
	Cell Signaling	•			•
Kit Format *only applies to MILLIPLEX® kits **Conferma® ELISAs only	Configurable (Select Your Own Analytes)*	•	•	-	-
	Premixed (Fixed Panel)*	•	•	-	-
	Bulk Premixed (Space Saver)*	•	•	-	-
	Custom Premix*	•	•	-	-
	Lot Matched at Kit Level			•	•**
Qualified Sample Types (see specific kits for more details)	Serum/Plasma	•		•	•
	Cell Culture Supernatants	•	Screening assays are sample agnostic	•	•
	Cell/Tissue Lysates	•			•
	Cerebrospinal Fluid	•		•	•
	Urine	•			•
Custom Kits and Services	—	•		•	•

New Immunoassay Products

New Kits and Instruments

Description	Species	Cat. No.
Instruments		
FemtoQuest™ System	-	95-0200-00
BioTek® 405™ TSUVS Plate Washer for SMC® and MILLIPLEX® Technology	-	95-0004-06
SMC® High Sensitivity Kits		
2-Plex cTnI, IL-6	Human	03-0217-2P
2-Plex IL-1β, IL-1α	Human	03-0218-2P
2-Plex TNFα, IL-6	Human	03-0216-2P
2-Plex IL-17A, IL-17F	Human	03-0214-2P
2-Plex IL-23, IL-22	Human	03-0215-2P
CTLA-4 Singleplex	Human	03-0220-00
IL-22 Binding Protein Singleplex	Human	03-0219-00
Bead-Based Assay Development Kit (4 Plates)	-	03-0222-00
MILLIPLEX® Multiplex Panels		
AAV Serotyping Panel	Human	AAVSERG-230K
Cell Health Panel	Human	48-691MAG
Cytokine/Chemokine/Growth Factor Expanded Panel 1	Mouse	MCYT1-190K
Humanized Mouse Panel	Human, Mouse	HUMU-210K
Neurodegenerative Autoantibody Panel	Human	HNDGAB-220K
TSH Singleplex	Rat, Mouse	RMTSH-200K

Coming Soon

Description	Species
SMC® High Sensitivity Kits	
2-Plex Aβ42, Aβ40	Human
2-Plex NF-L, Total Tau	Human
2-Plex IL-17A, IL-22	Human
Plate-Based Immunogenicity Assay Development Kit	-
MILLIPLEX® Multiplex Panels	
Dual Reporter IgG/IgM Reagent Pack	Human
Cytokine/Chemokine/Growth Factor Expansion Panel	Porcine

Reveal Elusive Biomarkers

Conquer your pursuit for immunoassay sensitivity with the ultrasensitive FemtoQuest™ system

Measure down to **fg/mL** levels of biomarkers using advanced SMC® technology with improved precision and robust data. This simple-to-use system has an enhanced optical design for **higher quality dual-plex and single analyte analysis** for efficient and reliable results.




Explore more at
SigmaAldrich.com/femtoquest



SMC® Technology

SMC® technology provides maximum immunoassay performance while following a workflow similar to traditional ELISA technology, as shown below for dual-plex analysis. By combining a unique assay elution step and robust digital counting on the FemtoQuest™ system, SMC® technology improves signal-to-noise ratios over traditional immunoassay technologies, enhancing quantification at both low and high levels of expression with one system. The FemtoQuest™ instrument can be used for measuring both single analyte and dual-plex assays.



Steps 2-3

Antibodies translate each biomarker into a signal

Step 4

Fluorescent dye-labeled detection antibodies dissociate from the immunocomplex

Step 5

On the FemtoQuest™ instrument, signal is collected from free-floating fluorochromes using a rotating laser, camera, and counting individual molecules by an avalanche photodiode

Digital counting improves sensitivity and dynamic range

The FemtoQuest™ system captures all digital events counted above the background threshold. Using enhanced algorithms, digital events are computed across a spectrum of time series for a single standard. This digital counting of single molecules improves the assay sensitivity and extends the dynamic range beyond what can be achieved with traditional methods.


Read More About Ultrasensitive Technology

Explore all the ways researchers are using SMC® ultrasensitive assays at SigmaAldrich.com/smc-learn



control your Biomarker Quest

Gain your desired
immunoassay sensitivity
with the ultrasensitive
FemtoQuest™ system



Start Your Quest at SigmaAldrich.com/femtoquest

FOR RESEARCH USE ONLY. NOT FOR USE IN DIAGNOSTIC PROCEDURES.

SMC® Technology for High Sensitivity Analysis

Control Your Biomarker Quest



Gain your desired immunoassay sensitivity with the ultrasensitive FemtoQuest™ system.

- Measure down to femtogram/mL levels
- Improved precision and robust data
- Perform **dual-plex** and **single analyte** analysis
- Low maintenance and automation compatible
- Use with a variety of off-the-shelf kits
- Integrated data analysis
- Lightweight fluidics-free benchtop instrument
- Cat. No. **95-0200-00**

Dynamic Range	>4 logs
Limit of Detection (LOD)	<1 fM
Instrument Footprint	Height: 358.53 mm (14.11 in) Width: 444.5 mm (17.5 in) Depth: 609.91 mm (24.0 in)
Instrument Weight	29.7 kg (65.5 lb)
Read Format	96-well assay format read on RFID-tagged SMC® Read Plates
Regulatory Compliance	LIMS compatible
Automation Compatible	Compatible with automation, including the AAW™ Workstation



Continually expanding list of available 2-Plex kits for use on the FemtoQuest™ instrument include:

- IL-17A, IL-17F (Cat. No. 03-0214-2P)
- IL-23, IL-22 (Cat. No. 03-0215-2P)
- TNFα, IL-6 (Cat. No. 03-0216-2P)
- cTnI, IL-6 (Cat. No. 03-0217-2P)
- IL-1β, IL-1α (Cat. No. 03-0218-2P)

Three Levels of Onsite Service Support for FemtoQuest™ System

- **Total Service:** Unlimited visits including labor, travel, expenses and all parts for any service for one year.
- **Advanced Service:** Labor, travel and expenses for one preventative maintenance visit and one floating visit for one year.
- **Essential Service:** Labor for one preventative maintenance visit for one year.

SMC® Singleplex High Sensitivity Kits

Product Description	Cat. No.	LLOQ (pg/mL) ¹	Species ²	Sample Type ³
Immunology/Inflammation				
IFN-α2	03-0186-00	0.06	H	P,S
IFN-β1	03-0191-00	0.15	H	P,S
IFN-γ	03-0181-00	0.03	H	P,S
IFNλ1	03-0213-00	0.26	H	P,S
IL-1α2	03-0167-00	0.12	H	P,S
IL-1β	03-0160-00	0.20	H	P,S
IL-2	03-0195-00	0.09	H	P,S
IL-4	03-0161-00	0.04	H	P,S
IL-5	03-0168-00	0.04	H	P,S
IL-6	03-0155-00	0.08	H	P,S
IL-10	03-0176-00	0.10	H	P,S
IL-12p70	03-0182-00	0.10	H	P,S
IL-13	03-0156-00	0.04	H	P,S
IL-17A/F Heterodimer	03-0177-00	2.34	H	P,S
IL-17A	03-0159-00	0.07	H	P,S
IL-17F	03-0164-00	0.20	H	P,S
IL-18	03-0190-00	0.09	H	P,S
IL-22	03-0162-00	0.10	H	P,S
IL-22BP NEW	03-0219-00	3.91	H	P,S
IL-23	03-0157-00	0.10	H	P,S
MCP-1	03-0187-00	0.15	H	P,S
TNFα	03-0163-00	0.20	H	P,S
VEGF-A	03-0180-00	0.20	H	P,S
Neuroscience				
Phospho-α-Synuclein(Ser129)	03-0188-00	0.10	H	P,S,C
Total-α-Synuclein	03-0196-00	1.95	H	P,S,C
Amyloid beta 1-40	03-0145-00	5.86	H,M,R	P,C
Amyloid beta 1-42	03-0146-00	0.98	H,M,R	P,C
BDNF	03-0171-00	0.04	H	P,S,C
GFAP	03-0203-00	0.23	H	P,S,C
NF-L	03-0202-00	0.87	H	P,S,C
NPTX2	03-0199-00	0.58	H	P,S,C
SNAP-25	03-0206-00	0.26	H	P,S,C
TDP-43	03-0205-00	5.21	H	P,S,C
Phospho-Tau181	03-0184-00	0.94	H	P,S,C
Phospho-Tau217	03-0210-00	1.95	H	P,S,C
Phospho-Tau231	03-0211-00	1.95	H	P,S,C
Total Tau	03-0185-00	4.69	H	P,S,C
UCHL1	03-0183-00	2.60	H	P,S,C

SMC® Singleplex High Sensitivity Kits (continued)

Product Description	Cat. No.	LLOQ (pg/mL) ¹	Species ²	Sample Type ³
Cancer				
CTLA-4 NEW	03-0220-00	0.30	H	P,S
PD-1	03-0207-00	3.47	H	P,S
PD-L1	03-0208-00	0.78	H	P,S
Cardiovascular				
cTnI	03-0154-00	0.69	H,Cy,R,C,GP	P,S
Metabolism/Endocrinology				
Glucagon	03-0153-00	0.78	H,M,R	P
Immunogenicity				
IgE ⁴	03-0201-00	31.00	H	P,S
IgM ⁴	03-0204-00	206.00	H	P,S
Virology				
SARS-CoV-2 RBD IgG ⁵	03-0193-00	NA ⁵	H	P,S
SARS-CoV-2 S1 IgA ⁵	03-0197-00	NA ⁵	H	P,S

New SMC® 2-Plex High Sensitivity Kits for Use on the FemtoQuest™ Instrument

Product Description	Cat. No.	LLOQ (pg/mL) ¹	Species ²	Sample Type ³
Immunology/Inflammation				
2-Plex IL-1 β , IL-1 α NEW	03-0218-2P	0.04 (IL-1 β), 0.04 (IL-1 α)	H	P,S
2-Plex TNF α , IL-6 NEW	03-0216-2P	0.02 (TNF α), 0.06 (IL-6)	H	P,S
2-Plex IL-17A, IL-17F NEW	03-0214-2P	0.02 (IL-17A), 0.09 (IL-17F)	H	P,S
2-Plex IL-23, IL-22 NEW	03-0215-2P	0.04 (IL-23), 0.09 (IL-22)	H	P,S
Cardiovascular				
2-Plex cTnI, IL-6 NEW	03-0217-2P	0.35 (cTnI), 0.06 (IL-6)	H	P,S

¹ LLOQ: Lowest point on standard curve with CV < 20% and accuracy within 20% of expected values. Lot-specific LLOQ will be reported on the Certificate of Analysis. ² Optimized for first species type listed. Other listed species have been tested, but not optimized for peak performance. Key: H=Human; M=Mouse; R=Rat; GP=Guinea Pig; Cy=Cynomolgus Monkey; C=Canine. ³ Optimized for use in sample type(s) listed. Key: P=Plasma; S=Serum; L=Lysate; U=Urine; C=Cerebrospinal Fluid (CSF). ⁴ Plate-based assay. ⁵ Qualitative assay.

Multiplexing Options That Fit Your Purpose

Introducing Screening and Qualified MILLIPLEX® Assays

Compelling PlexAbility with MILLIPLEX® Screening Assays


- Save sample, time, and money by profiling up to 115 analytes simultaneously without sacrificing specificity
- Excludes Serum Matrix to create sample agnostic panel for greater flexibility
- Ideal for detecting differences between experimental groups
- Human assay available
- Uses same critical raw materials as Qualified assays

Screen to identify analytes of interest and move to Qualified for further analysis



Genuine PlexAbility with MILLIPLEX® Qualified Assays

- Lot-to-lot reproducibility with rigorous QC testing
- Includes key reagents like Quality Controls and Serum Matrix for sample normalization
- Ideal for long-term or cross-site studies
- Broadest selection of analytes across research areas and species
- Configurable, premixed, and bulk kit options to fit your exact research needs



MILLIPLEX® Analyte Index

Analyte	Page No.	Analyte	Page No.	Analyte	Page No.
4-6		Argonaute-2 (Ago2) (autoantibody)	21	CD80/B7-1	20,24
4-1BBL/TNFSF9	20,24	ATF2 (Thr71)	28	CD81	20
4E-BP1 (total)	28	ATR (total)	28	CD86/B7-2	20
4E-BP1 (Thr37/46)	28	AXL (soluble)	20	CD137/4-1BB/TNFRSF9 (soluble)	17,20,22,24
5'-NT/CD73	20,21,24,25	B		CD226/DNAM-1	20,24
6Ckine/CCL21/Exodus-2	17,22,26	β-2-Microglobulin	21,24,25,26	CD9	20
A		β-Endorphin	21,25	CEA	20
α-1-Acid Glycoprotein (AGP)	19,23,25	β2-Glycoprotein (autoantibody)	18	CENP-A (autoantibody)	18
α-1-Antitrypsin (A1AT)	21	β-Tubulin (total)	30	CENP-B (autoantibody)	18
α-1 Microglobulin	21	B7-H2/ICOSL	20,24	CHI3L1/YKL40	18,20,22
α-2 Macroglobulin (A2M)	19,21,23,25	B7-H3/CD276	20,24	Chk1 (Ser345)	28
α-Fetoprotein (AFP)	19,20	B7-H4/VTCN1	20	Chk2 (Thr68)	28
α-MSH	21,24,25	B7-H5/VISTA	20	CHOP (Total)	27
α-Synuclein	21	B7-H6	20	CK-MB	16,19
α-Synuclein (autoantibody)	21	BAD (total)	27	Cleaved PARP (total)	27
AAV1 (serology)	19	BAD (Ser112)	27	Clusterin	21,24,25,26
AAV2 (serology)	19	BAFF/Blys	17,18,20,22	CNTF	19,22
AAV5 (serology)	19	BAFF/Blys (autoantibody)	18	Collagen IV	21
AAV6 (serology)	19	BAX (total)	27	COMP (cartilage oligomeric matrix	18
AAV8 (serology)	19	BCA-1/CXCL13	16,17,22,24,26	protein)	18
AAV9 (serology)	19	Bcl-2 (total)	25	Complement C1q	18
AChR (autoantibody)	21	Bcl-2 (Ser70)	25	Complement C2	18
ACTH	16,19,20,22,23,24,25,26	Bcl-xL (total)	25	Complement C3	18,21
Active Caspase 8 (total)	27	Bcl-xL/BAD (interaction)	25	Complement C3b	18
Active Caspase 9 (total)	27	BDNF	16,19,21,23,24	Complement C4	18,21
ADAMTS13	19	Betacellulin	22,24	Complement C4b	18
Adiponectin	19,23,24,25	BIM	27	Complement C5	18
Adipsin/Factor D	18,19,23	Blk (Tyr389)	29	Complement C5a	18
AGNA (SOX1) (autoantibody)	21	BMP-9	20	Complement C5b-9	18
Agouti-Related Protein (AgRP)	19,22	BNP	16,19	Complement C9	18
ALK-1 (soluble)	24	BRAF (Ser446)	29	Complement Factor B	18
Akt/PKB (Ser473)	27,28,29	BRAK/CXCL14	18	Complement Factor H	18,21
Akt/PKB (total)	27,28,29	BTLA	20,24	Complement Factor I	18
Akt1 (Ser473)	29	C		Complex IV (Total)	27
Akt1 (total)	29	c-Jun (Ser73)	28	Connective Tissue Growth Factor	25
Akt2 (Ser474)	29	c-Kit (panTyr)	28	(CTGF)	25
Akt2 (total)	29	c-Kit/SCFR (soluble)	20	Contactin-1	21
Albumin	21,25,26	c-Met/HGFR (panTyr)	28	Corticosterone	24
ALDH1A1	20	c-Myc (total)	28	Cortisol	21,26
AMPA -R (autoantibody)	21	C-Peptide	16,19,22	CRAF (Ser338)	29
Amphiphysin (autoantibody)	21	C-Peptide 2	23,24	Creatine Kinase Muscle (CKM)	25
Amphiregulin	24	C-Reactive Protein (CRP)	19,21,23,26	CREB (Ser133)	28,29
Amylin (active)	16,19,22,23,24	C1q (autoantibody)	21	CREB (total)	28,29
Amylin (total)	19,26	CA125	20	CRMP5 (autoantibody)	21
Amyloid beta 1-40 (Aβ 1-40)	21,24	CA15-3	20	CRYAB (autoantibody)	21
Amyloid beta 1-42 (Aβ 1-42)	21,24	CA19-9	20	CTACK/CCL27	17,19,23,26
Amyloid beta 1-42 (Aβ 1-42)		Calbindin	21	CTAG1B/NY-ESO-1 (autoantibody)	20
(autoantibody)	21	Calreticulin (CALR)	20	CTLA-4/CD152	20,24
Angiogenin (ANG)	21	Carbonic Anhydrase 9 (CA9)	20	CXCL6/GCP-2	16,17,18,19
Angiopoietin-2	20,24	Cardiac Troponin I (cTnI)	16,19,23,25	CXCL16	17,18,19,22
Angiostatin/Kringle	20	Cardiac Troponin T (cTnT)	20,23,25	Cyclin B1 (Total)	27
Angiotensinogen (AGT)	21	Cathepsin D	20,21	CYFRA21-1	17
ANGPTL3	19	Caveolin-1 (CAV-1)	25	Cystatin C	21,24,25,26
ANGPTL4	19	CCL25/TECK	22	D	
ANGPTL6/AGF	19	CCL28	17,18	D-dimer	19
ANNA2 (Ri)/NOVA1 (autoantibody)	21	CCNB1/Cyclin B1 (autoantibody)	20	DKK1	16,20,25
Apelin	19	CD3ε (panTyr)	29	DPP4	20
Apolipoprotein AI (Apo AI)	20,21	CD14 (soluble)	20	DPPX (autoantibody)	21
Apolipoprotein AII (Apo AII)	20	CD25/IL-2Rα	18,20,22,24	DRD2 (autoantibody)	21
Apolipoprotein B (Apo B)	20	CD27	20,24	E	
Apolipoprotein CII (Apo CII)	20	CD28	20	E-Cadherin	20,24
Apolipoprotein CIII (Apo CIII)	20,21	CD30/TNFRSF8 (soluble)	18,20,22	EGF	16,17,20,21,22,24,25
Apolipoprotein E (Apo E)	20,21	CD31/PECAM-1 (soluble)	20,23,24	EGFR/HER1/ErbB1 (soluble)	18,20
ApoE4	21	CD40	20,24	EGFR2/Her2/ErbB2 (soluble)	20
APRIL	17,20	CD40L (soluble)	16,17,20,22,23	EGFR3/Her3/ErbB3 (soluble)	20
AQP4 (autoantibody)	21	CD44	20	ELAVL4 (HuD) (autoantibody)	21
Arginase-1 (ARG1)	20,21,25	CD63	20	eIF-4B (Ser422)	28
Argonaute-2 (Ago2)	20				

MILLIPLEX® Analyte Index (continued)

Analyte	Page No.	Analyte	Page No.	Analyte	Page No.
eIF-4E (Ser209).....	28	Glial Fibrillary Acidic Protein (GFAP)	21	IGFBP2	19
eIF-4G (Ser1108).....	28	Glial Fibrillary Acidic Protein (GFAP)		IGF2BP2/IMP2 (autoantibody)	20
eIF2a (Ser51).....	28	(autoantibody).....	21	IGFBP3	19,20
ENA-78/CXCL5.....	16,17,27	GLP-1 (active).....	19,22,23,24,26	IGF2BP3/IMP3 (autoantibody)	20
Endocan-1 (ESM-1).....	19,23	GLP-1 (total)	16,19,23,24	IGFBP4	19
Endoglin	20,24	Glucagon	16,19,22,23,24,26	IGFBP5	19
Endostatin	20	GM-CSF	16,17,18,22,23,24,25,26	IGFBP6	19
Endothelin-1.....	20,24	GnRH.....	19,23	IGFBP7	19
ENO1 (autoantibody).....	20	GOT1.....	25	IgG1.....	19,23
Eotaxin/CCL11.....	16,17,22,24,26	GP130 (soluble)	18,22	IgG2.....	19
Eotaxin-2/CCL24/MPIF-2.....	16,17	Granulysin	20	IgG2a.....	23
Eotaxin-3/CCL26.....	16,17	Granzyme A	16,17,22	IgG2b.....	23
EpCAM.....	20	Granzyme B	16,17,18,20,22,24	IgG3.....	19,23
Erythropoietin (EPO)	16,19,22,23,24	GROa/CXCL1	16,17,22,23,24,25,26	IgG4.....	19
ErbB1/EGFR (panTyr).....	28	GRP78 (Total).....	27	IgM	19,23
ErbB2/HER2 (panTyr).....	28	GSK3a (total).....	27	IkBa (Ser32).....	28
ErbB3/HER3 (panTyr).....	28	GSK3a (Ser21).....	27	IKKa/β (Ser177/181).....	28
ErbB4/HER4 (panTyr).....	28	GSK3β (total).....	27	IL-1a.....	16,17,18,22,23,24,25,26
Erk/MAPK 1/2 (Thr185/Tyr187)	28,29	GSK3β (Ser9).....	27	IL-1a (autoantibody).....	18
Erk/MAPK 1/2 (total).....	28,29	GSTa	21,25	IL-1β.....	16,17,19,20,22,23,24,25,26
E-Selectin (soluble).....	20,23,25	H		IL-1RI (soluble).....	18,22
Estradiol	26	H2AX (Ser139)	27,28	IL-1RII (soluble).....	18,22
Exodus-2/CCL21/6Ckine	17,22,26	Haptoglobin.....	19,23,25,26	IL-1Ra.....	16,17,22,26
F		HB-EGF.....	16,20	IL-2	16,17,22,23,24,25,26
FABP1.....	19,21	HCC-1/CCL14.....	18	IL-2 (autoantibody)	18
FABP3.....	16,19,21,25	HCC-4/CCL16	18	IL-2Ra (soluble)	18,20,22,24
FABP4.....	16,19	HCGβ.....	20	IL-3	16,17,22,23
FADD (Ser194).....	28	Hck (Tyr411).....	29	IL-3 (autoantibody)	18
Fas Ligand (sFasL) (soluble)		HE4.....	20	IL-4	16,17,22,23,24,25,26
.....	16,17,18,20,22,24	Hepsin	20	IL-4 (autoantibody)	18
Fas/TNFRSF6 (soluble)	16,17,18,20,22	HER2/ErbB2 (autoantibody)	20	IL-4R (soluble).....	18,22
Ferritin	20,21	HGF.....	16,19,20,24	IL-5	16,17,22,23,24,26
Fetuin A	19,21	HGFR/c-Met (soluble)	20	IL-6	16,17,19,20,22,23,24,25,26
FGF-1/FGF-acidic	20	HIF-1a (Total).....	27	IL-6 (autoantibody)	18
FGF-2/FGF-basic	16,20,22,24,26	HIF-1a (autoantibody).....	20	IL-6R (soluble).....	18,22
FGF-19.....	19	Histone H3 (Ser10).....	27	IL-6Ra (soluble)	20
FGF-21.....	16,19,23,24	HMGB1	17,18	IL-7	16,17,22,23,25
FGF-23	16,19,20,25	HSP27 (Ser78)	28	IL-8/CXCL8.....	16,17,18,19,20,22,23,25,26
FGFR1 (panTyr).....	28	HSP60 (autoantibody)	20	IL-8/CXCL8 (autoantibody).....	18
FGL1/Hepassocin	20	HSP70	18	IL-9	16,17,22
Fgr (Tyr412)	29	HSP70 (Total).....	27	IL-10.....	16,17,19,22,23,24,25,26
Fibrinogen.....	19,25	Human Serum Albumin (HSA).....	21	IL-10 (autoantibody).....	18
Fibroblast Activation Protein (FAP).....	20,20	HVEM	20,24	IL-11.....	16,17,18,22
Flotillin-1 (FLOT-1).....	20	I		IL-12.....	26
Flt3 Ligand.....	16,17,22,26	I-309/CCL1.....	16,17,26	IL-12 (p40)	16,17,22,23,26
Flt3 (panTyr)	28	ICAM-1 (soluble)	18,19,21,22,23,25	IL-12 (p40) (autoantibody)	18
Follistatin (FST).....	20,23,24	ICOS	20	IL-12 (p70)	16,17,22,23,24,26
Follistatin-like Protein 1 (FSTL1) 23,24,25		IDO1	20	IL-13.....	16,17,22,24,26
Fractalkine/CX3CL1.....	16,17,19,22,24,26	IFNa	22	IL-14/a -Taxilin.....	18
FSH	19,22,23,24,26	IFNa2	16,17,18,22	IL-15.....	16,17,19,22,23,24,25
Fyn (Tyr420).....	295	IFNa2 (autoantibody)	18	IL-15 (autoantibody).....	18
G		IFNβ	17,18,22	IL-16.....	17,22,25,26
Galectin-1	20,24	IFNβ (autoantibody)	18	IL-17A/CTLA8	16,17,22,23,24,25,26
Galectin-1 (GAL1) (autoantibody).....	20	IFNγ	16,17,18,22,23,24,25,26	IL-17A/CTLA8 (autoantibody).....	18
Galectin-3	20,24	IFNγ (autoantibody)	18	IL-17E/IL-25	17,22
Galectin-3 (GAL3) (autoantibody).....	20	IFNγ Receptor 1 (IFNGR1).....	18	IL-17F	16,17,22
GAPDH (total).....	20,30	IFNε	18	IL-17F (autoantibody)	18
G-CSF.....	16,17,20,22,23,24,26	IFNω	17,18	IL-18.....	16,17,18,19,22,23,24,25,26
G-CSF (autoantibody).....	18	IFNω (autoantibody).....	18	IL-18 (autoantibody).....	18
GDF-11	19	IgA.....	19,23	IL-18BPα	18
GDF-15	19,20,22	IgE.....	19,23	IL-19.....	18
GDNF.....	21	IGF-1.....	19	IL-20	17,22,26
GH	19,22,23,24,26	IGF-2.....	19	IL-21	16,17,22,25,26
Ghrelin (active).....	16,19,22,23,24,26	IGF1R (total)	27	IL-22	16,17,22
GIP (total).....	16,19,22,23,24,26	IGF1R (panTyr)	28	IL-22 (autoantibody).....	18
GITR	20,24	IGF1R (Tyr1135/1136)	27	IL-23	16,17,22,26
GITRL.....	20	IGFBP1	19	IL-24	17,18
				IL-27	17,22
				IL-28A/IFNλ2.....	17,18,22,26

MILLIPLEX® Analyte Index (continued)

Analyte	Page No.	Analyte	Page No.	Analyte	Page No.
IL-28B/IFNA3	18,22	MEK1 (Ser217/221)	29	Osteopontin (OPN)	16,20,21,24,25,26
IL-29/IFNA1	17,18	MEK1 (Ser222)	28	Osteopontin (OPN) (autoantibody)	18
IL-31	17,22	Melanoma Inhibitory Activity Protein (MIA)	20	Osteoprotegerin (OPG)	16,20,25
IL-32a	18	Melatonin	21,24	OX40/CD134	20
IL-33/NF-HEV (mature)	16,17,22,26	Mesothelin	20	Oxytocin	21,24,25
IL-34	17,18	mGluR1 (autoantibody)	21		
IL-35	17,18	Mi-2 (autoantibody)	18	P	
IL-36β/IL-1F8	18	MICA	20	PP16-INK4a (autoantibody)	20
IL-36Ra/IL-1F5	25,26	MICB	20	p21 (total)	28
IL-37/IL-1F7	18	Midkine	20	p38/SAPK2A/B (Thr180/Tyr182)	28,30
IL-38/IL-1F10	18	MIF	18,20	p38/SAPK2A/B (total)	28,30
Insulin	16,19,20,22,23,24,25,26	MIG/CXCL9	16,17,18,22,23	p53 (autoantibody)	20
IP-10/CXCL10	16,17,21,22,23,24,25,26	MIP-1α/CCL3	16,17,18,22,24,25,26	p53 (Ser15)	27,28
IR (total)	27	MIP-1β/CCL4	16,17,18,22,25,26	p53 (Ser46)	27
IR (Tyr162/1163)	27	MIP-1δ/MIP-5/CCL15	16,17,26	p70S6 Kinase (total)	27,28
Irisin	19,23,24	MIP-2/CXCL2	22,24	p70S6 Kinase (Thr389/412)	27,28
IRS1 (Ser636)	27	MIP-3α/CCL20	16,17,18,22,25	PAI-1 (total)	18,19,21,23,24,25
IRS1 (total)	27	MIP-3β/CCL19	16,17,18,22	Pancreatic Polypeptide (PP)	16,22,23,24,26
I-TAC/CXCL11	16,17,18,22	MIP-4/PARC/CCL18	18,21	PARK5/Uchl1	21
J		MMP-1	16,18	PARK7/DJ1	21
Jag1	19,23	MMP-2	16,18,22,23	PCA1 (Yo)/CDR2 (autoantibody)	21
JNK/SAPK1 (Thr183/Tyr185)	27,28,30	MMP-3	16,18,22,23	PCNA (autoantibody)	18
JNK/SAPK1 (total)	28,30	MMP-7	16,18	PD-1	20,24
Jo-1 (autoantibody)	18	MMP-8	18,22,23	PDGF-AA	16,17,21
K		MMP-9	16,18	PDGF-AB/BB	16,17,20,21
Kallikrein-6	20,21	MMP-10	16,18	PDGF-BB	26
KC-like Protein	25	MMP-12	16,18,22,23	PDGFRβ (panTyr)	28
KC/GRO/CINC-1/CXCL1	22,23,24,25,26	MMP-13	18	PD-L1	20,24
KIM-1	21,24,25,26	MOG (autoantibody)	21	PD-L2	20,24
Ki-67 (Total)	27	MPIF/CCL23	17,18	PEDF	21
Ku (autoantibody)	18	MSK1 (Ser212)	28	Pentraxin-3 (PTX3)	20
L		mTOR (Ser2448)	27,30	Perforin	16,17,20,22
Lactotransferrin (LTF)	18	mTOR (total)	27,30	Periostin	20
LAG-3	20,24	Mucin-1 (MUC1) (autoantibody)	20	Polyubiquitin K48-linkage (Total)	27
LAT (panTyr)	29	Myeloperoxidase (MPO)	19,20,21	Progranulin (pGRN)	20
LC3B (Total)	27	Myeloperoxidase (MPO) (autoantibody)	18	PL-12 (Alanyl-tRNA Synthetase) (autoantibody)	18
Lck (panTyr)	29	Myoglobin	19	Placental Growth Factor 2	23,24
Lck (Tyr394)	29	Myosin Light Chain 3 (MYL3)	25	Placental Growth Factor (PIGF)	16,19,20
Leptin	16,19,20,22,23,24,25,26	Myostatin/GDF8	16,19,23,24	Platelet Factor 4 (PF4)/CXCL4	19
Leucine-rich alpha-2-glycoprotein 1 (LRG1)	20	N		PF4 (autoantibody)	18
Leukemia Inhibitory Factor (LIF)	16,17,19,22,23,24,26	NAP-2/CXCL7	18	PM/Sc1 100 (autoantibody)	18
LH	19,22,23,24,26	NCAM (soluble)	21	PNMA1 (Ma1) (autoantibody)	21
LIGHT	19,23	NCAM1/L1CAM/CD171	20	Progesterone	26
LIX/CXCL5	22,24	Nectin-2	20	Prolactin	20,23,24,26
L-Selectin (soluble)	19	Nectin-4	20	ProMMP-9	22,23
Lymphotoxin/XCL1	17,18	Neurogranin (NRGN)	21	Properdin	18
Lyn (Tyr397)	29	Neuron-specific Enolase (NSE)	20,21	Proteinase 3 (autoantibody)	18
M		Neuropilin-1 (soluble)	20	PSA (free)	20
Mannose-Binding Lectin (MBL)	18	Neurotensin	21,24,25	PSA (total)	20
MBP (autoantibody)	21	Neutrophil Elastase-2 (ELA2)	18	P-Selectin (soluble)	19,23
MCAM/MUC18/sCD146	20	NFκB (total)	28	PTEN (total)	27
Mcl-1/BIM (interaction)	27	NFκB (Ser536)	28	PTEN (Ser380)	27
Mcl-1 (total)	27	NF-L (autoantibody)	21	PTH	20,21,25
MCP-1/CCL2	16,17,19,22,23,24,25,26	NGAL/Lipocalin-2	18,19,21,24,25,26	PVR/CD155	20
MCP-2/CCL8	16,17,22,26	NGF	16,19	PYY (total)	16,19,22,23,24,26
MCP-3/CCL7	16,17,22	NMDAR1 (autoantibody)	21		
MCP-4/CCL13	16,17,26	Notch1	23	R	
MCP-5/CCL12	22	NOXA/Mcl-1 (interaction)	27	RAGE (soluble)	18,21,22
M-CSF	16,17,18,22,23,25	NRXN3 (autoantibody)	21	RANKL	20
M-CSFR (panTyr)	28	NT-proBNP	16,19	RANTES/CCL5	16,17,21,22,24,25,26
MDC/CCL22	16,17,22	O		Ras (total)	29
MDH1	21	Oncostatin-M (OSM)	19,23	RasG12D (total)	29
MDM2 (total)	28	Osteoactivin	21	RasG12V (total)	29
		Osteocalcin (OC)	16,20	RBP4	21,26
		Osteocrin (OSTN)/Musclin	19,23,24	Renin	21,24
		Osteonectin/SPARC	16,19,20,23,24	Resistin	18,19,23
				Ribosomal P (autoantibody)	18

MILLIPLEX® Analyte Index (continued)

Analyte	Page No.	Analyte	Page No.	Analyte	Page No.
RNA Pol II (Ser 2)	27	Substance P	21,24,25	TNF RII (soluble) (sTNFR2)	18,22
RNP (autoantibody)	18	Superoxide Dismutase 1 (soluble)		TPO	16,17,26
RNP/Sm (autoantibody)	18	(sSOD1)	21	TRAIL/TNFSF10	16,17,20,26
RPS6 (Ser235/Ser236)	27	Superoxide Dismutase 2 (soluble)		Transglutaminase 2 (TGM2)	20,21
RPS6 (total)	27	(sSOD2)	21	TRAP5	20
S		Survivin/BIRC5 (autoantibody)	20	TREM2	21
S100B	21	Syntenin-1 (Syn-1)	20	Troponin I (TnI)	16,19,23,25
SARS-CoV-2 N	19	Syk (panTyr)	29	Troponin T (TnT)	20,23,25
SARS-CoV-2 RBD	19	T		TSC2 (total)	27
SARS-CoV-2 Spike S1	19	T3	24,26	TSC2 (Ser939)	27
SARS-CoV-2 Spike S2	19	T4	24,26	TSG101	20
SCF	16,17,20,26	TARC/CCL17	16,17,22,26	TSH	19,22,23,24,26
Scl-70 (autoantibody)	18	Tau (Total)	21	TSLP	16,17,26
Sclerostin (SOST)	16,20,25	Tau (Total) (autoantibody)	21	TWEAK	20
SDF-1/CXCL12	16,17,24,26	Tau (Thr181)	21	U	
SDH	21,25	Testosterone	26	ucMGP	20
Secretin	19,23,24	TFF-3	21,26	uPAR (soluble)/CD87	20
Serum Amyloid A (SAA)	19	TGFα	16,17,20,22	Uromodulin	21
Serum Amyloid P (SAP)	19,21,23	TGFβ1	26	Uteroglobin	18
Sex Hormone Binding Globulin (SHBG)		TGFβ2	26	V	
.....	20	TGFβ3	26	VCAM-1 (soluble)	18,19,21
Siglec-7	20	TGFβRII (total)	29	VEGF	24,25
Siglec-9	20	Thrombomodulin	20,23	VEGF-A	16,17,20,22,24,25,26
Sm (autoantibody)	18	Thrombospondin-1 (TSP-1)	18	VEGF-C	16,20,24
SMAD2 (Ser465/467)	29	Thrombospondin-2 (TSP-2)	20	VEGF-D	16,20,24
SMAD3 (Ser423/425)	29	TIE1 (panTyr)	28	VEGFR1/Flt-1 (panTyr)	28
SMAD4 (total)	29	TIE2 (panTyr)	28	VEGFR1/Flt-1 (soluble)	18,20,22
SOX2 (autoantibody)	20	Tie-2 (soluble)	20	VEGFR2/KDR/Flk-1 (panTyr)	28
Src (Tyr419)	29	TIM-3	20,24	VEGFR2/KDR/Flk-1 (soluble)	18,20,22
SSA/Ro52 (autoantibody)	18	TIMP-1	18,21,24,25	VEGFR3/Flt-4 (panTyr)	28
SSA/Ro60 (autoantibody)	18	TIMP-2	18	VEGFR3/Flt-4 (soluble)	18,20,22
SSB/La (autoantibody)	18	TIMP-3	18	Y	
STAT1 (Tyr701)	28,29	TIMP-4	18	Yes (Tyr421)	29
STAT2 (Tyr690)	29	Tissue Factor (TF)	20	YKL40/CHI3L1	18,20,22
STAT3 (total)	28,30	TLR-2	20,24	Z	
STAT3 (Ser727)	28	TNFR1 (total)	28	ZAP-70 (panTyr)	29
STAT3 (Tyr705)	29,30	TNFα	16,17,19,20,22,23,24,25,26		
STAT5A/B (total)	28	TNFα (autoantibody)	18		
STAT5A/B (Tyr694/699)	28,29	TNFβ/Lymphotoxin-α (LTA)	16,17,22		
STAT6 (Tyr641)	29	TNF RI (soluble) (sTNFR1)	18,22		

Analytes in blue font: available in Screening and Qualified assays. **Analytes in black font:** available in Qualified assays only. Human pp. 16-21; Non-Human Primate p. 22; Mouse pp. 22-24; Rat pp. 24-25; Other/Multi-Species pp. 25-26; Cell Signaling kits pp. 27-30

Multiplex Your Research

Explore all the ways researchers are using MILLIPLEX® multiplex assays at SigmaAldrich.com/milliplex-learn



What's In A Typical Qualified MILLIPLEX® Kit?



What's In A Typical Qualified Cell Signaling MILLIPLEX® Kit?



What's In A Typical Qualified Autoantibody MILLIPLEX® Kit?



MILLIPLEX® PLEXpedition Screening Assays

HUMAN

Multiple Research Areas

Human Screening Assay

(Cat. No. HPLX1-115SP)

80 (Cat. No. HPLX1-115SP-PX80)◆

115 (Cat. No. HPLX1-115SP-PX)

xMAP® INTELLIFLEX® or FLEXMAP 3D® Instrument						
Luminex® 200™ Instrument						
MAGPIX® Instrument						
EGF♦	IL-2♦	MCP-1♦	ACTH♦	M-CSF♦	Amylin (Active)	MCP-2
FGF-2♦	IL-4♦	MIG♦	BDNF♦	MCP-3♦	BCA-1	MCP-4
Fractalkine♦	IL-5♦	MIP-1α♦	C-Peptide♦	MDC♦	BNP	MIP-16
G-CSF♦	IL-6♦	MIP-1β♦	Eotaxin♦	MIP-3α♦	CK-MB	MIP-3β
Ghrelin (Active)♦	IL-7♦	OPN♦	FABP4♦	MMP-1♦	GCP-2	MMP-3
GIP♦	IL-8♦	PDGF-AA♦	FLT3 Ligand♦	MMP-2♦	DKK1	MMP-10
Glucagon♦	IL-10♦	PDGF-AB/BB♦	GLP-1 Total♦	MMP-7♦	ENA-78	MMP-12
GM-CSF♦	IL-12 (p40)♦	Perforin♦	Granzyme A♦	MMP-9♦	Eotaxin-2	Myostatin
Granzyme B♦	IL-12 (p70)♦	RANTES♦	I-TAC♦	OPG♦	Eotaxin-3	NGF
GROα♦	IL-13♦	sCD40L♦	IL-3♦	PIGF♦	Erythropoietin (EPO)	NTproBNP
HGF♦	IL-15♦	SCF♦	IL-9♦	PP♦	FABP3	Osteocalcin
IFNα2♦	IL-17A♦	sFAS♦	IL-17F♦	PYY♦	FGF-21	Osteonectin
IFNγ♦	IL-18♦	sFASL♦	IL-21♦	TARC♦	FGF-23	SDF-1
IL-1α♦	IL-22♦	TGFα♦	IL-33♦	TNFβ♦	HB-EGF	SOST
IL-1β♦	IL-23♦	TNFα♦	Insulin♦	Troponin I♦	I-309	TPO
IL-1Ra♦	IP-10♦	TRAIL♦			IL-11	TSLP
	Leptin♦	VEGF-A♦			LIF	VEGF-C
						VEGF-D

Configure Your Multiplex Kits with Ease

Check out our enhanced kit configurator where you can select your analytes for MILLIPLEX® qualified assays as well as our new MILLIPLEX® PLEXpedition screening kits. Design your kit at SigmaAldrich.com/milliplex-order



MILLIPLEX® Qualified Assays

HUMAN

Immunology

Human Cytokine/Chemokine/ Growth Factor Panel A

☐ (Cat. No. HCYTA-60K)

38 (Cat. No. HCYTA-60K-PX38) ♦

38 (Cat. No. HCYTA-60K-PXBK38) ♦

48 (Cat. No. HCYTA-60K-PX48)

48 (Cat. No. HCYTA-60K-PXBK48)

sCD40L	IL-13 ♦
EGF ♦	IL-15 ♦
Eotaxin/CCL11 ♦	IL-17A/CTLA8 ♦
FGF-2/FGF-basic	IL-17E/IL-25 ♦
Flt3 Ligand	IL-17F ♦
Fractalkine/CX3CL1	IL-18 ♦
G-CSF ♦	IL-22 ♦
GM-CSF ♦	IL-27
GROα	IP-10/CXCL10 ♦
IFNα2 ♦	MCP-1/CCL2 ♦
IFNγ ♦	MCP-3/CCL7
IL-1α ♦	M-CSF ♦
IL-1β ♦	MDC/CCL22
IL-1RA ♦	MIG/CXCL9 ♦
IL-2 ♦	MIP-1α/CCL3 ♦
IL-3 ♦	MIP-1β/CCL4 ♦
IL-4 ♦	PDGF-AA ♦
IL-5 ♦	PDGF-AB/BB ♦
IL-6 ♦	RANTES/CCL5 ♦▲*
IL-7 ♦	TGFα
IL-8/CXCL8 ♦	TNFα ♦
IL-9	TNFβ/Lymphotoxin-α (LTA) ♦
IL-10 ♦	VEGF-A ♦
IL-12 (p40) ♦	
IL-12 (p70) ♦	

Get both Human Panel A and Panel B premixed kits with one catalog number!

76-Plex (Two 38-plex premixed kits)

Cat. No. HCYTPAB-76SK

96-Plex (Two 48-plex premixed kits)

Cat. No. HCYTPAB-96SK

Kits cannot be combined.

Human Cytokine/Chemokine/ Growth Factor Panel B

☐ (Cat. No. HCYTB-60K)

38 (Cat. No. HCYTB-60K-PX38) ♦

38 (Cat. No. HCYTB-60K-PXBK38) ♦

48 (Cat. No. HCYTB-60K-PX48)

48 (Cat. No. HCYTB-60K-PXBK48)

6Ckine/CCL21 ♦	IL-28A/IFNλ2 ♦
APRIL ♦	IL-29 /IFNλ1 ♦
BAFF/Blys ♦	IL-31 ♦
BCA-1/CXCL13 ♦	IL-33/NF-HEV (mature) ♦
CCL28	IL-34
sCD137/4-1BB/ TNFRSF9 ♦	IL-35
CTACK/CCL27 ♦	IFNβ ♦
CXCL6/GCP-2	IFNω ♦
CXCL16	I-TAC/CXCL11 ♦
ENA-78/CXCL5 ♦	LIF ♦
Eotaxin-2/CCL24/ MIPF-2 ♦	Lymphotoxin/XCL1
Eotaxin-3/CCL26 ♦	MCP-2/CCL8 ♦
sFAS/TNFRSF6 ♦	MCP-4/CCL13 ♦
sFASL ♦	MIP-1δ /MIP-5/ CCL15 ♦
Granzyme A ♦	MIP-3α/CCL20 ♦
Granzyme B ♦	MIP-3β/CCL19
HMGB1 ♦	MIPF-1/CCL23
I-309/CCL1 ♦	Perforin ♦
IL-11	SCF ♦
IL-16 ♦	SDF-1/CXCL12 ♦
IL-20 ♦	TARC/CCL17 ♦
IL-21 ♦	TPO ♦
IL-23 ♦	TRAIL/TNFSF10 ♦
IL-24	TSLP ♦

Human High Sensitivity T Cell

☐ (Cat. No. HSTCMAG-28SK)

15 (Cat. No. HSTCMAG28SPMX13) ♦

15 (Bulk Cat. No. HSTCMAG28SPMX13BK) ♦

21 (Cat. No. HSTCMAG28SPMX21)

21 (Bulk Cat. No. HSTCMAG28SPMX21BK)

Fractalkine/CX3CL1	IL-12 (p70) ♦
GM-CSF ♦	IL-13 ♦
IFNγ ♦	IL-17A/CTLA8
IL-1β ♦	IL-21
IL-2 ♦	IL-23
IL-4 ♦	I-TAC/CXCL11
IL-5 ♦	MIP-1α/CCL3
IL-6 ♦	MIP-1β/CCL4
IL-7 ♦	MIP-3α/CCL20
IL-8/CXCL8 ♦	TNFα ♦
IL-10 ♦	

384-Well Human High Sensitivity T Cell

(Cat. No. HSTC384-28K)

21 (Cat. No. HSTCMAG384-PX21)

21 (Bulk Cat. No. HSTCMAG384PX21BK)

Fractalkine/CX3CL1	IL-12 (p70)
GM-CSF	IL-13
IFNγ	IL-17A/CTLA8
IL-1β	IL-21
IL-2	IL-23
IL-4	I-TAC/CXCL11
IL-5	MIP-1α/CCL3
IL-6	MIP-1β/CCL4
IL-7	MIP-3α/CCL20
IL-8/CXCL8	TNFα
IL-10	

Human Th17

(Cat. No. HTH17MAG-14K)

25 (Cat. No. HT17MG-14K-PX25)

25 (Bulk Cat. No. HT17MAG14PMX25BK)

GM-CSF	IL-17E/IL-25
IFNγ	IL-17F
IL-1β	IL-21
IL-2	IL-22
IL-4	IL-23
IL-5	IL-27
IL-6	IL-28A/IFNλ2
IL-9	IL-31
IL-10	IL-33/NF-HEV (mature)
IL-12 (p70)	MIP-3α/CCL20
IL-13	TNFα
IL-15	TNFβ/Lymphotoxin-α (LTA)
IL-17A/CTLA8	

Human CD8+ T Cell

☐ (Cat. No. HCD8MAG-15K)

17 (Cat. No. HCD8MAG15K17PMX)

17 (Bulk Cat. No. HCD8MAG15K17BK)

sCD137/4-1BB/ TNFRSF9	IL-4
sFAS/TNFRSF6	IL-5
sFasL	IL-6
GM-CSF	IL-10
Granzyme A	IL-13
Granzyme B	MIP-1α/CCL3
IFNγ	MIP-1β/CCL4
IL-2	Perforin
	TNFα

MILLIPLEX® Immunology Kits

Profile more immune biomarkers faster with MILLIPLEX® multiplex immunoassays. Learn more at SigmaAldrich.com/milliplex-immunology



Legend key for MILLIPLEX® kits

† Analytes which cannot be plexed together:

- Active and total
- Free and total

♦ Available in Cat. No. listed

▼ Premix panel only

Bulk indicates Space Saver Packaging

▲ These analytes cannot be plexed with other analytes in this panel in serum/plasma

► Requires a protease inhibitor during sample collection

■ Requires sample extraction

** No standard/QC; antibody levels are reported as MFIs (Median Fluorescence Intensities)

● Serum/Plasma only

★ Tissue Culture samples only

^ Competitive assay format

☐ Available for custom premix

° Analyte requires a different sample dilution from others in panel

○ Analyte cannot be measured in serum

Requires sample acidification

§ Analyte cannot be measured in plasma

u Urine only

Human Interferon

(Cat. No. HIFN-130K)

9 (Cat. No. HIFN-130K-PMX9)

IFNα2	IFNε
IFNβ	IFNω
IFNγ	IL-28A/IFNλ2
IFNγ Receptor 1 (IFNGR1)	IL-28B/IFNλ3
	IL-29/IFNλ1

Human Soluble Cytokine Receptor

(Cat. No. HSCRMAG-32K)

14 (Cat. No. HSCRMAG32KPX14)

14 (Bulk Cat. No. HSCRMAG32PMX14BK)

sCD30	sIL-6R
sEGFR/sHER1/ErbB1	sRAGE
sGP130	sTNF RI
sIL-1RI	sTNF RII
sIL-1RII	sVEGFR1/sFlt-1
sIL-2Rα	sVEGFR2/sKDR/sFlk-1
sIL-4R	sVEGFR3/sFlt-4

Human Cytokine/Chemokine Panel III

(Cat. No. HCPY3MAG-63K)

HCC-1/CCL14▲	M-CSF
IL-11	MIG/CXCL9
IL-29/IFNλ1	MIP-3α/CCL20
I-TAC/CXCL11	MIP-3β/CCL19
CXCL6/GCP-2	NAP-2/CXCL7▲
Lymphotactin/XCL1	

Human Cytokine/Chemokine Panel IV

20 (Cat. No. HCPY4MAG-64K)

20 (Cat. No. HCY4MG-64K-PX20)

20 (Bulk Cat. No. HCP4MG64KPX20BK)

BAFF/Blys	IL-28B/IFNλ3
BRAK/CXCL14	IL-32α
CCL28	IL-34
CXCL16	IL-35
HCC-4/CCL16	IL-36β/IL-1F8
HMGB1●	IL-37/IL-1F7
IFNβ	IL-38/IL-1F10
IL-14/α-Taxilin	MIP-4/PARC/CCL18
IL-19	MPIF/CCL23
IL-24	YKL40/CHI3L1

Human IL-18 Singleplex

(Cat. No. HIL18MAG-66K)

IL-18

Human Complement Expanded Panel 1

20 (Cat. No. HCMPEX1-19K)

Adipsin/Factor D	C9
C2	Factor I
C4b	Mannose-Binding Lectin (MBL)
C5	Properdin
C5a	

Human Complement Panel 2

20 (Cat. No. HCMP2MAG-19K)

C1q	C4
C3	Factor B
C3b	Factor H

Human Complement C5b-9 Singleplex

(Cat. No. HC5B9-140K)

C5b-9

Human MMP Panel 1

(Cat. No. HMMP1MAG-55K)

MMP-3	MMP-13
MMP-12	

Human MMP Panel 2

(Cat. No. HMMP2MAG-55K)

MMP-1	MMP-9
MMP-2	MMP-10
MMP-7	

Human TIMP Panel 1 (Serum/Plasma samples)

(Cat. No. HTMP1MAG-54K)

TIMP-1	TIMP-2
--------	--------

Human TIMP Panel 2 (Cell culture samples)

(Cat. No. HTMP2MAG-54K)

TIMP-1	TIMP-3
TIMP-2	TIMP-4

Human Fibrosis Panel 1

(Cat. No. HFIB1-100K)

COMP	Uteroglobin
IL-18BPα	

Immune Response**Human Autoimmune Autoantibody IgG****

(Cat. No. HAIAB-10K)

QUALITATIVE KIT

β2-Glycoprotein	PM/Sci 100
C1q	Proteinase 3
CENP-A	Ribosomal P
CENP-B	RNP
Jo-1	RNP/Sm
Ku	Sci-70
Mi-2	Sm
Myeloperoxidase (MPO)	SSA/Ro52
PCNA	SSA/Ro60
PL-12 (Alanyl-tRNA Synthetase)	SSB/La

Human Cytokine Autoantibody Expanded IgG, IgA, and IgM **

IgG (Cat. No. HCYTABG-17K)

IgA (Cat. No. HCYTABA-17K)

IgM (Cat. No. HCYTABM-17K)

QUALITATIVE KIT

BAFF/Blys	IL-8/CXCL8
G-CSF	IL-10
GM-CSF	IL-12 (p40)
IFNα2	IL-15
IFNβ	IL-17A/CTLA8
IFNγ	IL-17F
IFNω	IL-18
IL-1α	IL-22
IL-2	Osteopontin
IL-3	PF4
IL-4	TNFα
IL-6	

Human Sepsis Panel 1

(Cat. No. HSP1MAG-63K)

sFAS/TNFRSF6	MIF
sFasL	PAI-1 (total)
sICAM-1	sVCAM-1

Human Sepsis Panel 2

(Cat. No. HSP2MAG-63K)

Granzyme B	MIP-1α/CCL3
HSP70	MIP-1β/CCL4
IL-1α	MMP-8
IL-8/CXCL8	

Human Sepsis Panel 3

(Cat. No. HSP3MAG-63K)

Lactotransferrin (LTF)	Resistin
Neutrophil Elastase-2 (ELA2)	Thrombospondin-1 (TSP-1)
NGAL/Lipocalin-2	

MILLIPLEX® Autoantibody Profiling

Discover the benefits of multiplexing autoantibodies at
SigmaAldrich.com/milliplex-autoab



Human Immunoglobulin Isotyping

(Cat. No. HGAMMAG-301K)

IgA	IgG3
IgG1	IgG4
IgG2	IgM

Human IgE – Singleplex

(Cat. No. HGAMMAG-303E)

IgE

Virology**AAV Serotyping Panel IgG******NEW**

(Cat. No. AAVSERG-230K)

QUALITATIVE KIT

AAV1	AAV6
AAV2	AAV8
AAV5	AAV9

SARS-CoV-2 Antigen Panel 1 IgA**

(Cat. No. HC19SERA1-85K)

QUALITATIVE KIT

SARS-CoV-2 N	SARS-CoV-2 Spike S1
SARS-CoV-2 RBD	SARS-CoV-2 Spike S2

SARS-CoV-2 Antigen Panel 1 IgG**

(Cat. No. HC19SERG1-85K)

QUALITATIVE KIT

SARS-CoV-2 N	SARS-CoV-2 Spike S1
SARS-CoV-2 RBD	SARS-CoV-2 Spike S2

SARS-CoV-2 Antigen Panel 1 IgM**

(Cat. No. HC19SERM1-85K)

QUALITATIVE KIT

SARS-CoV-2 N	SARS-CoV-2 Spike S1
SARS-CoV-2 RBD	SARS-CoV-2 Spike S2

For Research Use Only. Not For Use In Diagnostic Procedures.**Metabolism/Endocrinology****Human Adipokine Panel 1 (Serum/Plasma samples)**

(Cat. No. HADK1MAG-61K)

Adiponectin	PAI-1 (total)
Adipsin/Factor D	Resistin
NGAL/Lipocalin-2	

Human Adipokine Panel 2 (Serum/Plasma samples)

(Cat. No. HADK2MAG-61K)

IL-1β	Leptin
IL-6	MCP-1/CCL2
IL-8/CXCL8	NGF
Insulin	TNFα

Human Adipocyte (Cell culture samples)

(Cat. No. HADCYMAG-61K)

Adiponectin	MCP-1/CCL2
HGF	NGF
IL-1β	PAI-1 (total)
IL-6	Resistin
IL-8/CXCL8	TNFα
Leptin	

Human Metabolic Hormone V3

(Cat. No. HMH3-34K)

Amylin (active) †	Insulin
Amylin (total) †	Leptin
C-Peptide	MCP-1/CCL2
Ghrelin (active) †	Pancreatic Polypeptide (PP)
GIP (total)	PYY (total)
GLP-1 (active) †	Secretin
GLP-1 (total) †	TNFα
Glucagon †	
IL-6	

Human Myokine

(Cat. No. HMYOMAG-56K)

Apelin	IL-15
BDNF	Irisin
Erythropoietin (EPO)	LIF
FABP3	Myostatin/GDF8
FGF-21	Oncostatin-M (OSM)
Fractalkine/CX3CL1	Osteonectin (OSTN)/Musclin
FSTL1	Osteonectin/SPARC
IL-6	

Human Aging Panel 1

(Cat. No. HAGE1MAG-20K)

CTACK/CCL27	IL-6
FGF-21	IL-10*
GDF-11	IL-18
GDF15	Jag1
GnRH	Leptin

Human Liver Protein

(Cat. No. HLPPMAG-57K)

α-Fetoprotein (AFP)	FGF-19
ANGPTL3	FGF-21
ANGPTL4	FGF-23
ANGPTL6	HGF
FABP1	

Human IGF Binding Protein

(Cat. No. HIGFBMAG-53K)

IGFBP1	IGFBP5
IGFBP2	IGFBP6
IGFBP3*	IGFBP7
IGFBP4	

Human IGF

(Cat. No. HIGFMAG-52K)

IGF-1	IGF-2
-------	-------

Human Pituitary Panel 1

(Cat. No. HPTP1MAG-66K)

ACTH	FSH
Agouti-Related Protein (AgRP)	GH
CNTF	LH
	TSH

Cardiovascular**Human CVD Panel 1**

(Cat. No. HCVD1MAG-67K)

BNP	LIGHT
CK-MB	NT proBNP
CXCL6/GCP-2	Oncostatin-M (OSM)
CXCL16	Placental Growth Factor (PIGF)
Endocan-1 (ESM-1)	Troponin I (TnI)
FABP3	
FABP4	

Human CVD Panel 2

(Cat. No. HCVD2MAG-67K)

ADAMTS13	Myoglobin
D-dimer ^s	NGAL/Lipocalin-2
GDF15	sP-Selectin
sICAM-1	Serum Amyloid A
Myeloperoxidase (MPO)	sVCAM-1

Human CVD Panel 3 (Acute Phase)

(Cat. No. HCVD3MAG-67K)

α-1-Acid Glycoprotein (AGP)	Haptoglobin
α-2-Macroglobulin	sL-Selectin
Adipsin/Factor D	Platelet Factor 4 (PF4)/CXCL4
CRP	Serum Amyloid P (SAP)
Fetuin A	
Fibrinogen ^u	

Legend key for MILLIPLEX® kits

† Analytes which cannot be plexed together:
– Active and total
– Free and total

♦ Available in Cat. No. listed

▼ Premix panel only

Bulk indicates Space Saver Packaging

▲ These analytes cannot be plexed with other analytes in this panel in serum/plasma

‡ Requires a protease inhibitor during sample collection

■ Requires sample extraction

** No standard/QC; antibody levels are reported as MFIs (Median Fluorescence Intensities)

● Serum/Plasma only

★ Tissue Culture samples only

^ Competitive assay format

■ Available for custom premix

° Analyte requires a different sample dilution from others in panel

○ Analyte cannot be measured in serum

Requires sample acidification

^s Analyte cannot be measured in plasma

^u Urine only

Human CVD Panel 4

(Cat. No. HCV4MAG-67K)

sCD31/sPECAM-1	Thrombomodulin
sE-Selectin	Tissue Factor (TF)
Follistatin (FST)	Troponin T (TnT)
Pentraxin-3 (PTX3)	

Human CVD Panel 6

(Cat. No. HCV6MAG-67K)

sCD14	MCAM/MUC18
DPP4	Progranulin (pGRN)
Endostatin	ucMGP
LRG1	

Human Apolipoprotein

(Cat. No. APOMAG-62K)

Apo AI	Apo CII
Apo AII	Apo CIII
Apo B	Apo E

Bone**Human Bone**

(Cat. No. HBNMAG-51K)

ACTH	Osteocalcin (OC)
DDK1	Osteopontin (OPN)
FGF-23	Osteoprotegerin (OPG)
IL-1 β	PTH
IL-6	Sclerostin (SOST)
Insulin	TNF α
Leptin	

Human RANKL – Singleplex

(Cat. No. HRNKMAG-51K-01)

RANKL

Cancer**Human Immuno-Oncology Checkpoint Protein Panel 1**

(Cat. No. HCKP1-11K)

① (Cat. No. HCKP1-11K-PX17)

② (Bulk Cat. No. HCKP1-11K-PXBK17)

BTLA	HVEM
CD27	ICOS
CD28	LAG-3
CD40	PD-1
CD80/B7-1	PD-L1
CD86/B7-2	PD-L2
CTLA-4/CD152	TIM-3
GITR	TLR-2
GITRL	

Human Immuno-Oncology Checkpoint Protein Panel 2

(Cat. No. HCKP2-11K)

4-1BBL/TNFSF9	FGL1/Hepassocin
5'-NT/CD73	Galectin-1
APRIL	Galectin-3
Arginase-1	Granulysin
B7-H2/ICOSL	Granzyme B
B7-H3/CD276	IDO1
B7-H4/VTCN1	MICA
B7-H5/VISTA	MICB
B7-H6	Nectin-2
BAFF/BLyS	Nectin-4
CD25/IL-2R α	OX40/CD134
CD30/TNFRSF8	Perforin
CD40L	PVR/CD155
CD137/4-1BB	Siglec-7
CD226/DNAM-1	Siglec-9
E-Cadherin	

Human Cancer Autoantibody IgG**

(Cat. No. HCABMAG-13K)

QUALITATIVE KIT

CCNB1/Cyclin B1	IGF2BP2/IMP2
CTAG1B/NY-ESO-1	IGF2BP3/IMP3
ENO1	Mucin-1 (MUC1)
Galectin-1 (GAL1)	P16-INK4a
Galectin-3 (GAL3)	p53
HER2/ErbB2	SOX2
HIF-1 α	Survivin/BIRC5
HSP60	

Human Exosome Characterization

(Cat. No. HEXSM-170K)

① (Cat. No. HEXSM-170K-PMX)

② (Bulk Cat. No. HEXSM-170K-BKPMX)

Argonaute-2 (Ago2)*	Flotillin-1 (FLOT-1)
Calreticulin (CALR)	GAPDH
CD9	Syntenin-1 (Syn-1)
CD63	TSG101
CD81	

*The Ago2 bead is static and will always be included in the kit format.

Human Circulating Cancer Biomarker Panel 1

(Cat. No. HCCBP1MAG-58K)

α -Fetoprotein (AFP)	IL-8/CXCL8
CA125	Leptin
CA15-3	MIF
CA19-9	Osteopontin (OPN)
CEA	Prolactin
CYFRA21-1	PSA (free) [†]
sFAS/TNFRSF6	PSA (total) [†]
sFasL	SCF
FGF-2/FGF-basic	TGF α
HCG β	TNF α
HE4	TRAIL/TNFSF10
HGF	VEGF-A
IL-6	

Human Circulating Cancer Biomarker Panel 3

(Cat. No. HCCBP3MAG-58K)

Cathepsin D	Melanoma Inhibitory Activity (MIA)
Ferritin	Myeloperoxidase (MPO)
Fibroblast Activation Protein (FAP)	Sex Hormone Binding Globulin (SHBG)
Galectin-3	
IGFBP3	

Human Circulating Cancer Biomarker Panel 4

(Cat. No. HCCB4MAG-58K)

ALDH1A1	Kallikrein-6
Carbonic Anhydrase 9 (CA9)	Mesothelin
CD44	Midkine
EpCAM	NCAM1/L1CAM/CD171
Hepsin	Transglutaminase 2 (TGM2)

Human Cancer/Metastasis Biomarker Panel 1

(Cat. No. HCMBMAG-22K)

DDK1	Osteoprotegerin (OPG)
GDF15	Periostin
Neuron-specific Enolase (NSE)	TRAP5
Osteonectin/SPARC	TWEAK
	YKL40/CHI3L1

Human Angiogenesis/Growth Factor Panel 1

(Cat. No. HAGP1MAG-12K)

Angiopoietin-2	HB-EGF
BMP-9	HGF
EGF	IL-8/CXCL8
Endoglin	Leptin
Endothelin-1	Placental Growth Factor (PlGF)
FGF-1/FGF-acidic	VEGF-A
FGF-2/FGF-basic	VEGF-C
Follistatin (FST)	VEGF-D
G-CSF	

Human Angiogenesis Panel 2

(Cat. No. HANG2MAG-12K)

Angiostatin/Kringle	sIL-6R α
sAXL	sNeuropilin-1 (sNRP-1)
sCD31/sPECAM-1	Osteopontin (OPN)
sc-Kit/sStem Cell Factor Receptor (SCFR)	PDGF-AB/BB
sE-Selectin	Thrombospondin-2 (TSP-2)
sEGFR/sHER1/sErbB1	sTIE-2
sHER2/sEGFR2/sErbB2	suPAR
sHER3/sEGFR3/sErbB3	sVEGFR1/sFlt-1
SHGFR/sc-Met	sVEGFR2/sKDR/sFlk-1
	sVEGFR3/sFlt-4

MILLIPLEX® Cancer Kits

See how our kits are advancing cancer and immuno-oncology research at
SigmaAldrich.com/milliplex-cancer



Neuroscience

Human Amyloid Beta and Tau (CSF samples)

(Cat. No. HNA8TMAG-68K)

Amyloid beta 1-40	pTau (Thr181)
Amyloid beta 1-42	Tau (total)

Human Neuroscience Panel 1 (CSF samples)

(Cat. No. HNS1MAG-95K)

α-Synuclein	PARK5/UCHL1
Glial Fibrillary Acidic Protein (GFAP)	PARK7/DJ1
Neuron-specific Enolase (NSE)	Transglutaminase 2 (TGM2)

Human Neuroscience Panel 2

(Cat. No. HNS2MAG-95K)

Angiogenin (ANG) ⁺	Ferritin
ApoE4 ⁺	Neurogranin (NRGN)
FABP3	TREM2

Human Neurodegenerative Autoantibody IgG** **NEW**

(Cat. No. HNDGAB-220K)

QUALITATIVE KIT

α-synuclein	DRD2
Aβ42	ELAVL4 (HuD)
AChR	GFAP
AGNA (SOX1)	MBP
Ago2 (Su)	mGluR1
AMPA-R	MOG
Amphiphysin	NF-L
ANNA2 (Ri)/NOVA1	NMDAR1
AQP4	NRXN3
C1q	PCA1 (Yo)/CDR2
CRMP5	PNMA1 (Ma1)
CRYAB	tTau
DPPX	

Human Neurodegenerative Disease Panel 1

(Cat. No. HNDG1MAG-36K)

α-2-Macroglobulin	Complement Factor C3
Apo AI	Complement Factor H (CFH)
Apo CIII	
Apo E	

Human Neurodegenerative Disease Panel 2

(Cat. No. HNDG2MAG-36K)

α-1-Antitrypsin (A1AT)	MIP-4/PARC/CCL18
C4	PEDF
CRP	Serum Amyloid P (SAP)

Human Neurodegenerative Disease Panel 3

(Cat. No. HNDG3MAG-36K)

BDNF	PAI-1 (total)
Cathepsin D	PDGF-AA
sICAM-1	PDGF-AB/BB
Myeloperoxidase (MPO)	RANTES/CCL5
sNCAM	sVCAM-1

Human Neurodegenerative Disease Panel 4 (CSF samples)

(Cat. No. HNDG4MAG-36K)

Amyloid beta 1-40	sRAGE
Amyloid beta 1-42	S100B
GDNF	

Human Neurological Disorders Panel 3

(Cat. No. HND3MAG-39K)

Angiotensinogen (AGT)	Osteopontin (OPN)
Contactin-1	Soluble Superoxide Dismutase 1 (sSOD1)
Fetuin A ⁺	Soluble Superoxide Dismutase 2 (sSOD2)
Kallikrein-6	

Human Neuropeptide [■] [^]

(Cat. No. HNP8MAG-35K)

α-MSH	Oxytocin
β-Endorphin	Substance P
Neurotensin	

Human Circadian Stress [■] [^]

(Cat. No. HNC8MAG-35K)

Cortisol	Melatonin
----------	-----------

Toxicity

Human Kidney Injury Panel 1 (Urine samples)

(Cat. No. HKI1MAG-99K)

Calbindin	KIM-1
Collagen IV	Renin
GSTα	TFF-3
IP-10/CXCL10	TIMP-1

Human Kidney Injury Panel 2 (Urine samples)

(Cat. No. HKI2MAG-99K)

α-1-Microglobulin	EGF
Albumin	NGAL/Lipocalin-2
Clusterin	Osteopontin (OPN)
Cystatin C	

Human Kidney Injury Panel 4 (Serum/Plasma samples)

(Cat. No. HKI4MAG-99K)

EGF	Osteopontin (OPN)
FABP1	PTH
IP-10/CXCL10	Renin
KIM-1	

Human Kidney Injury Panel 5 (Serum/Plasma samples)

(Cat. No. HKI5MAG-99K)

α-1-Microglobulin	Osteoactivin
Collagen IV	TIMP-1
NGAL/Lipocalin-2	Uromodulin

Human Kidney Injury Panel 6 (Serum/Plasma samples)

(Cat. No. HKI6MAG-99K)

β-2-Microglobulin	Cystatin C
Clusterin	RBP4

Human Liver Injury

(Cat. No. HLINJMAG-75K)

5'NT/CD73	MDH1
ARG1	SDH
GSTα	

HUMAN

Explore Biomarkers for Alzheimer's Disease Research

Learn how to combine multiplex and high sensitivity assay analysis for AD biomarker studies at SigmaAldrich.com/immunoassays-AD



Legend key for MILLIPLEX® kits

† Analytes which cannot be plexed together:
– Active and total
– Free and total

◆ Available in Cat. No. listed

▼ Premix panel only

Bulk indicates Space Saver Packaging

▲ These analytes cannot be plexed with other analytes in this panel in serum/plasma

■ Requires a protease inhibitor during sample collection

■ Requires sample extraction

** No standard/QC; antibody levels are reported as MFIs (Median Fluorescence Intensities)

● Serum/Plasma only

★ Tissue Culture samples only

^ Competitive assay format

■ Available for custom premix

° Analyte requires a different sample dilution from others in panel

○ Analyte cannot be measured in serum

Requires sample acidification

° Analyte cannot be measured in plasma

u Urine only

PRIMATE

Immunology

Non-Human Primate Cytokine/
Chemokine /Growth Factor
Panel A

- (Cat. No. PRCYTA-40K)
 38 (Cat. No. PRCYTA-40K-PX38)♦
 38 (Cat. No. PRCYTA-40K-BK38)♦
 48 (Cat. No. PRCYTA-40K-PX48)
 48 (Cat. No. PRCYTA-40K-BK48)

BCA-1/CXCL13	IL-15♦
sCD137/4-1BB/ TNFRSF9♦	IL-16
sCD40L♦	IL-17A/CTLA8♦
Eotaxin/CCL11	IL-17E/IL-25
sFASL♦	IL-18♦
FGF-2/FGF-basic	IL-21♦
Fractalkine/CX3CL1	IL-22♦
G-CSF♦	IL-23♦
GM-CSF♦	IL-28A/IFNA2
Granzyme A♦	IL-31
Granzyme B♦	IL-33/NF-HEV (mature)♦
IFNa2♦	IP-10/CXCL10♦
IFNy♦	I-TAC/CXCL11♦
IL-1a	MCP-1/CCL2♦
IL-1β♦	MIG/CXCL9♦
IL-1RA♦	MIP-1a/CCL3♦
IL-2♦	MIP-1β/CCL4♦
IL-4♦	MIP-3a/CCL20♦
IL-5♦	Perforin♦
IL-6♦	RANTES/CCL5♦▲°
IL-7♦	TGFa♦
IL-8/CXCL8♦	TNFa♦
IL-10♦	TNFβ/LTA
IL-12 (p70)♦	VEGF-A♦

Metabolism/
EndocrinologyNon-Human Primate
Metabolic Hormone

(Cat. No. NHPMHMAG-45K)

Amylin (active)♦	Insulin
C-Peptide	Leptin
Ghrelin (active)♦	MCP-1/CCL2
GIP (total)	Pancreatic Polypeptide (PP)
GLP-1 (active)♦	PYY (total)
Glucagon♦	
IL-6	

Non-Human Primate Pituitary
Panel 1

(Cat. No. NHPPT1MG-46K)

ACTH	FSH
Agouti-Related Protein (AgRP)	GH
CNTF	LH
	TSH

MOUSE

Immunology

Mouse Cytokine/Chemokine/
Growth Factor Expanded
Panel 1 **NEW**

- (Cat. No. MCYT1-190K)
 41 (Cat. No. MCYT1-190K-SPX)♦
 41 (Cat. No. MCYT1-190K-SPXBK)♦
 68 (Cat. No. MCYT1-190K-LPX)
 68 (Cat. No. MCYT1-190K-LPXBK)

BAFF	IL-12p40♦
Betacellulin	IL-12p70♦
CCL25/TECK	IL-13♦
sCD137/4-1BB/ TNFRSF9	IL-15♦
CHI3L1	IL-16
CXCL16	IL-17A/CTLA8♦
EGF♦	IL-17F♦
Eotaxin/CCL11♦	IL-18♦
Erythropoietin (EPO)	IL-20
Exodus-2/ CCL21/6CKine	IL-22♦
sFas/TNFRSF6	IL-28B/IFNA3♦
sFasL	IL-31
FGF-2♦	IL-33♦
FLT3L	IP-10/CXCL10♦
Fractalkine/CX3CL1	KC/GRO/CINC-1/ CXCL1♦
G-CSF♦	LIF♦
GDF-15	LIX♦
GM-CSF♦	MDC/CCL22
Granzyme B	MCP-1/CCL2♦
sICAM-1	MCP-2
IFNa♦	MCP-3
IFNβ♦	MCP-5/CCL12
IFNy♦	M-CSF♦
IL-1a♦	MIG/CXCL9♦
IL-1β♦	MIP-1a/CCL3♦
IL-2♦	MIP-1β/CCL4♦
IL-3♦	MIP-2/CXCL2♦
IL-4♦	MIP-3a/CCL20
IL-5♦	MIP-3β/CCL19
IL-6♦	sRAGE
IL-7♦	RANTES/CCL5♦
IL-9♦	TARC/CCL17
IL-10♦	TNFa♦
IL-11	VEGF-A♦

Mouse High Sensitivity T Cell

- (Cat. No. MHSTCMAG-70K)
 18 (Cat. No. MHSTCMAG-70KPMX)
 18 (Bulk Cat. No. MHSTCMAG-70KPBK)

GM-CSF	IL-10
IFNy	IL-12 (p70)
IL-1a	IL-13
IL-1β	IL-17A/CTLA8
IL-2	KC/GRO/CINC-1/ CXCL1
IL-4	LIX
IL-5	MCP-1/CCL2
IL-6	MIP-2/CXCL2
IL-7	TNFa

Mouse Th17

- (Cat. No. MTH17MAG-47K)
 25 (Cat. No. MT17MAG47K-PX25)
 25 (Bulk Cat. No. MT17MAG47PMX25BK)

sCD40L	IL-17E/IL-25
GM-CSF	IL-17F
IFNy	IL-21
IL-1β	IL-22
IL-2	IL-23
IL-4	IL-27
IL-5	IL-28B/IFNA3
IL-6	IL-31
IL-10	IL-33/NF-HEV (mature)
IL-12 (p70)	MIP-3a/CCL20
IL-13	TNFa
IL-15	TNFβ/Lymphotoxin-α (LTA)
IL-17A/CTLA8	

Mouse CD8+ T Cell

- (Cat. No. MCD8MAG-48K)
 15 (Cat. No. MCD8MAG48K-PX15)
 15 (Bulk Cat. No. MCD8MAG48KPX15BK)

sCD137/4-1BB/ TNFRSF9	IL-4
sFas/TNFRSF6	IL-5
sFasL	IL-6
GM-CSF	IL-10
Granzyme B	IL-13
IFNy	MIP-1β/CCL4
IL-2	RANTES/CCL5
	TNFa

Mouse Soluble Cytokine
Receptor

- (Cat. No. MSCRMAG-42K)

sCD30	sRAGE
sGP130	sTNF RI
sIL-1RI	sTNF RII
sIL-1RII	sVEGFR1/sFlt-1
sIL-2Ra	sVEGFR2/sKDR/sFlk-1
sIL-4R	sVEGFR3/sFlt-4
sIL-6R	

Mouse MMP Panel 1
(Serum/Plasma samples)

(Cat. No. MMMP1MAG-79K)

MMP-2	MMP-8
MMP-3	

Mouse MMP Panel 2
(Serum/Plasma samples)

(Cat. No. MMMP2MAG-79K)

proMMP-9	MMP-12
----------	--------

Squeak Out The Best Results

Measure up to 68 mouse targets in one assay. Discover more details about the largest mouse cytokine multiplex assay at [SigmaAldrich.com/milliplex-mouse](https://www.sigmaaldrich.com/milliplex-mouse).



Mouse MMP Panel 3 (Cell culture samples)

(Cat. No. MMMP3MAG-79K)

MMP-2	proMMP-9
MMP-3	MMP-12
MMP-8	

Immune Response

Mouse Immunoglobulin Isotyping

☐ (Cat. No. MGAMMAG-300K)

IgA	IgG2b
IgG1	IgG3
IgG2a	IgM

Mouse IgE – Singleplex

(Cat. No. MGAMMAG-300E)

IgE	
-----	--

Metabolism/ Endocrinology

Mouse Adipokine (Serum/Plasma samples)

(Cat. No. MADKMAG-71K)

IL-6	PAI-1 (total)
Insulin	Resistin
Leptin	TNFA
MCP-1/CCL2	

Mouse Adipocyte (Cell culture samples)

(Cat. No. MADCYMAG-72K)

Adiponectin	PAI-1 (total)
IL-6	Resistin
Leptin	TNFA
MCP-1/CCL2	

Mouse Adiponectin – Singleplex (Serum/Plasma samples)

(Cat. No. MADPNMAG-70K-01)

Adiponectin	
-------------	--

Mouse Metabolic Hormone Expanded

(Cat. No. MMHE-44K)

Amylin (active) ▴	Leptin
C-Peptide 2	MCP-1/CCL2
Ghrelin (active) ▴	Pancreatic Polypeptide (PP)
GIP (total)	PYY (total)
GLP-1 (active) ▴	Resistin
GLP-1 (total) ▴	Secretin
Glucagon ▴	TNFA
IL-6	
Insulin	

Mouse Myokine

(Cat. No. MMYOMAG-74K)

BDNF	Irisin
Erythropoietin (EPO) ★	LIF
FGF-21	Myostatin/GDF8
Follistatin-like Protein 1 (FSTL1)	Oncostatin-M (OSM)
IL-6	Osteocrin (OSTN)/Musclin
IL-15	Osteonectin/SPARC

Mouse Aging Panel 1

(Cat. No. MAGE1MAG-25K)

CTACK/CCL27	Jag1
FGF-21	Leptin
GnRH	Notch1
IL-6	TNFA

Mouse Pituitary

(Cat. No. MPTMAG-49K)

ACTH	LH
BDNF	Prolactin
FSH	TSH
GH	

Mouse TSH – Singleplex **NEW**

(Cat. No: RMTSH-200K)

(Bulk Cat. No. RMTSH-200K-10PK)

TSH	
-----	--

Cardiovascular

Mouse CVD Panel 1

(Cat. No. MCVD1MAG-77K)

sCD31/sPECAM-1	ProMMP-9
sE-Selectin	sP-Selectin
sICAM-1	Thrombomodulin
PAI-1 (total)	

Mouse CVD Panel 2

(Cat. No. MCVD2MAG-77K)

sCD40L	Oncostatin M (OSM)
CXCL16	Placental Growth Factor 2
Endocan-1 (ESM-1)	Troponin I (TnI)
Follistatin (FST)	Troponin T (TnT)
LIGHT	

Mouse Acute Phase Panel 2

(Cat. No. MAP2MAG-76K)

α-1-Acid Glycoprotein (AGP)	CRP
α-2-Macroglobulin	Haptoglobin
Adipsin/Factor D	Serum Amyloid P (SAP)

Cancer

Humanized Mouse **NEW**

☐ (Cat. No. HUMU-210K)

41 (Cat. No. HUMU-210K-PMX)

41 (Cat. No. HUMU-210K-PMXBK)

G-CSF (Human)	IL-12p40 (Human)
G-CSF (Mouse)	IL-12p40 (Mouse)
GM-CSF (Human)	IL-12p70 (Human)
GM-CSF (Mouse)	IL-12p70 (Mouse)
IFNγ (Human)	IL-15 (Human)
IFNγ (Mouse)	IL-17A/CTLA8 (Human)
IL-1α (Human)	IL-17A/CTLA8 (Mouse)
IL-1β (Human)	IL-18 (Human)
IL-1β (Mouse)	IL-18 (Mouse)
IL-2 (Human)	IP-10/CXCL10 (Human)
IL-2 (Mouse)	IP-10/CXCL10 (Mouse)
IL-3 (Human)	MCP-1/CCL2 (Human)
IL-3 (Mouse)	MCP-1/CCL2 (Mouse)
IL-4 (Human)	M-CSF (Human)
IL-5 (Human)	M-CSF (Mouse)
IL-5 (Mouse)	MIG/CXCL9 (Human)
IL-6 (Human)	MIG/CXCL9 (Mouse)
IL-6 (Mouse)	TNFA (Human)
IL-7 (Human)	TNFA (Mouse)
IL-8 (Human)	
KC/GRO/CINC-1/CXCL1 (Mouse)	
IL-10 (Human)	

Legend key for MILLIPLEX® kits

† Analytes which cannot be plexed together:
– Active and total
– Free and total

♦ Available in Cat. No. listed

▼ Premix panel only

Bulk indicates Space Saver Packaging

▲ These analytes cannot be plexed with other analytes in this panel in serum/plasma

▴ Requires a protease inhibitor during sample collection

■ Requires sample extraction

** No standard/QC; antibody levels are reported as MFIs (Median Fluorescence Intensities)

● Serum/Plasma only

★ Tissue Culture samples only

^ Competitive assay format

☐ Available for custom premix

° Analyte requires a different sample dilution from others in panel

○ Analyte cannot be measured in serum

Requires sample acidification

ˢ Analyte cannot be measured in plasma

˘ Urine only

Mouse Angiogenesis / Growth Factor Panel 1

(Cat. No. MAGPMAG-24K)

sALK-1	IL-6
Amphiregulin	IL-17A/CTLA8
Angiopoietin-2 ▲	KC/GRO/CINC-1/ CXCL1
Betacellulin ▲	Leptin
sCD31/sPECAM-1 ▲	MCP-1/CCL2
EGF	MIP-1α/CCL3
Endoglin	Placental Growth Factor 2
sFasL	Prolactin
FGF-2/FGF-basic	SDF-1/CXCL12
Follistatin (FST)	TNFα
G-CSF	VEGF-A
HGF	VEGF-C
IL-1β	VEGF-D

Mouse Immuno-Oncology Checkpoint Protein Panel 1

☐ (Cat. No. MCKP1-110K)

28 (Cat. No. MCKP1-110K-PX28)

28 (Bulk Cat No. MCKP1-110K-PBK28)

4-1BBL/TNFSF9	Galectin-1
5'-NT/CD73	Galectin-3
B7-H2/ICOSL	GITR
B7-H3/CD276	Granzyme B
BCA-1/CXCL-13	HVEM
BTLA	IFNγ
CD137/4-1BB	IL-10
CD226/DNAM-1	LAG-3
CD25/IL-2Ra	PD-1
CD27	PD-L1
CD40	PD-L2
CD80/B7-1	TIM-3
CTLA-4/CD152	TLR-2
E-Cadherin	TNFα

Neuroscience

Mouse Amyloid Beta

(Cat. No. MABMAG-83K)

Amyloid beta 1-40	Amyloid beta 1-42
-------------------	-------------------

Mouse Neuropeptide ■ ^

(Cat. No. RMNPMAG-83K)

α-MSH	Oxytocin
β-Endorphin	Substance P
Neurotensin	

Toxicity

Mouse Kidney Injury Panel 1

(Cat. No. MKI1MAG-94K)

β-2-Microglobulin ^u	Renin
IP-10/CXCL10	TIMP-1
KIM-1	VEGF-A ^u

Mouse Kidney Injury Panel 2

(Cat. No. MKI2MAG-94K)

Clusterin	NGAL/Lipocalin-2
Cystatin C	Osteopontin (OPN)
EGF	

RAT

Immunology

Rat Cytokine/Chemokine

☐ (Cat. No. RECYTMAG-65K)

27 (Cat. No. RECYMAG65K27PMX)

27 (Bulk Cat. No. RECYMAG65PMX27BK)

EGF	IL-10
Eotaxin/CCL11	IL-12 (p70)
Fractalkine/CX3CL1	IL-13
G-CSF	IL-17A/CTLA8
GM-CSF	IL-18
KC/GRO/CINC-1/ CXCL1	IP-10/CXCL10
IFNγ	Leptin
IL-1α	LIX
IL-1β	MCP-1/CCL2
IL-2	MIP-1α/CCL3
IL-4	MIP-2/CXCL2
IL-5	RANTES/CCL5
IL-6	TNFα
	VEGF

Metabolism/ Endocrinology

Rat Adipokine (Serum/Plasma samples)

(Cat. No. RADPKMAG-80K)

IL-1β	MCP-1/CCL2
IL-6	PAI-1 (total)
Insulin	TNFα
Leptin	

Rat Adipocyte (Cell culture samples)

(Cat. No. RADPCMAG-82K)

Adiponectin	MCP-1/CCL2
IL-1β	PAI-1 (total)
IL-6	TNFα
Leptin	

Rat Metabolic Hormone Expanded

(Cat. No. RMHE-120K)

Amylin (active) ^u	Insulin
C-Peptide 2	Leptin
Ghrelin (active) ^u	MCP-1/CCL2
GIP (total)	Pancreatic Polypeptide (PP)
GLP-1 (active) ^u ^u	PYY (total)
GLP-1 (total) ^u ^u	Secretin
Glucagon ^u	TNFα
IL-6	

Rat Myokine

(Cat. No. RMYOMAG-88K)

BDNF	IL-15
Erythropoietin (EPO)	Irisin
FGF-21	LIF
Follistatin-like Protein 1 (FSTL1)	Myostatin/GDF8
Fractalkine/CX3CL1	Osteocrin (OSTN)/ Musclin
IL-6	Osteonectin/SPARC

Rat Pituitary

(Cat. No. RPTMAG-86K)

ACTH	LH
BDNF	Prolactin
FSH	TSH
GH	

Rat Stress Hormone ■

(Cat. No. RSHMAG-69K)

ACTH	Melatonin ^
Corticosterone ^	

Rat Thyroid

(Cat. No. RTHYMAG-30K)

T3 ^	TSH
T4 ^	

Rat TSH – Singleplex **NEW**

(Cat. No: RMTSH-200K)

(Bulk Cat. No. RMTSH-200K-10PK)

TSH

Quality in Every MILLIPLEX® Kit

We pride ourselves on our quality R&D, support, manufacturing, and QC.

Read more at: SigmaAldrich.com/milliplex-quality



Cardiovascular

Rat Cardiac Injury Panel 1

(Cat. No. RCI1MAG-87K)

Cardiac Troponin I (cTnI)	FABP3
Cardiac Troponin T (cTnT)	Follistatin-like Protein 1 (FSTL1)
Creatine Kinase Muscle (CKM)	Myosin Light Chain 3 (MYL3)
	TIMP-1

Rat Vascular Injury Panel 1 (Serum/Plasma samples)

(Cat. No. RV1MAG-26K)

Caveolin-1	IL-6
Connective Tissue Growth Factor (CTGF)	MCP-1 / CCL2
KC/GRO/CINC-1/CXCL1	PAI-1 (total)
	TIMP-1
	TNFα
	VEGF

Rat Vascular Injury Panel 2 (Serum/Plasma samples)

(Cat. No. RV2MAG-26K)

Adiponectin	sICAM-1
sE-Selectin	

Rat Vascular Injury Panel 3 (Serum/Plasma samples)

(Cat. No. RV3MAG-26K)

α-1-Acid Glycoprotein (AGP)	Haptoglobin
α-2-Macroglobulin (A2M)	

Bone

Rat Bone Panel 1 (Serum/Plasma samples)

(Cat. No. RBN1MAG-31K)

ACTH	Leptin
DKK1	Osteoprotegerin (OPG)
FGF-23	PTH
Insulin	Sclerostin (SOST)

Neuroscience

Rat Neuropeptide ■ ^

(Cat. No. RMNPMAG-83K)

α-MSH	Oxytocin
β-Endorphin	Substance P
Neurotensin	

Toxicity

Rat Kidney Toxicity Panel 1 (Urine samples)

(Cat. No. RKT1MAG-37K)

Clusterin	Osteopontin (OPN)
GSTα^	TIMP-1
IP-10/CXCL10	VEGF-A
KIM-1	

Rat Kidney Toxicity Panel 2 (Urine samples)

(Cat. No. RKT2MAG-37K)

α-1-Acid Glycoprotein (AGP)	Cystatin C
Albumin^	EGF
β-2-Microglobulin	NGAL / Lipocalin-2

Rat Liver Injury

(Cat. No. RLI1MAG-92K)

5'NT/CD73	GSTα
ARG1	SDH
GOT1	

COMPANION/AGRICULTURAL

Immunology

Bovine Cytokine/Chemokine Panel 1

⊙ (Cat. No. BCYT1-33K)

15 (Cat. No. BCYT1-33K-PX15)

15 (Bulk Cat. No. BCYT1-33K-PXBK15)

IFNγ	IL-36RA/IL-1F5
IL-1α	IP-10/CXCL10
IL-1β	MCP-1/CCL2
IL-4	MIP-1α/CCL3
IL-6	MIP-1β/CCL4
IL-8/CXCL8	TNFα
IL-10	VEGF-A
IL-17A/CTLA8	

Bovine Acute Phase Protein

(Cat. No. BAPP1-150K)

Haptoglobin	Fibrinogen ⊙
-------------	--------------

Canine Cytokine/Chemokine

⊙ (Cat. No. CCYTOMAG-90K)

13 (Cat. No. CCYTMG-90K-PX13)

15 (Bulk Cat. No. CCYTOMAG90KPX13BK)

GM-CSF	IL-15
IFNγ	IL-18
IL-2	IP-10/CXCL10
IL-6	KC-like
IL-7	MCP-1/CCL2
IL-8/CXCL8	TNFα
IL-10	

Chicken Cytokine/Chemokine

⊙ (Cat. No. GCYT1-16K)

12 (Cat. No. GCYT1-16K-PX12)

12 (Cat. No. GCYT1-16K-PXBK12)

IFNα	IL-21
IFNγ	M-CSF
IL-2	MIP-1β/CCL4
IL-6	MIP-3α/CCL20
IL-10	RANTES/CCL5
IL-16	VEGF

MILLIPLEX® Veterinary Medicine and Animal Health Kits

Fetch the latest in animal health research with our growing selection of multiplex assays.

Discover more at SigmaAldrich.com/vetmed



Legend key for MILLIPLEX® kits

† Analytes which cannot be plexed together:
– Active and total
– Free and total

♦ Available in Cat. No. listed

▼ Premix panel only

Bulk indicates Space Saver Packaging

▲ These analytes cannot be plexed with other analytes in this panel in serum/plasma

■ Requires a protease inhibitor during sample collection

■ Requires sample extraction

** No standard/QC; antibody levels are reported as MFIs (Median Fluorescence Intensities)

● Serum/Plasma only

★ Tissue Culture samples only

^ Competitive assay format

⊙ Available for custom premix

° Analyte requires a different sample dilution from others in panel

⊙ Analyte cannot be measured in serum

Requires sample acidification

° Analyte cannot be measured in plasma

u Urine only

Equine Cytokine/Chemokine

- (Cat. No. EQCYTMAG-93K)
 23 (Cat. No. EQCYTMAG-93KPX23)
 23 (Cat. No. EQCTMG93KPX23BK)

Eotaxin/CCL11	IL-6
FGF-2/FGF-basic	IL-8/CXCL8
Fractalkine/CX3CL1	IL-10
G-CSF	IL-12 (p70)
GM-CSF	IL-13
GRO	IL-17A/CTLA8
IFN γ	IL-18
IL-1 α	IP-10/CXCL10
IL-1 β	MCP-1/CCL2
IL-2	RANTES/CCL5
IL-4	TNF α
IL-5	

Feline Cytokine/Chemokine ▼

- 19 (Cat. No. FCYTMAG-20K-PMX)
 19 (Bulk Cat. No. FCYTMAG20KPX19BK)
NON-CONFIGURABLE KIT

sFAS/TNFRSF6	IL-13
Flt3 Ligand	IL-18
GM-CSF	KC/GRO/CINC-1/ CXCL1
IFN γ	MCP-1/CCL2
IL-1 β	PDGF-BB
IL-2	RANTES/CCL5
IL-4	SCF
IL-6	SDF-1/CXCL12
IL-8/CXCL8	TNF α
IL-12 (p40)	

Ovine Cytokine/Chemokine Panel 1

- (Cat. No. SCYT1-91K)
 14 (Cat. No. SCYT-91K-PX14)
 14 (Bulk Cat. No. SCYT-91K-PXBK14)

IFN γ	IL-17A/CTLA8
IL-1 α	IL-36RA/IL-1F5
IL-1 β	IP-10/CXCL10
IL-4	MIP-1 α /CCL3
IL-6	MIP-1 β /CCL4
IL-8/CXCL8	TNF α
IL-10	VEGF-A

Porcine Cytokine/Chemokine

- (Cat. No. PCYTMAG-23K)
 13 (Cat. No. PCYTMAG-23K-13PX)
 13 (Bulk Cat. No. PCYTMAG23PMX13BK)

GM-CSF	IL-6
IFN γ	IL-8/CXCL8
IL-1 α	IL-10
IL-1 β	IL-12
IL-1Ra	IL-18
IL-2	TNF α
IL-4	

Porcine Acute Phase Protein

(Cat. No. PAPP1-160K)

CRP	Haptoglobin
-----	-------------

Metabolism/Endocrinology**Canine Gut Hormone**

(Cat. No. CGTMAG-98K)

Amylin (total) †	Insulin
Ghrelin (active) †	Leptin
GIP (total)	Pancreatic
GLP-1 (active) †	Polypeptide (PP)
Glucagon	PYY (total)

Canine Pituitary Expanded Panel

(Cat. No. CANPIT-96K)

ACTH	LH
FSH	Prolactin
GH	TSH

Toxicity**Canine Kidney Toxicity Expanded Panel 1 (Urine samples)**

(Cat. No. CKT1MAG-97K)

Clusterin	MCP-1/CCL2
Cystatin C	NGAL/Lipocalin-2
IL-8/CXCL8	Osteopontin (OPN)
KIM-1	

Canine Kidney Toxicity Panel 2 (Urine samples)

(Cat. No. CKT2MAG-97K)

Albumin	RBP4
β -2-Microglobulin	TFF-3

MULTI-SPECIES**Immunology****Multi-Species TGF β – Singleplex #**

(Cat. No. TGFBMAG-64K-01)
 (Bulk Cat. No. TGFBMAG-64K-01BK)
 Species: C, E, F, H, M, NHP, Por, R, guinea pig, hamster, rabbit

TGF β 1

Multi-Species TGF β – 3 Plex ▼ #

(Cat. No. TGFBMAG-64K-03)
 Species: H, M, NHP, R, guinea pig, hamster, mini pig; additionally, TGF- β 1 and TGF- β 2 can be detected in the serum of C, E, and rabbit

NON-CONFIGURABLE KIT

TGF β 1	TGF β 3
TGF β 2	

Metabolism/Endocrinology**Multi-Species Hormone ■ ^**

(Cat. No. MSHMAG-21K)
 Species: C, E, F, H, M, NHP, Por, R, guinea pig, hamster, rabbit

Cortisol	T3
Estradiol	T4
Progesterone	Testosterone NEW

KITS TO BE PHASED OUT**Human Cytokine/Chemokine Panel II**

- (Cat. No. HCYP2MAG-62K)
 23 (Cat. No. HCP2MAG-62K-PX23)
 23 (Bulk Cat. No. HCP2MAG62KPX23BK)

6Ckine/CCL21/ Exodus-2	IL-28A/IFN λ 2
BCA-1/CXCL13	IL-33/NF-HEV (mature)
CTACK/CCL27	LIF
ENA-78/CXCL5	MCP-2/CCL8
Eotaxin-2/CCL24/ MIPF-2	MCP-4/CCL13
Eotaxin-3/CCL26	MIP-1 δ /MIP-5/CCL15
I-309/CCL1	SCF
IL-16	SDF-1/CXCL12
IL-20	TARC/CCL17
IL-21	TPO
IL-23	TRAIL/TNFSF10
	TSLP

Legend key for MILLIPLEX® kits

- † Analytes which cannot be plexed together:
 – Active and total
 – Free and total
 ♦ Available in Cat. No. listed
 ▼ Premix panel only
 Bulk indicates Space Saver Packaging
 ▲ These analytes cannot be plexed with other analytes in this panel in serum/plasma

- ‡ Requires a protease inhibitor during sample collection
 ■ Requires sample extraction
 ** No standard/QC; antibody levels are reported as MFIs (Median Fluorescence Intensities)
 ● Serum/Plasma only
 ★ Tissue Culture samples only

- ^ Competitive assay format
 ● Available for custom premix
 ° Analyte requires a different sample dilution from others in panel
 ◎ Analyte cannot be measured in serum
 # Requires sample acidification
 § Analyte cannot be measured in plasma
 u Urine only

Cell Signaling MILLIPLEX® Assays

Akt/mTOR (Phosphoprotein) – 11 Plex

(Cat. No. 48-611MAG) AB2 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
Akt/PKB	✓ (Ser473)	H, M, R
GSK3α	✓ (Ser21)	H, M, R
GSK3β	✓ (Ser9)	H, M, R
IGF1R	✓ (Tyr1135/1136)	H, M
IR	✓ (Tyr1162/1163)	H
IRS1	✓ (Ser636)	H, M, R
mTOR	✓ (Ser2448)	H, M, R
p70S6 Kinase	✓ (Thr412)	H, M, R
PTEN	✓ (Ser380)	H, M, R
RPS6	✓ (Ser235/236)	H, M, R
TSC2	✓ (Ser939)	H, M, R

Akt/mTOR (Total) – 11 Plex

(Cat. No. 48-612MAG) AB2 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
Akt/PKB	✓	H, M, R
GSK3α	✓	H, M, R
GSK3β	✓	H, M, R
IGF1R	✓	H, M, R
IR	✓	H, R
IRS1	✓	H, M, R
mTOR	✓	H, M, R
p70S6 Kinase	✓	H, M, R
PTEN	✓	H, M, R
RPS6	✓	H, M, R
TSC2	✓	H, M, R

Early Apoptosis – 7 Plex

(Cat. No. 48-669MAG) AB2 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
Akt/PKB	✓ (Ser473)	H, M, R
BAD	✓ (Ser112)	H, M
Bcl-2	✓ (Ser70)	H
Active Caspase-8 (Asp384)	✓	H
Active Caspase-9 (Asp315)	✓	H
JNK/SAPK1	✓ (Thr183/Tyr185)	H, M, R
p53	✓ (Ser46)	H

Human Bcl-2 Family Apoptosis Panel 1 - 6 Plex

(Cat. No. 48-682MAG) AB1 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
BAD	✓	✓ (Ser112) H
BAX	✓	H
Bcl-xL/BAD (interaction)	✓	H
BIM	✓	H
Mcl-1/BIM (interaction)	✓	H

Human Bcl-2 Family Apoptosis Panel 2 - 4 Plex

(Cat. No. 48-683MAG) AB1 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
Bcl-2	✓	H
Bcl-xL	✓	H
Mcl-1	✓	H
NOXA/Mcl-1 (interaction)	✓	H

Human Cell Health - 16 Plex **NEW**

(Cat. No. 48-691MAG) AB2 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
CHOP	✓	H
Cleaved PARP	✓	H
Complex IV	✓	H,M,R
Cyclin B1	✓	H
eIF4B		✓ (Ser422) H,M,R
GRP78	✓	H,M,R
HIF-1α	✓	H
Histone H2A.x		✓ (Ser139) H
Histone H3		✓ (Ser10) H
HSP70	✓	H
Ki-67	✓	H
LC3B	✓	H,M,R
NF-κB		✓ (Ser536) H
p53		✓ (Ser15) H
Polyubiquitin K48-linkage	✓	H,M
RNA Pol II		✓ (Ser2) H,M,R

Learn More About Cancer and Metastasis Signaling Pathways

Read about all of the kits that can elucidate your signaling research at SigmaAldrich.com/milliplex-cancer-cs



- Can be plexed with other 2 Plexes
- * Cannot plex with other phospho Akt
- ▼ Premix panel only

AB1: Uses Assay Buffer 1
AB2: Uses Assay Buffer 2

H Human
M Mouse
R Rat

Human DNA Damage/Genotoxicity – 7 Plex(Cat. No. 48-621MAG) AB1 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
ATR	✓	H
Chk1		✓ (Ser345) H, M, R
Chk2		✓ (Thr68) H
H2A.X		✓ (Ser139) H, M, R
MDM2	✓	H, M, R
p21	✓	H
p53		✓ (Ser15) H

MAPK/SAPK (Phosphoprotein) – 10 Plex(Cat. No. 48-660MAG) AB2 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
ATF2		✓ (Thr71) H, M
c-Jun		✓ (Ser73) H, M, R
Erk/MAPK 1/2		✓ (Thr185/Tyr187) H, M, R
HSP27		✓ (Ser78) H
JNK/SAPK1		✓ (Thr183/Tyr185) H, M, R
MEK1		✓ (Ser222) H, M, R
MSK1		✓ (Ser212) H, M
p38/SAPK2A/B		✓ (Thr180/Tyr182) H, M, R
p53		✓ (Ser15) H
STAT1		✓ (Tyr701) H, M

Human RTK (Phosphoprotein)

(Choose analytes that meet your needs)

(Cat. No. HPRTKMAG-01K) AB1

Analyte	Total	Phosphorylated
c-Kit		(pan Tyr) H
c-Met/HGFR		(pan Tyr) H
ErbB1/EGFR		(pan Tyr) H
ErbB2/HER2		(pan Tyr) H
ErbB3/HER3		(pan Tyr) H
ErbB4/HER4		(pan Tyr) H
FGFR1		(pan Tyr) H
Flt3		(pan Tyr) H
IGF1R		(pan Tyr) H
M-CSFR		(pan Tyr) H
PDGFRβ		(pan Tyr) H
TIE1		(pan Tyr) H
TIE2		(pan Tyr) H
VEGFR1/Flt-1		(pan Tyr) H
VEGFR2/KDR/Flk-1		(pan Tyr) H
VEGFR3/Flt-4		(pan Tyr) H, M, R

Multi-Pathway (Phosphoprotein) – 9 Plex(Cat. No. 48-680MAG) AB2 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
Akt/PKB		✓ (Ser473) H, M, R
CREB		✓ (Ser133) H, M, R
Erk/MAPK 1/2		✓ (Thr185/Tyr187) H, M, R
JNK/SAPK1		✓ (Thr183/Tyr185) H, M, R
NFκB		✓ (Ser536) H, M, R
p38/SAPK2A/B		✓ (Thr180/Tyr182) H, M, R
p70S6 Kinase		✓ (Thr412) H, M, R
STAT3		✓ (Ser727) H, M, R
STAT5A/B		✓ (Tyr694/699) H, M, R

Multi-Pathway (Total) – 9 Plex(Cat. No. 48-681MAG) AB2 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
Akt/PKB	✓	H, M, R
CREB	✓	H, M, R
Erk/MAPK 1/2	✓	H, M, R
JNK/SAPK1	✓	H, M, R
NFκB	✓	H, M, R
p38/SAPK2A/B	✓	H, M, R
p70S6 Kinase	✓	H, M, R
STAT3	✓	H, M, R
STAT5A/B	✓	H, M, R

NFκB – 6 Plex(Cat. No. 48-630MAG) AB1 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
c-Myc	✓	H
FADD		✓ (Ser194) H
IκBα		✓ (Ser32) H
IKKα/β		✓ (Ser177/181) H
NFκB		✓ (Ser536) H, M
TNFR1	✓	H

Protein Translation – 6 Plex(Cat. No. 48-655MAG) AB2 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
eIF2α		✓ (Ser51) H, M, R
eIF-4B		✓ (Ser422) H, M, R
eIF-4E		✓ (Ser209) H, M, R
eIF-4G		✓ (Ser1108) H, M, R
4E-BP1	✓	✓ (Thr37/46) H, M, R

Human Ras-Raf Oncoprotein — 6 Plex(Cat. No. 48-684MAG) AB2 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
BRAF	✓ (Ser446)	H, M, R
CRAF	✓ (Ser338)	H, M, R
MEK1	✓ (Ser217/221)	H, M, R
Ras	✓	H, M, R
RasG12D	✓	H
RasG12V	✓	H

Src Family Kinase Active Site (Phosphoprotein) — 8 Plex(Cat. No. 48-650MAG) AB2 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
Blk	✓ (Tyr389)	H
Fgr	✓ (Tyr412)	H, R
Fyn	✓ (Tyr420)	H, M, R
Hck	✓ (Tyr411)	H, M
Lck	✓ (Tyr394)	H, M, R
Lyn	✓ (Tyr397)	H, R
Src	✓ (Tyr419)	H, M, R
Yes	✓ (Tyr421)	H, M, R

STAT (Phosphoprotein) — 5 Plex(Cat. No. 48-610MAG) AB2 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
STAT1	✓ (Tyr701)	H, M
STAT2	✓ (Tyr690)	H
STAT3	✓ (Tyr705)	H, M, R
STAT5A/B	✓ (Tyr694/699)	H, M, R
STAT6	✓ (Tyr641)	H

T-Cell Receptor (Phosphoprotein) — 7 Plex(Cat. No. 48-690MAG) AB2 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
CD3ε	✓ (pan Tyr)	H
CREB	✓ (Ser133)	H, M, R
Erk/MAPK 1/2	✓ (Thr185/Tyr187)	H, M, R
LAT	✓ (pan Tyr)	H
Lck	✓ (pan Tyr)	H, M, R
Syk	✓ (pan Tyr)	H
ZAP-70	✓ (pan Tyr)	H

TGFβ — 6 Plex(Cat. No. 48-614MAG) AB2 ▼ **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
Akt/PKB	✓ (Ser473)	H, M, R
Erk/MAPK 1/2	✓ (Thr185/Tyr187)	H, M, R
SMAD2	✓ (Ser465/467)	H, M, R
SMAD3	✓ (Ser423/425)	H, M, R
SMAD4	✓	H, M, R
TGFβRII	✓	H

Akt Phospho/Total — 2 Plex(Cat. No. 48-618MAG) AB2 ▼ * ●● **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
Akt/PKB	✓ (Ser473)	H, M, R
Akt/PKB	✓	H, M, R

Akt1 Phospho/Total — 2 Plex(Cat. No. 48-631MAG) AB2 ▼ * ●● **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
Akt1	✓ (Ser473)	H, M, R
Akt1	✓	H, M, R

Akt2 Phospho/Total — 2 Plex(Cat. No. 48-632MAG) AB2 ▼ * ●● **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
Akt2	✓ (Ser474)	H, M, R
Akt2	✓	H, M, R

CREB Phospho/Total — 2 Plex(Cat. No. 48-628MAG) AB2 ▼ ●● **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
CREB	✓ (Ser133)	H, M, R
CREB	✓	H, M, R

Erk/MAPK 1/2 Phospho/Total — 2 Plex(Cat. No. 48-619MAG) AB2 ▼ ●● **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated
Erk/MAPK 1/2	✓ (Thr185/Tyr187)	H, M, R
Erk/MAPK 1/2	✓	H, M, R

- Can be plexed with other 2 Plexes
- * Cannot plex with other phospho Akt
- ▼ Premix panel only

AB1: Uses Assay Buffer 1
AB2: Uses Assay Buffer 2

H Human
M Mouse
R Rat

JNK Phospho/Total – 2 Plex(Cat. No. 48-622MAG) AB2 ▼ ●● **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated	
JNK/SAPK1		✓ (Thr183/Tyr185)	H, M, R
JNK/SAPK1	✓		H, M, R

mTOR Phospho/Total – 2 Plex(Cat. No. 48-625MAG) AB2 ▼ ●● **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated	
mTOR		✓ (Ser2448)	H, M, R
mTOR	✓		H, M

p38 Phospho/Total – 2 Plex(Cat. No. 48-624MAG) AB1 or AB2 ▼ ●● **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated	
p38/SAPK2A/B		✓ (Thr180/Tyr182)	H, M, R
p38/SAPK2A/B	✓		H, M, R

STAT3 Phospho/Total – 2 Plex(Cat. No. 48-623MAG) AB2 ▼ ●● **NON-CONFIGURABLE KIT**

Analyte	Total	Phosphorylated	
STAT3		✓ (Tyr705)	H, M, R
STAT3	✓		H, M, R

MAPmate™ Singleplex Loading Control Assays

Plex loading control MAPmate™ assays into existing MILLIPLEX® Cell Signaling Panels. Our Cell Signaling Buffer and Detection Kit (Cat. No. 48-602MAG), may be purchased if additional buffers are required.

MAPmate™ Kits	Species Homology (Buffer)	Cat. No.
β-Tubulin (total)	H, M, R (AB1 & AB2)	46-713MAG
GAPDH (total)	H (AB2)	46-667MAG

●● Can be plexed with other 2 Plexes

* Cannot plex with other phospho Akt

▼ Premix panel only

AB1: Uses Assay Buffer 1

AB2: Uses Assay Buffer 2

H Human

M Mouse

R Rat



Luminex® Multiplexing Platforms

Driving Assay Consistency

Combined with the largest portfolio of multiplex analytes available, we provide you the power of Luminex® xMAP® technology, the most trusted, widely used platform for biomarker screening and protein analysis. As a Luminex® partner, we are a preferred distributor of Luminex® instruments, accessories, and software.

Luminex® xMAP® technology offers many advantages compared to other immunoassay methods:

- **Multiplexing:** Data generated simultaneously is less prone to user error, enabling the end-user to construct cleaner data sets to explore multiple parameters.
- **Low sample volume:** With minimal hands-on time, screen multiple analytes in a single sample using a maximum of 25 µL per well.
- **Magnetic bead-based format:** Responds rapidly and efficiently to a magnetic field, enabling better and faster washing techniques, including high-throughput washing options.
- **Reproducibility:** High-volume production of xMAP® microspheres allows assay standardization that solid-phased flat arrays cannot provide.
- **Speed/high-throughput:** Simultaneously measure the concentration of a large number of different analytes in a single sample, in 96- or 384-well format, to do your work faster, gaining early and comprehensive data.



Specifications

Instruments	xMAP® INTELLIFLEX® DR-SE*	xMAP® INTELLIFLEX®	FLEXMAP 3D®	Luminex® 200™
Cat. No.	INTELLIFLEX-DRSE	INTELLIFLEX-RU0	40-014	40-012
Optics Hardware	Lasers/APDs/PMTs	Lasers/APDs/PMTs	Lasers/APDs/PMTs	Lasers/APDs/PMTs
Technology	Flow-based	Flow-based	Flow-based	Flow-based
Multiplexing	Up to 500	Up to 500	Up to 500	Up to 100 (80 on MagPlex® microspheres)
Dynamic Range**	≥5.5 logs (RP1) ≥4.5 logs (RP2)	≥5.5 logs (RP1)	≥4.5 logs (RP1)	≥3.5 logs (RP1)
Read Time	96-well in ~20 min 384-well in ~75 min	96-well in ~20 min 384-well in ~75 min	96-well in ~20 min 384-well in ~75 min	96-well in ~45 min
Applications	Protein/nucleic acid	Protein/nucleic acid	Protein/nucleic acid	Protein/nucleic acid
Automation-Compatible Hardware	Front and side eject	Front eject only	Front eject only	Front eject only
Reporter Laser	532 nm (green) 405 nm (violet)	532 nm (green)	532 nm (green)	532 nm (green)
IQ/OQ	Yes	Yes	Yes	Yes
21 CFR Compliance	Yes	Yes	Yes	Yes
Automation	Yes	Yes	Yes	Yes
Data Analysis	Belysa® software	Belysa® software	xPONENT® basic + Belysa® software	xPONENT® basic + Belysa® software
Plate Format	96-well and 384-well	96-well and 384-well	96-well and 384-well	96-well
Footprint (Linear Bench Space, including PC)	58.4 cm x 61 cm x 76.2 cm	58.4 cm x 61 cm x 76.2 cm	110 cm x 62 cm x 63 cm	115 cm x 60 cm x 50 cm
Weight	54.4 kg (120 lbs)	54.4 kg (120 lbs)	77.1 kg (170 lbs)	49 kg (113 lbs)

*DR-SE = dual reporter side eject; **RP = reporter

Luminex® 200™ and FLEXMAP 3D® systems run on the Luminex® xPONENT® 4.3 data acquisition platform; the xMAP® INTELLIFLEX® systems run on INTELLIFLEX 1.0. All systems provide a consistent experience, from data input to results, no matter which instrument is used. All software adapts to fit the capabilities of each platform.

Next Generation Multiplexing


Harness the power of the xMAP® INTELLIFLEX® system at
SigmaAldrich.com/intelliflex



Conferma® ELISAs

Conferma® ELISAs are developed with a focus on critical reagents to deliver assays with excellent detectability, sensitivity, and lot-to-lot consistency.

Analyte	Std. Range (pg/mL)	LLOQ (Curve) (pg/mL)	Cat. No.
IL-6 (Human)	1.17 – 150	1.17	EZIL6-98K
IL-8 (Human)	0.82 – 200	0.82	EZHIL8-100K
MCP-1 (Human)	7.81 – 1,000	7.81	EZMCP1-99KRM
TNF-α (Human)	1.65 – 400	1.65	EZHTNFA-150K



Three lots of the TNF-α Conferma® ELISAs were evaluated for parallelism. Variation was minimal demonstrating consistent lot-to-lot performance.

Curve	Parallelism
Lot 2 vs. Lot 1	0.983
Lot 3 vs. Lot 1	0.992

ELISAs Designed For Consistency

Get details on Conferma® ELISA performance and see the difference for yourself at: SigmaAldrich.com/conferma



Millipore® Brand ELISAs

Metabolic/Endocrine/ ELISAs	Species	Standard Curve Range	Sensitivity	Sample Volume	Cat. No.	Bulk Packaging Cat. No.*
Adiponectin	Human	1.56–200 ng/mL	0.2 ng/mL	10 µL	EZHADP-61K	EZHADP-61BK
Adiponectin (High Molecular Weight)	Human	1.5–200 ng/mL	0.5 ng/mL	10 µL	EZHMWAN-65K	
Adiponectin	Mouse	1–50 ng/mL	0.2 ng/mL	10 µL	EZMADP-60K	EZMADP-60BK
Amylin (active)	Human	1–100 pM	0.7 pM	50 µL	EZHA-52K	
C-Peptide	Human	0.2–20 ng/mL	0.05 ng/mL	10 µL	EZHCP-20K	EZHCP-20BK
C-Peptide	Canine	0.2–10 ng/mL	0.24 ng/mL	25 µL	EZCCP-47K	
C-Peptide 2	Mouse, Rat	25–1,600 pM	15.0 pM	20 µL	EZRMCP2-21K	
FGF-21	Human	31.25–2,000 pg/mL	10.0 pg/mL	50 µL	EZHFGF21-19K	
FGF-21	Mouse, Rat	49.4–12,000 pg/mL	10.0 pg/mL	10 µL	EZRMFGF21-26K	
FGF-23	Human	9.9–2,400 pg/mL	3.5 pg/mL	50 µL	EZHFGF23-32K	EZHFGF23-32BK
Ghrelin (active)	Human	25–2,000 pg/mL	15.0 pg/mL	20 µL	EZGRA-88K	EZGRA-88BK
Ghrelin (active)	Mouse, Rat	25–2,000 pg/mL	8.0 pg/mL	20 µL	EZRGRA-90K	
Ghrelin (total)	Human	100–5,000 pg/mL	50.0 pg/mL	20 µL	EZGRT-89K	EZGRT-89BK
Ghrelin (total)	Mouse, Rat	0.1–10 ng/mL	0.04 ng/mL	20 µL	EZRGR-91K	
GIP (total)	Human	8.2–2,000 pg/mL	4.2 pg/mL	20 µL	EZHGIP-54K	EZHGIP-54BK
GIP (total)	Mouse, Rat	8.2–2,000 pg/mL	4.2 pg/mL	10 µL	EZRMGIP-55K	EZRMGIP-55BK
GLP-1 (active)	Multi-Species	2–100 pM	1.0 pM	100 µL	EGLP-35K	EGLP-35BK
GLP-1 High Sensitivity (active) Δ●●	Multi-Species	See data sheet	0.14 pM	50 µL	EZGLPHS-35K	EZGLPHS-35BK
GLP-1 (total)	Multi-Species	4.1–1,000 pM	1.0 pM	20–50 µL	EZGLP1T-36K	EZGLP1T-36BK
GLP-2	Multi-Species	1–64 ng/mL	0.3 ng/mL	50 µL	EZGLP2-37K	

Metabolic/Endocrine/ ELISAs	Species	Standard Curve Range	Sensitivity	Sample Volume	Cat. No.	Bulk Packaging Cat. No.*
Glucagon Δ	Human, Mouse, Rat	0.02–2 ng/mL	0.003 ng/mL	150–300 μ L	EZGLU-30K	EZGLU-30BK
Growth Hormone (GH)	Mouse, Rat	0.7–50 ng/mL	0.07 ng/mL	10 μ L	EZRMGH-45K	EZRMGH-45BK
Insulin	Human	2–200 μ U/mL	1.0 μ U/mL	20 μ L	EZHI-14K	EZHI-14BK
Insulin	Mouse, Rat	0.2–10 ng/mL	0.1 ng/mL	10 μ L	EZRMI-13K	EZRMI-13BK
Leptin	Canine	0.78–50 ng/mL	0.21 ng/mL	20 μ L	EZCL-31K	
Leptin	Mouse	0.2–30 ng/mL	0.05 ng/mL	10 μ L	EZML-82K	EZML-82BK
Leptin	Rat	0.2–30 ng/mL	0.08 ng/mL	10 μ L	EZRL-83K	EZRL-83BK
Leptin “Dual Range”	Human	0.5–100 ng/mL	0.2 ng/mL	25 μ L	EZHL-80SK	EZHL-80BK
Procollagen Type IIA N-Propeptide (PIIANP)	Human	lot dependent	30.0 ng/mL	5 μ L	EZPIIANP-53K	
Proinsulin (total)	Human	2–200 pM	0.5 pM	20 μ L	EZHPI-15K	EZHPI-15BK
PYY (total)	Human	10–2,000 pg/mL	6.5 pg/mL	20 μ L	EZHPYYT66K	
Resistin	Human	0.16–5 ng/mL	0.02 ng/mL	20 μ L	EZHR-95K	EZHR-95BK
SAA-3	Mouse	0.078–5 μ g/mL	0.078 μ g/mL	10 μ L	EZMSAA3-12K	
Neuroscience ELISAs	Species	Standard Curve Range	Sensitivity	Sample Volume	Cat. No.	
Amyloid beta 1-40	Human	16–500 pg/mL	4 pg/mL	50 μ L	EZHS40	
Amyloid beta 1-42	Human	16–500 pg/mL	5 pg/mL	50 μ L	EZHS42	
Amyloid beta, Set	Human	Contains 1 each of EZHS40 and EZHS42			EZHS-SET	
Amyloid beta (Brain) 1-40	Human	16–500 pg/mL	4 pg/mL	50 μ L	EZBRAIN40	
Amyloid beta (Brain) 1-42	Human	16–500 pg/mL	5 pg/mL	50 μ L	EZBRAIN42	
Amyloid beta (Brain), Set	Human	Contains 1 each of EZBRAIN40 and EZBRAIN42			EZBRAIN-SET	
BDNF (Brain-Derived Neurotrophic Factor)	Human, Rat	7.8–500 pg/mL	7.8 pg/mL	50 μ L	CYT306	
NPY (Neuropeptide Y)	Human	5–1,000 pg/mL	2 pg/mL	50 μ L	EZHNPY-25K	
NPY (Neuropeptide Y)	Mouse, Rat	0.01–2 ng/mL	0.004 ng/mL	20 μ L	EZRMNPY-27K	
PEDF (Pigment Epithelium-Derived Factor)	Human	0.9–62.5 ng/mL	0.9 ng/mL	50 μ L	CYT420	
Phosphorylated Neurofilament, (pNF-H) Sandwich	Multi- Species	0.0293–15 ng/mL	0.0585 ng/mL	1–10 μ L	NS170	
S100B	Human	2.7–2,000 pg/mL	1.3 pg/mL	50 μ L	EZHS100B-33K	

* Bulk packaging available on select kits — more environmentally friendly and saves space (10 kit equivalent)

• Preferred assay for measuring GLP-1 (active)

Δ Chemiluminescent assay

Sigma-Aldrich® Brand ELISAs

We offer a portfolio of >1,300 ELISAs, covering a diverse range of species, research areas, and sample types. Find your ELISA at SigmaAldrich.com/elisa



Ancillary Equipment to Optimize Your Assays



Instruments	BioTek® 405™ TSUV Plate Washer for SMC®/MILLIPLEX® Technology NEW	BioTek® 405™ TS Magnetic 96-Well Washer
Cat. No.	95-0004-06	40-092AB
Supported Technology	SMC® immunoassays MILLIPLEX® immunoassays	MILLIPLEX® immunoassays
Instrument Control	Touchscreen and computer software	Touchscreen and computer software
Features	• Custom magnetic plate specific for use with SMC® technology • Ultrasonic Advantage™ program and 4 buffer switching • Optimized cell wash including Shaking & Soaking	• Supports 96-well magnetic bead washing • Ultrasonic Advantage™ program for maintenance • Quick menu for priming and washing
Wash Protocols	Pre-programmed with SMC® and MILLIPLEX® assay wash protocols	Predefined sample methods for easy operation
Plate Format	96-well for SMC® assays 96- and 384-well for MILLIPLEX® assays	96-well plates
Washer/Dispenser Options	Vacuum filtration, biomagnetic separation	Biomagnetic separation
Volume Range	50 – 3,000 µL/well	25 – 3,000 µL/well, in 1 µL increments
Residual Volume	≤ 2 µL per well	≤ 2 µL per well
Wash or Read Speed	300 µL/well, 3 cycles; ≤ 30 s	300 µL/well, 3 cycles; ≤ 30 s
Wash Cycles	1 to 250	1 to 250
Shaking	Programmable up to 60 min: slow, medium, fast, or variable	Programmable up to 60 min: slow, medium, fast, or variable
Automation Capability	BioSpa, BioStack, BenchCel, 3rd Party	BioTek® BioStack microplate stacker and 3rd Party
Footprint	14" W x 17" D x 10" H (35.6 x 43.2 x 25.4 cm)	14" W x 17" D x 10" H (35.6 x 43.2 x 25.4 cm)
Weight	With internal buffer switching: 36 lb (16.5 kg)	30 lb (13.5 kg)

Related Products

Description	Cat. No.
BioTek® 50™ TS Microplate Washer	40-301
BioTek® 800™ TS Absorbance Reader with Gen5™ Software	40-006
BioTek® MultiFlo™ FX Multimode Dispenser	40-999
SMC® Plate Washer Evaluation Kit	03-0165-00
Flat Magnet, for 96-Well Plates, for use with MILLIPLEX® Assays (and for use with Cat. No. 95-0004-06)	7103016
Flat Magnet, for 384-Well Plates, for use with MILLIPLEX® Assays (and for use with Cat. No. 95-0004-06)	7103017
Handheld Magnetic Bead Washer Separator Block for 96-Well Flat Bottom or Conical Well Plates	40-285
BioTek® 800™ TS Product Qualification Package (to be sold with Cat. No. 40-006)	1560516
Absorbance Test Plate (to be sold with Cat. No. 40-006)	7260522
Vacuum Filter 96-Well (to be sold with Cat. No. 40-092AB)	1170008

Enhance Your Workflows

Explore BioTek® washers for our platforms at
SigmaAldrich.com/smc-washer and SigmaAldrich.com/milliplex-washer



Belysa® Immunoassay Curve Fitting Software

(Cat. No. 40-122)

Our proprietary software package for curve fitting, examination, and comparison of data acquired from a variety of immunoassay platforms. Belysa® software has been designed to provide an easy-to-use tool to optimize curve fit and confirm the integrity of data within a plate or across plates from multiple runs.

Key Features and Benefits


- User-friendly interface
- Automatic and manual curve fitting (4pl, 5pl, linear, competitive, cubic spline)
- Curve comparison tools
- Rules-based data flagging
- Suitable for use with RUO Luminex® instruments, FemtoQuest™ platform, and ELISA .csv acquisition files
- Windows 10 and macOS (beta) compatible

Data displayed after selecting curve fit model:


- Sample concentration
- Standard recovery
- Equation of line
- Limit of Detection (LOD)
- Lower Limit of Quantitation (LLOQ)
- Minimum Detectable Dose (MD)

Other features:

- Data is exportable to: Excel, .csv, .txt, and .pdf
- Data autoflagging based on bead count, %CV, or BLOQ
- Curve comparison tool to evaluate parallelism and relative potency of standards



Example 1. Simply drag and drop the .csv output file into the Belysa® browser for instant data review.



Example 2. Comparison of two standard curves in Belysa® software from two lots of the same MILLIPLEX® assay run 1 year apart.

Ready To Start Comparing Curves?

Get more details about Belysa® Software at: SigmaAldrich.com/belysa



CADI: Custom Assay Development & Innovation

Accelerate your research with custom SMC®, MILLIPLEX®, and ELISA assays designed for your specific biomarker needs.

We understand you don't always have the time, resources, or expertise to develop your own assay for your protein of interest. Rely on our vast development expertise and our ability to produce high-quality, reproducible immunoassays to help you accelerate your program from discovery research into clinical trials with a custom-designed solution.



Get started today!

View a complete listing of services at SigmaAldrich.com/customassay



Fit-For-Purpose Custom Assay Project Workflow

Develop a new SMC®, MILLIPLEX®, or ELISA assay which is fit for your purpose. We follow a milestone-based approach to generate an assay that quantifies your exact protein or proteins of interest. You will receive updates and data reviews during each milestone, offering you peace of mind that your project is on schedule and meeting specifications.



Example Custom Assay Offerings

Cat. No.	Description	Description
SPRCUS1014	Custom Human 384-Well Circulating Cancer Biomarker Panel 3 8-Plex	H (S/P, Sup, Lys)
SPRCUS1016	Custom Human 384-Well Angiogenesis Panel 2 20-Plex	H (S/P, Sup, Lys)
SPRCUS1042	Custom Human 384-Well Immuno-Oncology Checkpoint Protein Panel 17-Plex	H (S/P, Sup)

Beyond the Assay Development Workflow

In addition to our assay development services, we can support your other custom assay needs.

Our additional capabilities include:

Switching Formats

- MILLIPLEX® Assays: 96-well to 384-well
- SMC® Assays: bead-based to plate-based
- Converting MILLIPLEX® assays to SMC® assay platform

Sample Testing

- Prototype sample testing
- Custom kit sample testing (SMC® and MILLIPLEX® assays)
- Off-the-shelf immunoassay kit testing (SMC® and MILLIPLEX® assays)

Biotherapeutic Assay Development

- Pharmacokinetics
- Pharmacodynamics
- Immunogenicity

SMCxPlore™ Proof of Concept Sample Testing:

Use our SMCxPlore™ proof of concept sample testing service to “explore” SMC® technology with your analyte of interest or critical samples. Test up to 30 of your critical samples using one of our highly verified SMC® immunoassays.

Questions About CADI?

Explore our FAQs at SigmaAldrich.com/cadi-faqs



Find Out What Makes Our Immunoassays Stand Out

"MILLIPLEX® multiplex assays are high quality, reliable kits to detect low concentration markers such as cytokines, for use in limited volume samples."

"We value the reproducibility of MILLIPLEX® kits and their low plate-to-plate variation. The ease of panel configuration and ordering, as well as easy to follow protocols, save time both before and during analysis."

— **Danielle Stephens**, Forsyth Institute Multiplex Core, Cambridge, MA

"MILLIPLEX® assays save valuable time and sample by allowing us to measure several targets at once. We also only have to thaw plasma samples once, lessening the risk of sample degradation."

"We trusted the proven specificity and sensitivity of MILLIPLEX® assays, so we knew we would not be wasting precious samples."


— **Mary Young**, University of Virginia School of Medicine, Division of Infectious Diseases, Charlottesville, VA

"This panel has allowed me to quantify more cytokines with less sample and more quickly than anything else."

— **Dr. Kyle McLean**, Department of Animal Science, University of Tennessee Institute of Agriculture, Knoxville, TN

Get Inspired by the Latest Immunoassay Research Posters at
SigmaAldrich.com/immunoassays-posters





Beyond Biomarkers

Keep your focus on the next stage

Rigorous Assay Development

Specificity ●●

- Antibody specificity is tested to ensure negligible cross-reactivity in the tested sample types
- Assay specificity is ensured by confirming consistent performance in singleplex and multiplex formats

Method Comparisons ●●

- We test our kits against in-house kits and kits from other vendors when available, ensuring the highest performing kits

Selectivity ●●

- Assay buffers and bead diluents are optimized to enhance antibody binding to only those analytes of interest in samples

Detection and Sensitivity ●

- The assay range and minimum detectable concentrations (minDCs or LLOQ) for each analyte is published in our protocols, and is based on actual samples

Performance in a Sample Matrix ●

- Assays are verified for the sample type noted in the protocol; for serum/plasma sample kits, we provide an optimized serum matrix to mimic the environment of the sample, normalizing assay performance

Reproducible Results You Can Trust

Stability ●●

- All kits are rigorously tested for shipping stability to determine impact on each analyte
- Sample stability is examined at a range of temperatures, and by freeze/thaw

Precision ●●

- Precision of control standards are typically within 15% CV for intra-assay and 20% CV for inter-assay

Accuracy ●

- Spike recovery in sample is performed for each analyte at three concentrations; accuracy is normally within $\pm 30\%$

Dilution Linearity/Parallelism ●

- Diluted sample results must be directly proportional to the concentration of analyte in the sample, typically within $\pm 30\%$

Lot-to-Lot Consistency ●

- A “gold standard” calibrator is defined during assay development and used as a reference for all future production lots

We'll help you choose the right platform and assays to meet your needs today, and we'll partner with you to meet those needs in the future — without compromising quality.

- Screening Assays
- Qualified and Verified Assays



Preparation, Separation,
Filtration & Monitoring Products

MilliporeSigma
400 Summit Drive
Burlington, MA 01803

SigmaAldrich.com



Scan to download
a digital copy.



Keep up to date!

Don't miss out on updates by
signing up for our newsletter:
SigmaAldrich.com/analyteupdate

To place an order or receive technical assistance

Order/Customer Service: **SigmaAldrich.com/order**

Technical Service: **SigmaAldrich.com/techservice**

Safety-related Information: **SigmaAldrich.com/safetycenter**

We have built a unique collection of life science brands with
unrivalled experience in supporting your scientific advancements.

Millipore® Sigma-Aldrich® Supelco® Milli-Q® SAFC® BioReliance®

© 2025 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved. MilliporeSigma, the vibrant M, Millipore, Sigma-Aldrich, Supelco, Milli-Q, SAFC, BioReliance, AAW, Belysa, Conferma, FemtoQuest, MAPmate, and MILLIPLEX are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. All other trademarks are the property of their respective owners. Detailed information on trademarks is available via publicly accessible resources.