

Product information sheet

## Anti-Caspr2 antibody produced in rabbit

Affinity Isolated Antibody, lyophilized powder

**C8737**

### Product Description

Anti-Caspr2 (Contactin-Associated Protein 2) is developed in rabbit using a highly purified synthetic peptide corresponding to amino acids residues 1315-1331 (CDPNFTETIDESKKEWLI) of human Caspr2, with an additional N-terminal cysteine, as the immunogen. This sequence is identical in the mouse protein. The antibody was affinity isolated on immobilized immunogen.

Anti-Caspr2 recognizes the Caspr2 protein in rat brain membranes by immunoblotting.

Caspr2, a member of the neurexin superfamily, is a mammalian homolog of *Drosophila* Neurexin IV (Nrx-IV).<sup>1</sup> Localized to myelinated axons, Caspr2 is believed to play a role in the local differentiation of the axon into functional subdomains. This division is important as salutatory conduction depends on different sets of ion channels being present along myelinated axons. The domains, established during axonal development,<sup>2</sup> are believed to act as barriers that membrane proteins cannot cross. Caspr2 is precisely colocalized with Shaker-like K<sup>+</sup> channels in the juxtaparanodal region flanking nodes of Ranvier and has been shown to interact with the channels as well as PSD-95 through its C-terminal PDZ domain.<sup>3</sup> Caspr (Paranodin) as well as two recently identified family members, Caspr3 and Caspr4,<sup>4</sup> are expressed in different and distinct regions of the central nervous system (CNS) where they may function in cell recognition. The intracellular partners of these proteins are poorly characterized. However, Caspr and Caspr2 may interact with the actin-based cytoskeleton through 4.1B.<sup>5</sup>

### Reagents

Anti-Caspr2 is supplied as an affinity isolated antibody lyophilized at 0.4 mg/mL from phosphate buffered saline, pH 7.4, containing 1% bovine serum albumin, 5% sucrose, and ≤ 0.1% sodium azide.

### Precautions and Disclaimer

This product is for R&D use only. Not for drug, household, or other uses. Please consult the Safety Data Sheet for information regarding hazards and safe handling practices.

### Preparation Instructions

Reconstitute the lyophilized vial with 0.05 mL or 0.2 mL of deionized water, depending on the package size purchased. Antibody dilutions should be made in buffer containing 1-3% bovine serum albumin.

### Storage/Stability

Prior to reconstitution, store at -20 °C. After reconstitution, the stock antibody solution may be stored at 4 °C for up to 2 weeks. For extended storage, freeze in working aliquots. Repeated freezing and thawing is not recommended. Storage in "frost-free" freezers is not recommended. If slight turbidity occurs upon prolonged storage, clarify the solution by centrifugation before use. Working dilution samples should be discarded if not used within 12 hours.

### Product Profile

The recommended working dilution is 1:200 for immunoblotting. This antibody detects a single band at ~180 kDa.

Note: In order to obtain best results and assay sensitivities of different techniques and preparations, it is recommended to determine optimal working dilutions by titration test.

### References

1. Poliak, S. et al., *Neuron*, **24**, 1037-1047 (1999).
2. Poliak, S. et al., *J. Neurosci.*, **21**, 7568-7575 (2001).

3. Rasband, M.N. et al., J. Cell Biol., **159**, 663-672 (2002).
4. Spiegel, I. et al., Mol. Cell. Neurosci., **20**, 283-297 (2002).
5. Denisenko-Nehrbass, N. et al., Eur. J. Neurosci., **17**, 411-416 (2003).

## Notice

We provide information and advice to our customers on application technologies and regulatory matters to the best of our knowledge and ability, but without obligation or liability. Existing laws and regulations are to be observed in all cases by our customers. This also applies in respect to any rights of third parties. Our information and advice do not relieve our customers of their own responsibility for checking the suitability of our products for the envisaged purpose.

The information in this document is subject to change without notice and should not be construed as a commitment by the manufacturing or selling entity, or an affiliate. We assume no responsibility for any errors that may appear in this document.

## Technical Assistance

Visit the tech service page at [SigmaAldrich.com/techservice](https://SigmaAldrich.com/techservice).

## Standard Warranty

The applicable warranty for the products listed in this publication may be found at [SigmaAldrich.com/terms](https://SigmaAldrich.com/terms).

## Contact Information

For the location of the office nearest you, go to [SigmaAldrich.com/offices](https://SigmaAldrich.com/offices).

The life science business of Merck KGaA, Darmstadt, Germany operates as MilliporeSigma in the U.S. and Canada.

MilliporeSigma, and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. All other trademarks are the property of their respective owners. Detailed information on trademarks is available via publicly accessible resources.

© 2022 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved.

C8737dat Rev 03/22

**Millipore  
Sigma**