

Recommended Reagents

Below is a list of suitable reagents to work with bottle top dispenser :-

Acetaldehyde	Butyl methyl ether
Acetic acid (glacial), 100%	Butylamine
Acetic acid, ≤ 96%	Butyric acid
Acetic anhydride	Calcium carbonate
Acetone	Calcium chloride
Acetonitrile	Calcium hydroxide
Acetophenone	Calcium hypochlorite
Acetyl chloride	Carbon tetrachloride
Acetylacetone	Chloro naphthalene
Acrylic acid	Chloroacetaldehyde, ≤ 45%
Acrylonitrile	Chloroacetic acid
Adipic acid	Chloroacetone
Allyl alcohol	Chlorobenzene
Aluminium chloride	Chlorobutane
Amino acids	Chloroform
Ammonia, ≤ 20%	Chlorosulfonic acid
Ammonia, 20-30%	Chromic acid, ≤ 50%
Ammonium chloride	Chromosulfuric acid
Ammonium fluoride	Copper sulfate
Ammonium sulfate	Cresol
n-Amyl acetate	Cumene (Isopropyl benzene)
Amyl alcohol (Pentanol)	Cyclohexane
Amyl chloride (Chloropentane)	Cyclohexanone
Aniline	Cyclopentane
Barium chloride	Decane
Benzaldehyde	1-Decanol
Benzene (Benzol)	Dibenzyl ether
Benzine (Petroleum benzine)	Dichloroacetic acid
bp 70-180 °C	Dichlorobenzene
Benzoyl chloride	Dichloroethane
Benzyl alcohol	Dichloroethylene
Benzylamine	Dichloromethane
Benzylchloride	Diesel oil (Heating oil), bp 250-350 °C
Boric acid, ≤ 10%	Diethanolamine
Bromobenzene	Diethyl ether
Bromonaphthalene	Diethylamine
Butanediol	1,2 Diethylbenzene
1-Butanol	Diethylene glycol
n-Butyl acetate	

Recommended Reagents

Dimethyl sulfoxide (DMSO)	Methyl formate
Dimethylaniline	Methyl propyl ketone
Dimethylformamide (DMF)	Methylene chloride
1.4 Dioxane	Mineral oil (Engine oil)
Diphenyl ether	Monochloroacetic acid
Essential oil	Nitric acid, ≤ 30%
Ethanol	Nitrobenzene
Ethanolamine	Oleic acid
Ethyl acetate	Oxalic acid
Ethylbenzene	n-Pentane
Ethylene chloride	Peracetic acid
Fluoroacetic acid	Perchloric acid
Formaldehyde, ≤ 40%	Perchloroethylene
Formamide	Petroleum, bp 180-220 °C
Formic acid, ≤ 100%	Petroleum ether, bp 40-70 °C
Glycerol	Phenol
Glycol (Ethylene glycol)	Phenylethanol
Glycolic acid, ≤ 50%	Phenylhydrazine
Heating oil (Diesel oil), bp 250-350 °C	Phosphoric acid, ≤ 85%
Heptane	Phosphoric acid, 85%
Hexane	Sulfuric acid, 98% 1:1
Hexanoic acid	Piperidine
Hexanol	Potassium chloride
Hydriodic acid, ≤ 57%	Potassium dichromate
Hydrobromic acid	Potassium hydroxide
Hydrochloric acid, ≤ 20%	Potassium permanganate
Hydrochloric acid, 20-37%	Propionic acid
Hydrogen peroxide, ≤ 35%	Propylene glycol (Propanediol)
Isoamyl alcohol	Pyridine
Isobutanol	Pyruvic acid
Isooctane	Salicylaldehyde
Isopropanol (2-Propanol)	Scintillation fluid
Isopropyl ether	Silver acetate
Lactic acid	Silver nitrate
Methanol	Sodium acetate
Methoxybenzene	Sodium chloride
Methyl benzoate	Sodium dichromate
Methyl butyl ether	Sodium fluoride
Methyl ethyl ketone	Sodium hydroxide, ≤ 30%
	Sodium hypochlorite

Recommended Reagents

Sulfuric acid, ≤ 98%
Tartaric acid
Tetrachloroethylene
Tetramethylammonium hydroxide
Toluene
Trichloroacetic acid
Trichlorobenzene
Trichloroethane
Trichloroethylene
Trichlorotrifluoro ethane
Triethanolamine
Triethylene glycol
Trifluoro ethane
Trifluoroacetic acid (TFA)
Turpentine
Urea
Xylene
Zinc chloride, ≤ 10%
Zinc sulfate, ≤ 10%

CAUTION:-

Always follow instructions in the operating manual of the dispenser as well as the reagent manufacturer's specifications. In addition to these chemicals, a variety of organic and inorganic saline solutions (e.g., biological buffers), biological detergents and media for cell culture can be dispensed. If used with strong acids, it is advised to rinse & remove dispenser at the end of every working day & store it safely. If require information on chemicals not listed, please contact us.