

Product Information

Collagens for Cell Culture

<u>Product Number</u>	<u>Description</u>	<u>Source</u>	<u>Storage</u>	<u>Target Cells For Attachment</u>	<u>Concentration For Use</u>	<u>Refs.</u>
C1809	COLLAGEN TYPE I Acid soluble powder	kangaroo tail	2-8 °C	muscle cells, hepatocytes, spinal ganglion, embryonic lung cells, schwann cells. Mediate the attachment of many cell types	6-10 µg/cm ²	33
C7661		rat tail				1,2,5,7, 8,11,17
C9791		calf skin				
C8919	COLLAGEN TYPE I 0.1% Solution Sterile-filtered (Not suitable for 3D gel formation)					
C9301	COLLAGEN TYPE II Powder	chicken sternal cartilage		chondrocytes		18,19
C0543	COLLAGEN TYPE IV Powder	Engelbreth-Holm-Swarm mouse sarcoma	-20 °C; store solubilized product at 2-8 °C	epithelial cells, endothelial cells, muscle cells, nerve cells		5,12,13, 14,15, 16,17
C5533	COLLAGEN TYPE IV Lyophilized	human placenta	-20 °C			34

Product Use

- **Collagen Type I (Product Nos. C1809, C7661, C9791, and C8919)**
Optimal conditions for attachment must be determined for each cell line and application.
 1. Add collagen to 0.1 M acetic acid to obtain 0.1% (w/v) collagen solution. Stir at room temperature 1-3 hours until dissolved. (C8919 is prepared as a 0.1% solution, step 1 is not necessary for this product.)
 2. We recommend transferring the collagen solution to a glass bottle with a screw cap and carefully layering chloroform at the bottom. The amount of chloroform to use should be ~10% of the volume of collagen solution. DO NOT SHAKE OR STIR. Allow to stand overnight at 2-8 °C. Aseptically remove the top layer containing the collagen solution. We do not recommend sterilizing the collagen solution by membrane filtration. We have found substantial protein loss by this method. (C8919 is a sterile solution, step 2 is not necessary for this product.)
 3. Dilute desired volume (according to surface area to be treated) of sterile stock solution in step 2 or C8919 10-fold to a working concentration of 0.01% for coating surfaces.
 4. Coat dishes with 6-10 µg/cm². Allow the protein to bind for several hours at room temperature or 37 °C, or overnight at 2-8 °C.

- 5. Remove excess fluid from the coated surface, and allow it to dry overnight. If the collagen solution is not sterile, the dried, coated surface can be sterilized easily by overnight exposure to UV light in a sterile tissue culture hood.
 - 6. Rinse with sterile tissue culture grade water or a balanced salt solution before introducing cells and medium.
- **Collagen Type II and Type IV (Product Nos. C9301, C0543, and C5533)**
Optimal conditions for attachment must be determined for each cell line and application.
 1. Collagen Types II and IV may be reconstituted to a concentration of 0.5-2.0 mg/ml in 0.25% acetic acid. **Dissolve for several hours at 2-8 °C, occasionally swirling.**
 2. Coating of tissue culture plastic dishes may be performed by air drying the above protein solution or by preincubating the same solution overnight at 2-8 °C (or several hours at 37 °C) without air drying.
 3. Dried coated dishes can be sterilized overnight by exposure to UV light in a sterile tissue culture hood or by rinsing with 70% ethanol. Alternatively, the collagen solution may be sterilized by dialysis in a 0.25% acetic acid and 0.5% chloroform solution.

References:

1. Cannella, M. and Ross, R. (1987). Experimental Neurology 95:652-660.
2. Foster, R. et al. (1987). Developmental Biology 122:11-20.
3. Grant, P. and Tseng, Y. (1986). Developmental Biology 114:475-491.
4. Hauschka, S. (1972). Cultivation of muscle tissue. In: Growth, Nutrition, and Metabolism of Cells in Culture. Rothblat G. and Cristofals, V. (eds). Academic Press, NY. Vol 2: 67-130.
5. Kleinman, H. et al. (1987). Analytical Biochemistry 166:1-13.
6. Kleinman, H. (1985). Cellular Biochem. 27:317-325.
7. Leifer, D. (1984). Science 224(4646): 303-306.
8. Needham, L. et al. (1988). Laboratory Investigation 59(4): 538-548.
9. Yaffe, D. (1973). Rat Skeletal Muscle Cells. In: Tissue Culture: Methods and Applications. Kruse, P. and Patterson, M. (eds). New York Academic Press, pp 106-109.
10. Yamada, K. and Akiyama, S. (1984). Preparation of Cellular Fibronectin. In: Methods for Preparation of Media, Supplements, and Substrata for Serum -Free Animal Cell Culture Vol 1. Alan R. Liss, Inc., New York, NY. pp. 215-230.
11. Yong, V. W. et al. (1988). Dev. Neuroscience 10:222-230.
12. Aumailley, M. and Timpl, R. (1986). Cell Biol. 103:1569-1575.
13. Bornstein, M. (1958). Laboratory Investigation 7(2):134-137.
14. Terranova, V. et al. (1980). Cell 22:719-726.
15. Timpl, R. et al. (1978). Eur J Biochem. 84:43-52.
16. Tryggvason, K. et al. (1980). Biochemistry 19:1284-1289.
17. Kleinman, H. et al. (1982). Biochemistry 21:6188-6193.
18. Trelstad, R. et al. (1970). Biochemistry 9:4993.
19. Miller, E. (1971). Biochemistry 10:1652.
20. Ruoslahti, E. and Pierschbacher, M. (1987). Science 238:491-497.
21. Pierschbacher, M. and Ruoslahti, E. (1987). J. Biol. Chem. 262(36):17294-17298.
22. Cappello, J. and Crissman, J. (1990). ACS Polymer Preprints 31(1):193-194.
23. Cappello, J. et al. (1990). Materials Research Society Symposium Proceedings 174:267-276
24. Dixit, S. Conn. (1985). Tissue Res. 14:31.
25. Wewer, U. et al. (1983). J. Biol. Chem. 258:12654.
26. Barnes, D. and Silnutzer, J. (1983). J. Biol. Chem. 258:12548-12552.
27. Barnes, D. et al. (1984). Anal. Biochem. 137:196-204.
28. Silnutzer, J. and Barnes, D. (1984). Biochem Biophys. Res. Commun. 118:339-343.
29. Pytela, R. et al. (1986). Science 231:1559-1562.
30. Charo, I. et al. (1987). J. Biol. Chem. 262:9935-9938.
31. Cheresh, D. and Spiro, R. (1987). J. Biol. Chem. 262:17703-17711.
32. Oldberg, A. et al. (1988). J. Biol. Chem. 263: 19433-19436.
33. Niyibizi, et al. (1984). J. Biol. Chem. 259: 14170.
34. Bailey, A. J., et al. (1979) FEBS Letters 99: 361.