

SIGMA QUALITY CONTROL TEST PROCEDURE

ProductInformation

Enzymatic Assay of L-LACTIC DEHYDROGENASE¹ (EC 1.1.1.27)

PRINCIPLE:

Abbreviations used:

 β -NADH = β -Nicotinamide Adenine Dinucleotide, Reduced Form β -NAD = β -Nicotinamide Adenine Dinucleotide, Oxidized Form

CONDITIONS: $T = 37^{\circ}C$, pH = 7.5, A_{340nm} , Light path = 1 cm

METHOD: Continuous Spectrophotometric Rate Determination

REAGENTS:

- A. 100 mM Sodium Phosphate Buffer, pH 7.5 at 37°C (Prepare 200 ml in deionized water using Sodium Phosphate, Monobasic, Anhydrous, Sigma Prod. No. S-0751. Adjust to pH 7.5 at 37°C with 1 M NaOH.)
- B. 0.13 mM β-Nicotinamide Adenine Dinucleotide, Reduced Form Solution (β-NADH) (Prepare 10 ml in cold Reagent A using β-Nicotinamide Adenine Dinucleotide, Reduced Form, Disodium Salt, Sigma Prod. No. N-8129 or dissolve the contents of 1 mg vial of β-Nicotinamide Adenine Dinucleotide, Reduced Form, Disodium Salt, Sigma Stock No. 340-101, in the appropriate volume of Reagent A. **PREPARE FRESH**.)
- C. 69 mM Sodium Pyruvate Solution (Pyruvate)
 (Prepare 1.0 ml in cold Reagent A using Pyruvic Acid, Sodium Salt, Sigma Prod. No. P-2256.)
- D. 1.0% (w/v) Bovine Serum Albumin Solution (BSA)
 (Prepare 50 ml in Reagent A using Albumin, Bovine, Sigma Prod. No. A-4503. PREPARE FRESH.)
- E. L-Lactic Dehydrogenase Enzyme Solution (Immediately before use, prepare a solution containing 0.25 0.75 unit/ml of L-Lactic Dehydrogenase in cold Reagent D.)

SPPYRU02 Revised: 05/04/98 Page 1 of 3

Enzymatic Assay of L-LACTIC DEHYDROGENASE¹ (EC 1.1.1.27)

PROCEDURE:

Pipette (in milliliters) the following reagents into suitable cuvettes:

	<u>l est</u>	Blank
Reagent B (β-NADH)	2.80	2.80
Reagent C (Pyruvate)	0.10	0.10

Mix by inversion and equilibrate to $37^{\circ}C$. Monitor the A_{340nm} until constant, using a suitably thermostatted spectrophotometer. Then add:

Reagent D (BSA)		0.10
Reagent E (Enzyme Solution)	0.10	

Immediately mix by inversion and record the decrease in A_{340nm} for approximately 5 minutes. Obtain the ΔA_{340nm} /minute using the maximum linear rate for both the Test and Blank.

CALCULATIONS:

Units/ml enzyme =
$$\frac{(\Delta A_{340nm}/min \text{ Test - } \Delta A_{340nm}/min \text{ Blank})(3)(df)}{(6.22)(0.1)}$$

3 = Total volume (in milliliters) of assay

df = Dilution factor

6.22 = Millimolar extinction coefficient of β -NADH at 340 nm

0.1 = Volume (in milliliter) of enzyme used

SPPYRU02 Page 2 of 3 Revised: 05/04/98

Enzymatic Assay of L-LACTIC DEHYDROGENASE¹ (EC 1.1.1.27)

UNIT DEFINITION:

One unit will reduce 1.0 µmole of pyruvate to L-lactate per minute at pH 7.5 at 37°C.

FINAL ASSAY CONCENTRATION:

In a 3.00 ml reaction mix, the final concentrations are 100 mM sodium phosphate, 0.12 mM β -nicotinamide adenine dinucleotide, reduced form, 2.3 mM pyruvate, 0.033% (w/v) bovine serum albumin and 0.025 - 0.075 unit L-lactic dehydrogenase.

REFERENCES:

Bergmeyer, H.U. and Bernt, E. (1974) in *Methods of Enzymatic Analysis*, (Bergmeyer, H.U. ed.) Volume 2, 574-578, Academic Press, New York, NY

NOTES:

- This assay is suitable for the following L-Lactic Dehydrogenases, Sigma Prod. Nos.: L-2375, L-2500, L-5132, L-1378, L-1254, L-3379, L-0755, L-3632, L-3757, L-3882, L-9757, L-4387, L-0883, L-2518, L-6504, L-6383, L-5008, L-9887, L-0508, L-6508, and L5762.
- 2. This assay is based on the cited reference.
- 3. Where Sigma Product or Stock numbers are specified, equivalent reagents may be substituted.

Sigma warrants that the above procedure information is currently utilized at Sigma and that Sigma products conform to the information in Sigma publications. Purchaser must determine the suitability of the information and products for its particular use. Upon purchase of Sigma products, see reverse side of invoice or packing slip for additional terms and conditions of sale.

SPPYRU02 Page 3 of 3

Revised: 05/04/98