

Product Information

Ganciclovir


Catalog Number **G2536**

Storage Temperature 2-8 °C

CAS RN: 82410-32-0

Synonyms: 9-(1,3-Dihydroxy-2-propoxymethyl)guanine; 2'-Nor-2'-deoxyguanosine; 2'-NDG; BIOLF-62; DHPG; BW-759U

Product Description



Molecular formula: C₉H₁₃N₅O₄

Molecular weight: 255.23

Ganciclovir, a nucleoside analog, can be enzymatically phosphorylated to an active triphosphate analog by herpes simplex virus thymidine kinase (HSV-TK). The phosphorylated product causes inhibition of viral DNA polymerase. Ganciclovir has also been used to study sensitivity of different viruses to antiviral treatment.^{1,2}

This enzyme-prodrug reaction is being used to study gene therapy in cancer research.^{3,4} Expression of a suicide gene encoding a viral enzyme such as TK results in the phosphorylation of the non-toxic prodrug, ganciclovir. The active, phosphorylated analog is incorporated into the DNA of replicating bystander eukaryotic cells causing death of the malignant dividing cells.⁵

Ganciclovir was found to be more cytotoxic than other HSV-TK substrates, acyclovir and araT (1-β-D- arabinofuranosylthymine).⁶ The mechanism presumably proceeds via irreversible cell cycle arrest at the G2-M checkpoint.⁷ The involvement of gap junctions with the bystander effect observed with the HSV-TK gene and ganciclovir was reported.⁸

The HSV-TK gene and ganciclovir are used in molecular biology for negative selection against random recombination events when homologous recombination of a gene of interest is required.⁹ Negative selection with the HSV-TK gene and ganciclovir was recently used for measuring loss of telomeres in the study of chromosome healing.¹⁰ Recently it has been widely used as a potent treatment against Cytomegalovirus infection following tissue transplantation.^{11,12}

Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

Preparation Instructions

Soluble at 10 mg/ml in 0.1 N HCl.

Storage/Stability

Store desiccated at 2-8 °C. Under these conditions the product is stable for 3 years.

References

1. Oon, C.J., et al., Hepatitis B virus variants with lamivudine-related mutations in the DNA polymerase and the 'a' epitope of the surface antigen are sensitive to ganciclovir., *Antiviral Res.*, **41**, 113-8 (1999).
2. Cannon, J.S., et al., Human herpes virus 8-encoded thymidine kinase and phosphotransferase homologues confer sensitivity to ganciclovir., *J. Virol.*, **73**, 4786-93 (1999).
3. Maatta, A.M., et al., Non-small cell lung cancer as a target disease for herpes simplex type 1 thymidine kinase-ganciclovir gene therapy., *Int J. Oncol.*, **24**, 943-9 (2004).
4. Wang, J., et al., Herpes simplex virus thymidine kinase and ganciclovir suicide gene therapy for human pancreatic cancer., *World J. Gastroenterol.*, **10**, 400-3 (2004).

5. Rubsam, L.Z., et al., Cytotoxicity and accumulation of ganciclovir triphosphate in bystander cells cocultured with herpes simplex virus type 1 thymidine kinase-expressing human glioblastoma cells., *Cancer Res.*, **59**, 669-75 (1999).
6. Rubsam, L.Z., et al., Superior cytotoxicity with ganciclovir compared with acyclovir and 1- β -D-arabinofuranosylthymine in herpes simplex virus-thymidine kinase-expressing cells: a novel paradigm for cell killing., *Cancer Res.*, **58**, 3873-82 (1998).
7. Halloran, P.J., and Fenton, R.G., Irreversible G2-M arrest and cytoskeletal reorganization induced by cytotoxic nucleoside analogues., *Cancer Res.*, **58**, 3855-65 (1998).
8. Yamasaki, H., et al., Role of connexin (gap junction) genes in cell growth control and carcinogenesis., *C. R. Acad. Sci. III*, **322**, 151-9 (1999).
9. Introduction of DNA into Mammalian Cells, in *Current Protocols in Molecular Biology*, Ausubel, F.M., et al., Eds., John Wiley & Sons, Inc. (New York, NY: 1999), Volume I, Supplement 45, 9.15.1-9.15.10.
10. Sprung, C.N., et al., Chromosome healing in mouse embryonic stem cells., *Proc. Natl. Acad. Sci. USA*, **96**, 6781-6 (1999).
11. Said, T., et al., Cytomegalovirus prophylaxis with ganciclovir in kidney transplant recipients receiving induction antilymphocyte antibodies., *Transplant Proc.*, **36**, 1847-9 (2004).
12. Zamora, M.R., et al., Following universal prophylaxis with intravenous ganciclovir and cytomegalovirus immune globulin, valganciclovir is safe and effective for prevention of CMV infection following lung transplantation., *Am. J. Transplant.*, **4**, 1635-42 (2004).

NDH,PHC 11/10-1

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.