

## Product Information

### 1,2-PROPANEDIOL

Product Number **P1009**

**CAS NUMBER:** 57-55-6

**SYNONYMS:** propylene glycol; methyl glycol; 1,2-dihydroxypropane

#### PHYSICAL DESCRIPTION:

Structure: dl-form

Appearance: clear colorless viscous liquid

Molecular formula:  $C_3H_8O_2$

Molecular weight: 76.10

Melting point:  $-59$  to  $-60^\circ C^{1,4}$

Boiling point: at 760 torr,  $188^\circ C^{1,4}$  ( $186-189^\circ C^2$ ) at 10 torr,  $83.2^\circ C^1$


Vapor pressure at  $25^\circ C = 0.02$  kPa ( $0.15$  torr)<sup>4</sup>

Density:  $1.0351-1.0364$  g/mL at  $25^\circ C^2$

Effective molarity of pure liquid: 13.1 M

Refractive index: 1.432 at  $20^\circ C^3$

Viscosity at  $25^\circ C = 40.4$  mPa·s<sup>5</sup>



#### STORAGE / STABILITY AS SUPPLIED:

The product is stable at room temperature for years<sup>6</sup>, but at high temperatures it tends to oxidize.<sup>1</sup> Containers should be kept sealed since the product is hygroscopic.

#### SOLUBILITY / STABILITY OF SOLUTIONS:

1,2-Propanediol is completely miscible with water, acetone and chloroform. It is soluble in ether. It is an excellent solvent, but is immiscible with fixed oils. A 2% solution is iso-osmotic with serum.<sup>7</sup>

Solutions are stable indefinitely at room temperature, although are incompatible with some oxidizing agents. Solutions may be sterilized by filtration.<sup>7</sup>

#### GENERAL REMARKS:

P1009 is reagent grade. P6209 meets ACS specification shown in Sigma Catalog and 8th edition of the ACS Reagents.

1,2-Propanediol, more commonly called propylene glycol, has been widely used in pharmaceutical manufacturing as a solvent and vehicle especially for drugs unstable or insoluble in water. It may also be used as a stabilizing agent, plasticizer and as a preservative.

**1,2-PROPANEDIOL**  
**Sigma Prod. Nos. P1009 and P6209**

**GENERAL REMARKS:** (continued)

U.S.P. Propylene glycol has been used extensively in foods and cosmetics, partly as a solvent, but more as a humectant and also for its preservative properties.<sup>8</sup> It has some antimicrobial value, based on the reduction in water activity. *Staphylococcus aureus* grew more slowly to lower maximum populations in the presence of propylene glycol at concentrations permitted in foods.<sup>9</sup>

Another major use is as an industrial antifreeze, substituting for ethylene glycol and glycerol.<sup>1,10</sup> The use of ethylene glycol as an automotive antifreeze poses a hazard for children and household pets (oral LD<sub>50</sub> for rats = 4.7 g/kg<sup>11</sup>) due to its sweet taste. Propylene glycol is considerably less toxic (oral LD<sub>50</sub> for rats = 20 g/kg<sup>11</sup>) and is being offered commercially as a safer alternative.<sup>10</sup>

**REFERENCES:**

1. *Merck Index*, 12th Ed., #8040 (1996).
2. Supplier data.
3. *Handbook of Chemistry and Physics*, 74th Ed., (CRC Press, 1993-94), p. 3-427.
4. *Ibid.*, p. 15.48
5. *Ibid.*, p. 6-137.
6. Sigma quality control.
7. *Martindale: The Extra Pharmacopoeia*, 28th Ed. (Pharmaceutical Press, 1982), ed. Reynolds, J., p. 708-709.
8. *Martindale: The Extra Pharmacopoeia*, 30th Ed. (Pharmaceutical Press, 1993), ed. Reynolds, J., p. 1406.
9. *Disinfection, Sterilization and Preservation*, 4th Ed., ed., Block, S. (Lea & Febiger, 1991), p. 823-4.
10. Goldfarb, B., *Chem Matters*, 14(3), 4-8 (1996). "Antifreeze Antidote."
11. Sigma Material Safety Data Sheet.

**Sigma warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.**