

Product Information

Anti-Guinea Pig IgG (whole molecule) FITC

produced in rabbit, affinity isolated antibody

Catalog Number **F7762**

Product Description

Antiserum is produced in rabbit using purified guinea pig IgG as the immunogen. Antibody is isolated from rabbit anti-guinea pig IgG antiserum by immunospecific purification that removes essentially all rabbit serum proteins, including immunoglobulins, which do not specifically bind to guinea pig IgG. Anti-Guinea Pig IgG is conjugated to fluorescein isothiocyanate (FITC). Free FITC is removed by gel filtration.

Specificity of the anti-guinea pig IgG antibodies for guinea pig IgG is determined by immunoelectrophoresis (IEP), prior to conjugation, using normal guinea pig serum and guinea pig IgG.

Identity and purity of the antibody is established by immunoelectrophoresis, prior to conjugation. Electrophoresis of the antibody preparation followed by diffusion versus anti-rabbit IgG and anti-rabbit whole serum results in single arcs of precipitation.

Reagent

The conjugate is provided as a solution in 0.01 M phosphate buffered saline, pH 7.4, containing 15 mM sodium azide.

Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

Storage

For continuous use, store at 2-8 °C for up to one month. For extended storage, the solution may be frozen in working aliquots. Repeated freezing and thawing, or storage in "frost-free" freezers, is not recommended. If slight turbidity occurs upon prolonged storage, clarify the solution by centrifugation before use.

Note: Store product protected from light.

Product Profile

Direct immunofluorescence: a minimum working dilution of 1:64 was determined using guinea pig spleen cells.

Immunohistochemistry: a minimum working dilution of 1:320 was determined using formalin-fixed, paraffin-embedded human pancreas sections and Anti-Insulin, Catalog Number I8510, as the primary antibody.

Note: In order to obtain the best results, it is recommended that each individual user determine the optimum working dilution for their system by titration assay.

Protein Concentration: 2.0-5.5 mg/ml by absorbance at 280 nm and 495 nm ($E_{280}^{1\%} = 14.0$).

F/P Molar Ratio: 3.0 to 8.0

The F/P Molar ratio of FITC-Antibody conjugates is determined spectrophotometrically as follows:

$$\frac{F}{P} = \frac{A_{495} \times 1.4 \times 0.41}{0.2 \times [A_{280} - (0.36 \times A_{495})]}$$

Where:

- 0.2 = The extinction coefficient of bound FITC at a concentration of 1 µg/ml at pH 7.2.
- 0.36 = The fluorochrome absorbance correction factor (non-protein absorbance).
- 0.41 = The factor for conversion of fluorochrome to protein ratios from weight to molar ratios.

NRC,KAA,PHC 09/08-1