3050 Spruce Street, St. Louis, MO 63103 USA Tel: (800) 521-8956 (314) 771-5765 Fax: (800) 325-5052 (314) 771-5757 email: techservice@sial.com sigma-aldrich.com

# **Product Information**

## Nidogen-1 (NID1) human

recombinant, expressed in HEK 293 cells cell culture tested

Product Number **D8935** Storage Temperature –20 °C

CAS RN 90170-80-2

Synonyms: NID, NID1, NID-1, Entactin

## **Product Description**

Recombinant human nidogen-1 is expressed in human HEK 293 cells as a glycoprotein with a calculated molecular mass of 133.5 kDa (amino acids 29-1247). This protein is manufactured in human cells, with no serum. The expression system of the human cells allows human-like glycosylation and folding, and often supports higher specific activity of the protein. The protein is produced with no artificial tags.

Nidogen-1 belongs to the nidogens family of glycoproteins. This family consists of nidogen-1 and nidogen-2, both of which are sulfated monomeric glycoproteins. Nidogen-1 is ubiquitously present in the synaptic and extra-synaptic basal lamina. 2 Nidogen-1 is thought to have an important role in the construction of basement membranes by linking between the networks of laminin and collagen IV.3 Genetic elimination of the nidogen-1 binding site on the mouse laminin γ1 chain leads to impaired deposition of basement membranes in embryoid bodies.4 Nidogen 1 and 2 double knockout in mouse fibroblasts led to the loss of all major basal membrane components from the epidermal-collagen interface, and complete abolishment of hemidesmosomes. Supplementation by either recombinant nidogen-1 or -2 compensated for these defects and promoted basal membrane formation.5

This recombinant human nidogen-1 product can be used as an attachment factor for cell adherence.

This product is supplied as a powder lyophilized from 0.22  $\mu$ m filtered solution of PBS.

The biological activity of recombinant human nidogen-1 was tested in culture by measuring the ability of immobilized nidogen-1 to support adhesion of SVEC4-10 mouse vascular endothelial cells.

Endotoxin: ≤1.00 EU/μg (LAL)

Uniprot: P14543

#### **Precautions and Disclaimer**

For R&D use only. Not for drug, household, or other uses. Please consult the Safety Data Sheet for information regarding hazards and safe handling practices.

## **Preparation Instructions**

Briefly centrifuge the vial before opening. Reconstitute in water to a concentration of 0.1 mg/mL. Do not vortex. This solution can be stored at 2–8 °C for up to 1 week. For extended storage, it is recommended to store in working aliquots at –20 °C.

### Storage/Stability

Store the lyophilized product at –20 °C. The product is stable for at least 2 years as supplied.

#### References

- Hortsch, M., and Umemori, H., The Sticky Synapse: Cell Adhesion Molecules and Their Role in Synapse Formation and Maintenance. New York, NY: Springer. p. 66 (2009).
- Fox, M.A. et al., A synaptic nidogen: developmental regulation and role of nidogen-2 at the neuromuscular junction. *Neural Dev.* 3(24), (2008).
- 3. Timpl, R., and Brown, J.C., Supramolecular assembly of basement membranes. *Bioessays*, **18**, 123–132 (1996).
- 4. Mayer, U. et al., Structural and genetic analysis of the laminin–nidogen interaction. *Ann. N.Y. Acad. Sci.*, **857**, 130–142 (1998).
- Nischt, R. et al., Lack of Nidogen-1 and -2 Prevents Basement Membrane Assembly in Skin-Organotypic Coculture. *J. Invest. Dermatol.*, 127(3), 545-554 (2007)

PG,NA,MAM 03/19-1

Purity: ≥95.0% (SDS-PAGE)