

## Product Information

**IKK $\alpha$ , active, GST tagged, human  
PRECISIO® Kinase  
recombinant, expressed in Sf9 cells**

Catalog Number **SRP5040**  
Storage Temperature  $-70\text{ }^{\circ}\text{C}$

Synonyms: CHUK, IKK1, IKBKA, TCF16, NFKBKA,  
IKK-alpha

### Product Description

IKK $\alpha$  is a serine/threonine protein kinase that phosphorylates the I $\kappa$ B protein, which is an inhibitor of the transcription factor NF $\kappa$ B complex. Phosphorylation of I $\kappa$ B protein triggers the degradation of the inhibitor via the ubiquitination pathway, thereby, activating NF $\kappa$ B complex.<sup>1</sup> IKK $\alpha$  is an essential regulator of NF $\kappa$ B-dependent gene expression through control of promoter-associated histone phosphorylation after cytokine exposure.<sup>2</sup> IKK $\alpha$  is a critical component of the cytoplasmic transductional-transcriptional processor leading to induction of IFN $\alpha$  production. IKK $\alpha$  is also involved in the epidermis where it antagonizes mitogenic and angiogenic signals, and represses tumor progression and metastases.

Recombinant, full-length, human IKK $\alpha$  was expressed by baculovirus in Sf9 insect cells using an N-terminal GST tag. The gene accession number is BC092514. Recombinant protein stored in 50 mM Tris-HCl, pH 7.5, 150 mM NaCl, 10 mM glutathione, 0.1 mM EDTA, 0.25 mM DTT, 0.1 mM PMSF, and 25% glycerol.

Molecular mass: ~114 kDa

Purity: 70–95% (SDS-PAGE, see Figure 1)

Specific Activity: 2.1–2.9 nmole/min/mg (see Figure 2)


### Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.


### Storage/Stability

The product ships on dry ice and storage at  $-70\text{ }^{\circ}\text{C}$  is recommended. After opening, aliquot into smaller quantities and store at  $-70\text{ }^{\circ}\text{C}$ . Avoid repeated handling and multiple freeze/thaw cycles.

**Figure 1.**  
SDS-PAGE Gel of Typical Lot  
70–95% (densitometry)



**Figure 2.**  
Specific Activity of Typical Lot  
2.1–2.9 nmole/min/mg



### Procedure

#### Preparation Instructions

Kinase Assay Buffer – 25 mM MOPS, pH 7.2, 12.5 mM glycerol 2-phosphate, 25 mM MgCl<sub>2</sub>, 5 mM EGTA, and 2 mM EDTA. Just prior to use, add DTT to a final concentration of 0.25 mM.

Kinase Dilution Buffer – Dilute the Kinase Assay Buffer 5-fold with a 50 ng/μl BSA.

Kinase Solution – Dilute the active IKK $\alpha$  (0.1  $\mu\text{g}/\mu\text{l}$ ) with Kinase Dilution Buffer to the desired concentration.

**Note:** The specific activity plot may be used as a guideline (see Figure 2). It is recommended the researcher perform a serial dilution of active IKK $\alpha$  kinase for optimal results.

10 mM ATP Stock Solution – Dissolve 55 mg of ATP in 10 ml of Kinase Assay Buffer. Store in 200  $\mu\text{l}$  aliquots at  $-20\text{ }^{\circ}\text{C}$ .

$\gamma$ - $^{33}\text{P}$ -ATP Assay Cocktail (250  $\mu\text{M}$ ) – Combine 5.75 ml of Kinase Assay Buffer, 150  $\mu\text{l}$  of 10 mM ATP Stock Solution, 100  $\mu\text{l}$  of  $\gamma$ - $^{33}\text{P}$ -ATP (1 mCi/100  $\mu\text{l}$ ). Store in 1 ml aliquots at  $-20\text{ }^{\circ}\text{C}$ .

Substrate Solution – Dissolve the synthetic peptide substrate in distilled water at a final concentration of 1 mg/ml.

1% phosphoric acid solution – Dilute 10 ml of concentrated phosphoric acid to a final volume of 1 L with water.

#### Kinase Assay

This assay involves the use of the  $^{33}\text{P}$  radioisotope. All institutional guidelines regarding the use of radioisotopes should be followed.

1. Thaw the active IKK $\alpha$ , Kinase Assay Buffer, Substrate Solution, and Kinase Dilution Buffer on ice. The  $\gamma$ - $^{33}\text{P}$ -ATP Assay Cocktail may be thawed at room temperature.
2. In a pre-cooled microcentrifuge tube, add the following solutions to a volume of 20  $\mu\text{l}$ :
  - 10  $\mu\text{l}$  of Kinase Solution
  - 5  $\mu\text{l}$  of Substrate Solution
  - 5  $\mu\text{l}$  of cold water (4  $^{\circ}\text{C}$ )
3. Set up a blank control as outlined in step 2, substituting 5  $\mu\text{l}$  of cold water (4  $^{\circ}\text{C}$ ) for the Substrate Solution.
4. Initiate each reaction with the addition of 5  $\mu\text{l}$  of the  $\gamma$ - $^{33}\text{P}$ -ATP Assay Cocktail, bringing the final reaction volume to 25  $\mu\text{l}$ . Incubate the mixture in a water bath at 30  $^{\circ}\text{C}$  for 15 minutes.
5. After the 15 minute incubation, stop the reaction by spotting 20  $\mu\text{l}$  of the reaction mixture onto an individually pre-cut strip of phosphocellulose P81 paper.

6. Air dry the pre-cut P81 strip and sequentially wash in the 1% phosphoric acid solution with constant gentle stirring. It is recommended the strips be washed a total of 3 times of  $\sim 10$  minutes each.
7. Set up a radioactive control to measure the total  $\gamma$ - $^{33}\text{P}$ -ATP counts introduced into the reaction. Spot 5  $\mu\text{l}$  of the  $\gamma$ - $^{33}\text{P}$ -ATP Assay Cocktail on a pre-cut P81 strip. Dry the sample for 2 minutes and read the counts. Do not wash this sample.
8. Count the radioactivity on the P81 paper in the presence of scintillation fluid in a scintillation counter.
9. Determine the corrected cpm by subtracting the blank control value (see step 3) from each sample and calculate the kinase specific activity

#### Calculations:

1. Specific Radioactivity (SR) of ATP (cpm/nmole)

$$\text{SR} = \frac{\text{cpm of } 5 \mu\text{l of } \gamma\text{-}^{33}\text{P}\text{-ATP Assay Cocktail}}{\text{nmole of ATP}}$$

cpm – value from control (step 7)

nmole – 1.25 nmole (5  $\mu\text{l}$  of 250  $\mu\text{M}$  ATP Assay Cocktail)

2. Specific Kinase Activity (SA) (nmole/min/mg)

$$\text{nmole/min/mg} = \frac{\Delta\text{cpm} \times (25/20)}{\text{SR} \times \text{E} \times \text{T}}$$

SR = specific radioactivity of the ATP (cpm/nmole ATP)

$\Delta\text{cpm}$  = cpm of the sample – cpm of the blank (step 3)

25 = total reaction volume

20 = spot volume

T = reaction time (minutes)

E = amount of enzyme (mg)

#### **References**

1. Anest, V. et al., A nucleosomal function for I-kappa-B kinase-alpha in NF-kappa-B-dependent gene expression. *Nature*, **423**, 659-663 (2003).
2. Hoshino, K. et al., I-kappa-B kinase-alpha is critical for interferon-alpha production induced by Toll-like receptors 7 and 9. *Nature*, **440**, 949-953 (2006).

PRECISIO is a registered trademark of Sigma-Aldrich Co. LLC.

TD,MAM 10/11-1