



CONTROL RANGES

MILLIPLEX® MAP Rat Kidney Toxicity Magnetic Bead Panel 1
Catalog # RKTX1MAG-37K
Control Catalog # RKTXMG1-6037-1
Lot: RKTX1-112 and RKTX1-212

<u>Analyte</u>	<u>QC Level</u>	<u>Expected Range</u>	<u>Units</u>
Clusterin	Control I	47 – 98	ng/mL
	Control II	242 – 502	ng/mL
GST α	Control I	34 – 70	ng/mL
	Control II	364 – 756	ng/mL
IP-10	Control I	0.58 – 1.2	ng/mL
	Control II	2.4 – 5.1	ng/mL
KIM-1	Control I	0.52 – 1.1	ng/mL
	Control II	2.8 – 5.8	ng/mL
OPN	Control I	0.51 – 1.1	ng/mL
	Control II	2.8 – 5.7	ng/mL
TIMP-1	Control I	6.1 – 13	ng/mL
	Control II	30 – 63	ng/mL
VEGF	Control I	0.55 – 1.1	ng/mL
	Control II	2.9 – 5.9	ng/mL

Note: The Quality Control Ranges are generated with using serum matrix provided in the kit. Quality Control values in culture media are not tested.

RKTXMG1-6037-1: RKTX1-112.212 (04 December 2023)

EMD Millipore • 1-800-645-5476 • 1-800-645-5439 (FAX) • emdmillipore.com

The M logo is a trademark of Merck KGaA, Darmstadt, Germany.

© 2013 EMD Millipore Corporation, Billerica, MA 01821 USA