

Technical Bulletin

Sephadex® G-50

BioReagent, for molecular biology, DNA grade

S5897

Product Description

Sephadex® G-50, Fine is a gel filtration chromatography product for desalting and buffer exchange of very large molecules. Sephadex® is prepared by crosslinking dextran with epichlorohydrin. Sephadex® products differ in their degree of crosslinking, and thus in their degree of swelling and their molecular fractionation range. On the general term "Sephadex" and other aspects of Sephadex® products:

- "Se" refers to "separation", and "dex" to dextran.¹
- "G" refers to "Gel".¹
- The G-number in a given Sephadex® listing refers to the water regain of the gel multiplied by 10, where water regain is defined as the maximum amount of grams of water taken up by 1 g of "dry xerogel".¹

The designation "Fine" indicates a smaller particle size which allows for shorter diffusion distances, highly efficient separations at high flow rates, and minimal non-specific binding, for use in routine laboratory work, such as small-scale preparative separations.

Several publications have cited use of this product in their research protocols.²⁻³

Product Summary

Bed volume⁴: 9-11 mL/g dry Sephadex®

DNA exclusion limit⁴: 20 bp

Oligonucleotide exclusion limit⁴: 20 bp

Recommended pH range: 2-10

Swelling time:

- 72 hours at 20 °C
- 5 hours at 90 °C

DNase and RNase: None detected

Storage/Stability

Store this product, as sold in lyophilized form, at room temperature.

Details on nuclease testing

The following nuclease tests use supernatant that has been isolated after centrifuging a resuspension of the Sephadex® beads in water at 91 mg beads per 1 mL of water, with overnight incubation at 2-8 °C. Small aliquots of the Sephadex® supernatant are used for the assays. In the course of the nuclease tests, degradation of DNA or RNA was not detected.

Endonuclease-Exonuclease

One µg of λ Hind III fragments was incubated in an aliquot of the Sephadex® supernatant for 16-18 hours at 37 °C, in a 50 µL reaction mixture containing 30 mM Trizma®-HCl (pH 7.8), 50 mM NaCl and 10 mM MgCl₂. No degradation of the DNA fragments was detected by agarose gel electrophoresis.

Endonuclease (Nickase)

One µg of pBR322 DNA was incubated in an aliquot of the Sephadex® supernatant for 16-18 hours at 37 °C, in a 50 µL reaction mixture containing 30 mM Trizma®-HCl (pH 7.8), 50 mM NaCl and 10 mM MgCl₂. No conversion of the covalently closed circular DNA to the nicked or linear form was observed by agarose gel electrophoresis.

RNase

Two µg of transfer RNA were incubated in an aliquot of the Sephadex® supernatant for 16-18 hours at 37 °C, in a 50 µL reaction mixture containing 30 mM Trizma®-HCl (pH 7.8), 50 mM NaCl and 10 mM MgCl₂. No degradation of the tRNA was detected by polyacrylamide gel electrophoresis.

Precautions and Disclaimer

For Research use only. Not for drug, household, or other uses. Please consult the Safety Data Sheet for information regarding hazards and safe handling practices.

References

1. Janson, J.-C., *Chromatographia*, **23(5)**, 361-369 (1987).
2. Cortinas, M.-N. *et al.*, *Mycol. Res.*, **110(Pt 2)**, 229-236 (2006).
3. Lippa, G.M. *et al.*, *Methods Mol. Biol.*, **848**, 159-184 (2012).
4. Supplier information.

Notice

We provide information and advice to our customers on application technologies and regulatory matters to the best of our knowledge and ability, but without obligation or liability. Existing laws and regulations are to be observed in all cases by our customers. This also applies in respect to any rights of third parties. Our information and advice do not relieve our customers of their own responsibility for checking the suitability of our products for the envisaged purpose.

The information in this document is subject to change without notice and should not be construed as a commitment by the manufacturing or selling entity, or an affiliate. We assume no responsibility for any errors that may appear in this document.

Technical Assistance

Visit the tech service page at SigmaAldrich.com/techservice.

Standard Warranty

The applicable warranty for the products listed in this publication may be found at SigmaAldrich.com/terms.

Contact Information

For the location of the office nearest you, go to SigmaAldrich.com/offices.

The life science business of Merck KGaA, Darmstadt, Germany operates as MilliporeSigma in the U.S. and Canada.

MilliporeSigma, and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. All other trademarks are the property of their respective owners. Detailed information on trademarks is available via publicly accessible resources.
© 2021 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved.