



Product Information

SIGMA QUALITY CONTROL TEST PROCEDURE Enzymatic Assay of PROTEIN KINASE C

PRINCIPLE:

Histone + γ ³²P-ATP $\xrightarrow{\text{Protein Kinase}}$ [³²P]-Phosphorylated Histone + ADP

Abbreviations used:

γ ³²P-ATP = Adenosine 5'-Triphosphate γ ³²P-labelled

ADP = Adenosine 5'-Diphosphate

CONDITIONS: T = 30°C, pH = 7.4

METHOD: Radiolabelled Stop Reaction

REAGENTS:

- A. 1 M Tris HCl Buffer, pH 7.4 at 25°C
(Prepare 100 ml in deionized water using Trizma Base, Sigma Prod. No. T-1503. Adjust to pH 7.4 at 25°C with 1 M HCl. Store at 4°C.)
- B. 4.9 M Magnesium Chloride Solution (MgCl₂)
(Use Magnesium Chloride, 4.9 M Solution, Sigma Stock No. 104-20.)
- C. 100 mM Ethylene Glycol-bis(β-Aminoethyl Ether)N,N,N',N'-Tetraacetic Acid Solution, pH 7.4 at 25°C (EGTA)
(Prepare 50 ml in Reagent A using Ethylene Glycol-bis (β-Aminoethyl Ether)N,N,N',N'-Tetraacetic Acid, Sigma Prod. No. E-4378. Adjust to pH 7.4 at 25°C with 1 M NaOH. Store at 4°C.)
- D. 500 mM Calcium Chloride Solution (CaCl₂)
(Prepare 50 ml in deionized water using Calcium Chloride, Dihydrate, Sigma Prod. No. C-3881. Store at 4°C.)
- E. 0.5 mM Adenosine 5'-Triphosphate Solution, pH 7.0 at 30°C
(Prepare 10 ml in deionized water using Adenosine 5'-Triphosphate, Disodium Salt, Sigma Prod. No. A-2383. Adjust to pH 7.0 at 30°C with either 1 M HCl or 1 M NaOH. Confirm the concentration by using a molar extinction coefficient¹ of 15,400 measured at 259 mμ. Store at -20°C.)
- F. 0.1% (w/v) Triton X-100 Solution (X-100)
(Prepare 10 ml in deionized water using Triton X-100, Sigma Stock No. X-100.)

Enzymatic Assay of PROTEIN KINASE C

REAGENTS: (continued)

- G. 1 mg/ml Histone Type III-S Solution (Histone)²
(Prepare 1 ml in deionized water using Histone, Type III-S, Sigma Prod. No. H-5505. The histone used should have a lysine and arginine content greater than or equal to 25.8% and 2.2%, respectively. **PREPARE FRESH.**)
- H. 250 mM Tris HCl Buffer with 100 mM Magnesium Chloride and 10 mM Ethylene Glycol-bis (β -Aminoethyl Ether)N,N,N',N'-Tetraacetic Acid, pH 7.4 at 30°C (Buffer I)
(Prepare 100 ml using Reagents A, B, and C.)
- I. 250 mM Tris HCl Buffer with 100 mM Magnesium Chloride and 5 mM Calcium Chloride, pH 7.4 at 30°C (Buffer II)
(Prepare 100 ml using Reagents A, B, and D.)
- J. 50 mM Tris HCl Buffer with 5 mM DL-Dithiothreitol, pH 7.4 at 30°C (Enz Dil)
(Prepare 25 ml in deionized water using Reagent A and DL-Dithiothreitol, Sigma Prod. No. D-0632.)
- K. 2 mg/ml Phosphatidylserine Solution (PS)
(Use L- α -Phosphatidyl-L-Serine, Chloroform:Methanol (95:5) Solution, Sigma Prod. No. P-6641.)
- L. Chloroform Solution
(Use Chloroform, Sigma Stock No. 27,063-6.)
- M. 0.5 mg/ml 1,2-Dioleoyl-rac-Glycerol Solution (DAG)
(Prepare 4 ml in Reagent L using 1,2-Dioleoyl-rac-Glycerol (C18:1,[cis]-9), Sigma Prod. No. D-3537. Store under nitrogen in a brown bottle.)
- N. Lipid Activator Solution (Lipids)
(Immediately before use, prepare by pipetting 0.25 ml of Reagent K and 40 μ l of Reagent M into a suitable container. Close the container immediately while sealing it under nitrogen. Dry the lipid solution under nitrogen while rotating the container gently. Then add 0.5 ml of Reagent F to the dried lipids. Sonicate in a cold bath sonicator for 1 minute. The solution will become cloudy.)
- O. γ -³²P-Adenosine 5'-Triphosphate Solution (γ -³²P-ATP)
(Use γ -³²P-Adenosine 5'-Triphosphate, 3000 Ci/mmmole, 10 mCi/ml.)
- P. ATP Reaction Mix (ATP)
(Immediately before use, prepare by adding 1 μ l of Reagent O to 100 μ l of Reagent E for each of the 9 wells.)
- Q. Protein Kinase C Enzyme Solution
(Immediately before use, prepare a solution containing 3.3 - 5.0 units/ml of Protein Kinase C in cold Reagent J.)

Enzymatic Assay of PROTEIN KINASE C

REAGENTS: (continued)

- R. Scintillation Fluid (Scin Fluid)
(Use Sigma-Fluor Universal LSC Cocktail for Aqueous Samples, Sigma Prod. No. S-4273.)
- S. 10% (v/v) Trichloroacetic Acid Solution (TCA)
(Prepare 1 liter in deionized water using Trichloroacetic Acid, 6.1 N Solution, approximately 100% (w/v), Sigma Stock No. 490-10.)
- T. Nitrocellulose Paper
(Use BA-85 Cellulose Nitrate, Ref. 401-491, Schleicher and Schuell.)

PROCEDURE:

This assay is performed in triplicate in a final volume of 0.05 ml. Each sample is assayed with and without activators. The assay components are added as 0.01 ml aliquots and the last component added is the enzyme solution. The reaction is conducted in a 96 well microtiter plate. A second microtiter plate is used to contain the enzyme solution prior to pipetting with a multichannel pipette.

Plan the assay on a 8 x 12 chart (as indicated) since a 12 row microtiter plate will be used. The first microtiter plate is set up for assaying samples, I-IV, 3 replications each, with (+) and without (-) activators. The second microtiter plate is for the Protein Kinase C samples.

Plate No. 1

	1	2	3	4	5	6	7	8	9	10	11	12
A -	I	I	I	II	II	II	III	III	III	IV	IV	IV
B +	I	I	I	II	II	II	III	III	III	IV	IV	IV

Plate No. 2

	1	2	3	4	5	6	7	8	9	10	11	12
A	I 30 µl	I 30 µl	I 30 µl	II 30 µl	II 30 µl	II 30 µl	III 30 µl	III 30 µl	III 30 µl	IV 30 µl	IV 30 µl	IV 30 µl

Before conducting the enzyme assay, set up a dot blot blotting apparatus in order that the wells from the microtiter plate can be blotted onto Reagent T (nitrocellulose paper) on top of Whatman 3 mm paper.

Enzymatic Assay of PROTEIN KINASE C

PROCEDURE: (continued)

Place the microtiter plate on ice. Pipette (in milliliters) the following reagents into 24 of the 96 wells of microtiter Plate No. 1 as previously indicated:

	<u>Test (-)</u> <u>Activator</u>	<u>Test (+)</u> <u>Activator</u>
Reagent G (Histone)	0.01	0.01
Reagent H (Buffer I)	0.01	-----
Reagent I (Buffer II)	-----	0.01
Reagent F (X-100)	0.01	-----
Reagent P (ATP)	0.01	0.01

In a second 96-well microtiter plate, pipette (in milliliter) 0.03 ml, per well, of Reagent Q (Enzyme Solution) as indicated in Plate No. 2.

For controls, pipette 0.03 ml of Reagent J (Enz Dil) into several wells. In the event there are more than 4 samples (including the control) leave one row of space between each row of samples (Plate No. 2). Volumes are to be added with a multichannel pipette from plate No. 2.

Prepare Reagent N (Lipids). Then add:

Reagent N (Lipids)	-----	0.01
Reagent Q (Enzyme Soln)	0.01	0.01

Incubate at 30°C for exactly 3 minutes; then place on ice. Connect the blot apparatus to a vacuum and transfer 40 μ l of the 50 μ l contents of the microtiter plate (Plate No. 1) to the parallel plate on the blotter. Leave for 5 minutes with vacuum applied.

Disassemble the blot apparatus. Soak the nitrocellulose paper in 200 - 300 ml of Reagent S (TCA). Shake gently for 10 - 15 minutes.

Change to Fresh Reagent S (TCA). Shake for another 10 - 15 minutes. Remove the nitrocellulose paper and place on filter paper to soak up the excess Reagent S (TCA). Cut out the circles (transferred samples) from the nitrocellulose paper and place into scintillation vials containing 1 ml of Reagent R (Scin Fluid). Count the radioactivity in a suitable scintillation counter.

Enzymatic Assay of PROTEIN KINASE C

CALCULATIONS:

$$\text{Units/ml enzyme} = \frac{(\text{cpm})(\text{df})}{(\text{SR})(3)(0.01)} \times 5/4$$

cpm = actual count - background on filter

df = Dilution factor

5/4 = Correction factor for removing 40 μl from the 50 μl reaction mixture

SR = Specific radioactivity (cpm/nmole)

3 = Time (in minutes) of assay as per the Unit Definition

0.01 = Volume (in milliliter) of enzyme used

UNIT DEFINITION:

One unit will transfer 1 nanomole of phosphate from ATP to Histone I (Histone Type III-S) per minute at pH 7.4 at 30°C.

FINAL ASSAY CONCENTRATION:

In a 0.05 ml reaction mix, the final concentrations are 200 $\mu\text{g/ml}$ histone, 60 mM Tris, 20 mM magnesium chloride, 1 mM calcium chloride, 200 $\mu\text{g/ml}$ phosphatidylserine, 8 $\mu\text{g/ml}$ 1,2-dioleoyl-rac-glycerol (C18:1,[cis]-9), 0.02% (w/v) triton X-100, 0.1 mM adenosine 5'-triphosphate, 1 mM DL-dithiothreitol, and 0.03 - 0.05 unit protein kinase C.

REFERENCE:

Huang K.-P. and Huang, F.L. (1991) *Methods in Enzymology* **200**, 241-252

NOTES:

1. The extinction coefficient is described in Keesey, J. (1987).
2. Sigma Prod. No. H-5505, Histone Type III-S contains the Bradbury H1 fraction as the major fraction.
3. For Protein Kinase C, Sigma Prod. No. P-7956, initially reconstitute the vial in 100 μl of deionized water or 10% (w/v) glycerol if the solution is to be stored frozen.
4. This assay is based on the cited reference.
5. Where Sigma Product or Stock numbers are specified, equivalent reagents may be substituted.

Sigma warrants that the above procedure information is currently utilized at Sigma and that Sigma products conform to the information in Sigma publications. Purchaser must determine the suitability of the information and products for its particular use. Upon purchase of Sigma products, see reverse side of invoice or packing slip for additional terms and conditions of sale.