



## QUALITY CONTROL RANGES

MILLIPLEX® MAP Non-Human Primate Cytokine/Chemokine Kit

Catalog # PRCYTOMAG-40K, PCYTMG-40K-PX23 and PRCYMA G40PMX23BK

Control Catalog # MXPR6040 Lot # PCC-121 / PCC-221

### Standard Catalog # MXPR8040

Lot# SC840-21K

| Analyte |  | Standard Value |
|---------|--|----------------|
| sCD40L  |  | 4,923 pg/mL    |

\*\*Please see reverse side for Quality Control Ranges\*\*

**Note: The Quality Control Ranges are generated with overnight assay format using serum matrix provided in the kit. Quality Control values in culture media are not tested.**

MXPR6040: PCC-121.221 (25 March 2021)

EMD Millipore • 1-800-645-5476 • 1-800-645-5439 (FAX) • [emdmillipore.com](http://emdmillipore.com)

The M logo is a trademark of Merck KGaA, Darmstadt, Germany.

© 2013 EMD Millipore Corporation, Billerica, MA 01821 USA.

**QUALITY CONTROL RANGES**  
**MILLIPLEX® MAP Non-Human Primate Cytokine/Chemokine Kit**  
**Catalog # PRCYTOMAG-40K, PCYTMG-40K-PX23 and PRCYMA40PMX23BK**  
**Control Catalog # MXPR6040 Lot # PCC-121 / PCC-221**



| <u>Cytokine</u> | <u>QC Level</u> | <u>Expected Range</u> | <u>Units</u> | <u>Cytokine</u> | <u>QC Level</u> | <u>Expected Range</u> | <u>Units</u> |
|-----------------|-----------------|-----------------------|--------------|-----------------|-----------------|-----------------------|--------------|
| GM-CSF          | Control 1       | 59 - 123              | pg/mL        | IL-4            | Control 1       | 103 - 213             | pg/mL        |
|                 | Control 2       | 422 - 876             | pg/mL        |                 | Control 2       | 805 - 1671            | pg/mL        |
| TGF $\alpha$    | Control 1       | 55 - 115              | pg/mL        | IL-5            | Control 1       | 70 - 146              | pg/mL        |
|                 | Control 2       | 342 - 710             | pg/mL        |                 | Control 2       | 483 - 1003            | pg/mL        |
| G-CSF           | Control 1       | 69 - 144              | pg/mL        | IL-6            | Control 1       | 56 - 116              | pg/mL        |
|                 | Control 2       | 573 - 1190            | pg/mL        |                 | Control 2       | 486 - 1009            | pg/mL        |
| IFN $\gamma$    | Control 1       | 64 - 134              | pg/mL        | IL-8            | Control 1       | 58 - 121              | pg/mL        |
|                 | Control 2       | 533 - 1106            | pg/mL        |                 | Control 2       | 463 - 961             | pg/mL        |
| IL-2            | Control 1       | 67 - 139              | pg/mL        | MIP-1 $\alpha$  | Control 1       | 117 - 243             | pg/mL        |
|                 | Control 2       | 538 - 1118            | pg/mL        |                 | Control 2       | 682 - 1417            | pg/mL        |
| IL-10           | Control 1       | 283 - 588             | pg/mL        | MCP-1           | Control 1       | 70 - 145              | pg/mL        |
|                 | Control 2       | 2268 - 4710           | pg/mL        |                 | Control 2       | 509 - 1057            | pg/mL        |
| IL-15           | Control 1       | 54 - 112              | pg/mL        | TNF $\alpha$    | Control 1       | 17 - 47               | pg/mL        |
|                 | Control 2       | 443 - 920             | pg/mL        |                 | Control 2       | 183 - 492             | pg/mL        |
| sCD40L          | Control 1       | 15 - 40               | pg/mL        | MIP-1 $\beta$   | Control 1       | 56 - 117              | pg/mL        |
|                 | Control 2       | 136 - 283             | pg/mL        |                 | Control 2       | 212 - 552             | pg/mL        |
| IL-17           | Control 1       | 62 - 130              | pg/mL        | IL-12/23 p40    | Control 1       | 63 - 131              | pg/mL        |
|                 | Control 2       | 490 - 1018            | pg/mL        |                 | Control 2       | 471 - 979             | pg/mL        |
| IL-1ra          | Control 1       | 50 - 105              | pg/mL        | VEGF            | Control 1       | 62 - 129              | pg/mL        |
|                 | Control 2       | 412 - 855             | pg/mL        |                 | Control 2       | 501 - 1040            | pg/mL        |
| IL-13           | Control 1       | 69 - 143              | pg/mL        | IL-18           | Control 1       | 277 - 576             | pg/mL        |
|                 | Control 2       | 500 - 1039            | pg/mL        |                 | Control 2       | 2365 - 4912           | pg/mL        |
| IL-1 $\beta$    | Control 1       | 55 - 115              | pg/mL        |                 |                 |                       |              |
|                 | Control 2       | 431 - 895             | pg/mL        |                 |                 |                       |              |

\*\*Please see reverse side for value assigned standard concentrations\*\*

**Note: The Quality Control Ranges are generated with overnight assay format using serum matrix provided in the kit. Quality Control values in culture media are not tested.**

MXPR6040: PCC-121.221 (25 March 2021)

EMD Millipore • 1-800-645-5476 • 1-800-645-5439 (FAX) • [emdmillipore.com](http://emdmillipore.com)

The M logo is a trademark of Merck KGaA, Darmstadt, Germany.

© 2013 EMD Millipore Corporation, Billerica, MA 01821 USA.