



3050 Spruce Street
Saint Louis, Missouri 63103 USA
Telephone 800-325-5832 • (314) 771-5765
Fax (314) 286-7828
email: techserv@sial.com
sigma-aldrich.com

Product Information

Anti-Synapsin II (C-terminal)

produced in rabbit, affinity isolated antibody

Catalog Number **S2947**

Product Description

Anti-Synapsin II (C-terminal) is produced in rabbit using as immunogen a synthetic peptide corresponding to amino acids 569-586 of rat synapsin IIa isoform (GeneID: 29179), conjugated to KLH. This sequence is identical in rat synapsin IIa, human synapsin IIa and mouse synapsin II, and is not found in rat and human synapsin IIb. The antibody is affinity-purified using the immunizing peptide immobilized on agarose.

Anti-Synapsin II (C-terminal) specifically recognizes human, rat and mouse synapsin II by immunoblotting (synapsin IIa ~74 kDa). Staining of the synapsin II band in immunoblotting is specifically inhibited by the immunizing peptide.

Synapsins are a family of neuron-specific phosphoproteins that are localized on the cytoplasmic surface of small synaptic vesicles.^{1,2} Synapsins regulate synaptic vesicle clustering, neurotransmitter release and the formation of synaptic terminals. This family consists of synapsin Ia and Ib (synapsin I, Syn1), synapsin IIa and IIb (synapsin II, Syn2) and synapsin III (Syn3). The various isoforms are generated via alternative splicing of different genes.³ Synapsins are ubiquitously expressed in neurons. They show high homologies in their amino terminal regions. The major difference between synapsins I and II is the presence of a proline-rich C-terminal domain of synapsin I that contains clusters of basic amino acids. Synapsin II is involved in the formation of synaptic terminals during neuronal development.⁴ Similar to synapsin I, synapsin II is able to link synaptic vesicles to the actin cytoskeleton, thus regulating the availability of synaptic vesicles for exocytosis.¹⁻⁴ Synapsin II association with synaptic vesicles is controlled by phosphorylation.^{1,5} Synapsin II has been proposed as a candidate associated with increased vulnerability to schizophrenia.⁶

Reagent

Supplied as a solution in 0.01 M phosphate buffered saline, pH 7.4, containing 15 mM sodium azide as a preservative.

Antibody concentration: ~1.5 mg/mL

Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

Storage/Stability

For continuous use, store at 2-8 °C for up to one month. For extended storage, freeze in working aliquots. Repeated freezing and thawing, or storage in "frost-free" freezers, is not recommended. If slight turbidity occurs upon prolonged storage, clarify the solution by centrifugation before use. Working dilutions should be discarded if not used within 12 hours.

Product Profile

Immunoblotting: a working antibody concentration of 0.25-0.5 µg/mL is recommended using extracts of HEK-293T cells expressing human synapsin II, using mouse brain extract (S1 fraction) and using rat PC12 cell lysate.

Note: In order to obtain the best results using various techniques and preparations, we recommend determining the optimal working dilutions by titration.

References

1. Greengard, P., et al., *Science*, **259**, 780-785 (1993).
2. Thiel, G., et al., *J. Biol. Chem.*, **265**, 16527-16533 (1990).
3. Südhof, T.C., et al., *Science*, **245**, 1474-1480 (1989).
4. Ferreira, A., et al., *Mol. Med.*, **4**, 22-28 (1998).
5. Nielander, H.B., et al., *Eur. J. Neurosci.*, **9**, 2712-2722 (1997).
6. Chen, Q., et al., *Am. J. Hum. Genet.*, **75**, 873-877 (2004).
ER,CS,PHC 08/07-1