3050 Spruce Street, St. Louis, MO 63103 USA
Tel: (800) 521-8956 (314) 771-5765 Fax: (800) 325-5052 (314) 771-5757
email: techservice@sial.com sigma-aldrich.com

# **Product Information**

# Superoxide Dismutase from Escherichia coli

Catalog Number **\$5639** Storage Temperature –20 °C

CAS RN 9054-89-1

EC 1.15.1.1

Synonyms: Superoxide:superoxide oxidoreductase; SOD

OOD

## **Product Description**

SOD from bovine erythrocytes was the first SOD to be found in mammalian tissues. Before its enzymatic activity was discovered the protein was known as haemocuprein or erythrocuprein.<sup>1</sup>

Superoxide Dismutase (SOD) catalyzes the conversion of superoxide radicals into hydrogen peroxide and molecular oxygen.

$$\begin{array}{ccc} & \text{SOD} \\ 2 \text{ O}_2^- + 2 \text{ H}^+ & \rightarrow & \text{O}_2 + \text{H}_2\text{O}_2 \end{array}$$

SOD plays a critical role in the defense of cells against the toxic effects of oxygen radicals. It competes with nitric oxide (NO) for superoxide anions, which react with NO to form peroxynitrite. SOD has suppressed apoptosis in cultured rat ovarian follicles, neural apoptosis in neural cell lines, and transgenic mice by preventing the conversion of NO to peroxynitrate, an inducer of apoptosis.<sup>2-4</sup>

Molecular mass: 5 39.5 kDa (ultracentrifugation)

*E. coli* can produce two SODs depending on growth conditions. Fe-SOD is a homodimeric non-covalently bound protein with one iron per mole and Mn-SOD has 1.6–1.8 moles Mn per mole. There is high structural homology between these two enzymes. This product (Catalog Number S5639) is a Mn-SOD.

Metal content (%):

Mn 0.1286 Fe 0.0022

There are three forms of SOD differentiated by the metal ions in the active site. These are Cu<sup>2+</sup>/Zn<sup>2+</sup>, Mn<sup>2+</sup>, and Fe<sup>2+</sup> SOD. In vertebrate organisms Cu/Zn-SOD is found in the cytoplasm and the mitochondrial intermembrane space, while Mn-SOD is found in the mitochondrial matrix space and in prokaryotes. Fe-SOD is found in prokaryotes and some higher plants. <sup>10</sup>

Extinction coefficient: E<sup>mM</sup> = 55 (280 nm)

pH optimum: 11 7.8

pH Range: 5 7.6-10.5

Isoelectric point: 12 4.93

Inhibitors:

Halides. <sup>13</sup> azide. <sup>13,14</sup> H<sub>2</sub>O<sub>2</sub>. <sup>14</sup> perchlorate <sup>15</sup>

This product (Catalog Number S5639) is highly purified from *E. coli*. It is supplied as a lyophilized powder containing ≥70% protein, with the balance being primarily Tris buffer salts.

Specific activity: ≥1,000 units/mg protein

Unit Definition: One unit will inhibit the rate of reduction of cytochrome c by 50% in a coupled system, using xanthine and xanthine oxidase, at pH 7.8 at 25 °C in a 3.0 ml reaction volume. The xanthine oxidase concentration should produce an initial (uninhibited)  $\Delta A_{550}$  of 0.025  $\pm$  0.005 per minute.

SOD is assayed spectrophotometrically in a 3.00 ml reaction mix. The final concentrations are 50 mM potassium phosphate, 0.1 mM EDTA, 0.01 mM cytochrome c, 0.05 mM xanthine, 0.005 unit of xanthine oxidase, and 1 unit of superoxide dismutase at pH 7.8 at 25 °C.

SOD has also been assayed photochemically in a system containing methionine, riboflavin, and nitroblue tetrazolium. <sup>16</sup>

#### **Precautions and Disclaimer**

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

#### **Preparation Instructions**

SOD is soluble in water at (1 mg/ml) yielding a colorless to light red-purple solution. SOD is also soluble in aqueous buffers such as 0.1 M potassium phosphate, pH 7.5.

### Storage/Stability

Store the product at -20 °C. When stored at -20 °C, the enzyme retains activity for at least two years.

A solution of SOD in 0.1 M potassium phosphate, pH 7.5, shows no loss of activity after one hour at 60  $^{\circ}$ C, after six hours at room temperature, or at least two days at 4  $^{\circ}$ C. For long term storage, store in aliquots at -20  $^{\circ}$ C.

#### References

- 1. McCord, J.M., and Fridovich, I., Superoxide dismutase. An enzymic function for erythrocuprein (hemocuprein). J. Biol. Chem., **244**, 6049 (1969).
- 2. Tilly, J.L., and Tilly, K.I., Inhibitors of oxidative stress mimic the ability of follicle-stimulating hormone to suppress apoptosis in cultured rat ovarian follicles. Endocrinology, **136**, 242-252 (1995).
- Keller, J.N., et al., Mitochondrial manganese superoxide dismutase prevents neural apoptosis and reduces ischemic brain injury: Suppression of peroxynitrite production, lipid peroxidation, and mitochondrial dysfunction. J. Neuroscience, 18, 687-697 (1998).
- Beckman, J.S., et al., Apparent hydroxyl radical production by peroxynitrite: implications for endothelial injury from nitric oxide and superoxide. Proc. Natl. Acad. Sci. USA, 87, 1620-1624 (1990).
- Keele, B.B., Jr., et al., Superoxide dismutase from Escherichia coli B. J. Biol. Chem., 245, 6176-81 (1970).

- 6. Takeda, Y., and Avila, H., Structure and gene expression of the *E. coli* Mn-superoxide dismutase gene. Nucleic Acids Res., **14**, 4577-89 (1986).
- 7. Yost, F.J., Jr. and Fridovich, I., An iron-containing superoxide dismutase from *Escherichia coli*. J. Biol. Chem. 248, 4905-08 (1973).
- 8. Hunter, T., et al., Thermostability of manganeseand iron-superoxide dusmutases from *Escherichia* coli is determined by the characteristic position of a glutamine residue. Eur. J. Biochem., **269**, 5137-48 (2002).
- 9. Marklund, S.L., Extracellular superoxide dismutase in human tissues and human cell lines. J. Clin. Invest., **74**, 1398-1403 (1984).
- 10. Bannister, J.V., *et al.*, Aspects of the structure, function, and applications of superoxide dismutase. CRC Crit. Rev. Biochem., **22**, 111-80 (1987).
- 11. Keele, B.B., Jr., *et al.*, Further characterization of bovine superoxide dismutase and its isolation from bovine heart. J. Biol. Chem., **246**, 2875-80 (1971).
- 12. Daugherty, H.W., *et al.*, A new iron-containing superoxide dismutase from *Escherichia coli*. J. Biol. Chem., **253**, 5220-23 (1978).
- Slykhouse, T.O., and Fee, J.A., Physical and chemical studies on bacterial superoxide dismutases. Purification and some anion binding properties of the iron-containing protein of *Escherichia coli* B. J. Biol. Chem., 251, 5472-77 (1976).
- 14. Beyer, W., et al., Superoxide dismutases. Prog. Nucleic Acid Res. Mol. Biol., 40, 221-53 (1991).
- 15. Cass, A.E.G., Superoxide dismutases. Top. Mol. Struct. Biol., **6**, 121-56 (1985).
- Beauchamp, C.O., and Fridovich, I., Superoxide dismutase: improved assays and an assay applicable to acrylamide gels. Anal. Biochem., 44, 276-87 (1971).

LS,KAD,RBG,JWM,MAM 01/11-1