

3050 Spruce Street
Saint Louis, Missouri 63103 USA
Telephone 800-521-8956 • (314) 771-5765
Fax 800-325-5052 • (314) 771-5757
sigma-aldrich.com

ProductInformation

Anti-Protein Kinase C δ Produced in Rabbit Delipidized, Whole Antiserum

Product No. P8333

Product Description

Anti-Protein Kinase C δ (PKC δ) is generated in rabbits using a synthetic peptide Lys-Ser-Phe-Val-Asn-Pro-Lys-Tyr-Glu-Gln-Phe-Leu-Glu corresponding to the C-terminal variable (V5) region (amino acids 662-673 with N-terminal added Lys) of rat PKC δ . The peptide, coupled to KLH with glutaraldehyde, is used as immunogen. The antiserum is treated to remove lipoproteins.

Anti-Protein Kinase C δ (PKC δ) reacts in immunoblotting (SDS-PAGE) with PKC δ (80 kDa polypeptide) from rat brain extract. Staining of the PKC δ 80 kD band is specifically inhibited with PKC δ peptide (662-673), but not with peptides corresponding to C-terminal sequences of PKC α (659-672), PKC β_1 (658-671), PKC β_2 (660-673), PKC γ (684-697), PKC ε (726-737), or PKC ε (577-592). Anti-Protein Kinase C δ specifically reacts in dot-blot immunoassay with PKC δ peptide conjugated to BSA with 1-ethyl-3-(3-dimethylamino-propyl)-carbodiimide (EDCI).

Protein Kinase C (PKC, 76-93 kD) is a family of serine/threonine (Ser/Thr)-specific protein kinases which are key enzymes playing a crucial role in signal transduction leading to cellular regulation, cell growth and differentiation, oncogenesis, and modulation of neurotransmission. PKC is a phospholipid-dependent enzyme, activated by the lipid 1,2-diacylglycerol (DAG), an intracellular second messenger produced as a result of hydrolysis of inositol phospholipids, in response to a variety of hormones, growth factors and neurotransmitters. 1-3 PKC is also the major cellular receptor for the tumor-promoting phorbol ester derivatives. PKC action is mediated through the phosphorylation of several cellular substrates. 4-6 Proteolysis of PKC in vivo is thought to be mediated by calpains I and II. Calpains cleave PKC in the V3 hinge region to produce two distinct fragments, one comprising the N-terminal regulatory domain (30 kDa) and a fragment containing the C-terminal kinase domain (50 kDa) which is catalytically active. 7,8 Molecular cloning has established that PKC consists of at least 9 different isoenzymes which can be subdivided into two major classes based on their primary structure and activation requirements: conventional

(cPKC) isoforms (α , β_1 , β_2 and γ) and novel (nPKC) isoforms $(\delta, \varepsilon, \xi, \eta(L))$ and θ). The cPKC isoforms have four conserved regions (C1 to C4) separated by five variable regions (V1 to V5) and require Ca²⁺, DAG and phosphatidylserine (PtdSer) for activity. The nPKC isoforms lack the C2 region presumably involved in Ca2+ binding. These isoforms have kinase activities regulated by DAG or PtdSer but are Ca^{2+} independent. The PKC δ isoenzyme appears to be widely expressed in the brain, lung, heart, spleen, liver, ovary, pancreas, thymus, adrenal gland, skin and rat embryonic fibroblasts, and is expressed in lower levels in certain mouse fibroblasts. 3,9,10,11,12 Overexpression and stimulation of PKC δ leads to cell division arrest in CHO cells and growth inhibition of NIH3T3 cells. 12,13 Antibodies that react specifically with PKC isoenzymes may be used to study the specific activation requirements, differential tissue expression, intracellular localization, of these isoenzymes.

Anti-Protein Kinase C δ (PKC δ) may be used for the detection of PKC δ isozyme by various immunochemical methods including immunoblotting, immunoprecipitation, ELISA and immunohisto-chemistry. The antibody may be used for detecting PKC δ by chemiluminescence detection systems.

Reagents

Rabbit Anti-Protein Kinase C δ is supplied as liquid containing 0.1% sodium azide as preservative.

Precautions and Disclaimer

Due to the sodium azide content a material safety sheet (MSDS) for this product has been sent to the attention of the safety officer of your institution. Consult the MSDS for information regarding hazardous and safe handling practices.

Product Profile

Protein Concentration: determined by Biuret.

A minimum working dilution of 1:10,000 was determined by immunoblotting using rat brain extract. Specific staining of PKC δ (80 kDa band) is blocked by incubating

prediluted antibody with PKC δ peptide (concentration 0.5 μ g/ml), for 2 hours at room temperature or overnight at 4 °C.

A minimum working dilution of 1:50,000 was determined by indirect dot blot immunoassay using PKC δ peptide conjugated to BSA with EDCI (conjugate concentration 125 ng/dot).

In order to obtain best results, it is recommended that each user determine the optimal working dilution for individual applications by titration assay.

Storage

For continuous use, store at 2-8 °C for up to one month. For extended storage freeze in working aliquots. Repeated freezing and thawing is not recommended. Storage in "frost-free" freezers is not recommended. If slight turbidity occurs upon prolonged storage, clarify the solution by centrifugation before use.

References

- 1. Nishizuka, Y., Nature, 334, 661 (1988).
- 2. Nishizuka, Y., Science, 258, 607 (1992).
- 3. Hug, H., and Sarre, T., Biochem. J., **291**, 329 (1993).
- 4. Robinson, P., Molecular Neurobiology, 5, 87 (1991).
- Mochly-Rosen, D., et al., J. Biol. Chem., 266, 14866 (1991).
- Huang, K., and Huang, F., Neurochemistry Int., 22, 417 (1993).
- Kishimoto, A., et al., J. Biol. Chem., 264, 4088 (1989).
- 8. Pears, C., and Parker, P., J. Cell Science, **100**, 683 (1991).
- Ogita, K., et al., Proc. Natl. Acad. Sci. USA, 89, 1592 (1992).
- 10. Borner, C., et al., J. Biol. Chem., 267, 12892 (1992).
- 11. Wetsel, W., et al., J. Cell. Biol., 117, 121 (1992).
- 12. Mischak, H., et al., J. Biol. Chem., 268 6090 (1993).
- 13. Watanabe, T. et al., Proc. Natl. Acad. Sci. USA, **89**, 10159 (1992).

Pcs8/99