


Product Information

**Acetaminophen
analytical standard**Catalog Number **A3035**
Lot Number 051M5015
Store at Room Temperature

CAS RN 103-90-2


Synonyms: 4'-Hydroxyacetanilide, 4-Acetamidophenol,
N-Acetyl-4-aminophenol, APAP**Product Description**Molecular Formula: CH₃CONHC₆H₄OH
Molecular Weight: 151.16This product meets USP specifications (Current through
USP 34, 1st supplement) and is traceable to USP
Reference Standard lot K01244.**Precautions and Disclaimer**This product is for R&D use only, not for drug,
household, or other uses. Please consult the Material
Safety Data Sheet for information regarding hazards
and safe handling practices.**Preparation Instructions**Dry a portion over silica gel for 18 hours before using.
Use promptly. Discard unused material.**Storage/Stability**Store in a sealed vial under argon at room temperature.
Protect from light.

KSP,MAM 09/11-1

TEST	USP 34 SPECIFICATIONS	Result Analytical Standard Lot 051M5015
Infrared absorption spectrum KBr dispersion <197K>	compares to standard	compares to standard
Ultraviolet absorption spectrum 5 µg/mL 0.1 N HCl in methanol <197U>	compares to standard	compares to standard
Identification C <201>	meets requirement	compares to standard
Melting range <741>	between 168 °C and 172 °C	169 °C
Water, <i>Method I</i> <921>	not more than 0.5%	0.2%
Residue on ignition <281>	not more than 0.1%	0.0%
Chloride <221>	not more than 0.014%	<0.014%
Sulfate <221>	not more than 0.02%	<0.02%
Sulfide	no coloration or spotting of test paper	no coloration or spotting
Heavy metals, <i>Method II</i> <231>	not more than 0.001%	<0.001%
Free <i>p</i> -aminophenol	not more than 0.005%	0.000%
Limit of <i>p</i> -chloroacetanilide	not more than 0.001%	0.000%
Readily carbonizable substances <271>	the test solution has no more color than <i>Matching Fluid A</i>	less than standard
Assay	not less than 98.0 percent and not more than 101.0 percent C ₈ H ₉ NO ₂ , calculated on the anhydrous basis	98.5%
Residual Solvent	meets the requirements	conforms (class 3 solvents only, < 0.5%)

See reverse side for IR and UV spectra of Analytical Standard

Infrared Spectrum
KBr Dispersion



Ultraviolet Spectrum
5 µg/ml in 0.1 N HCl in Methanol

