



**Instruction Manual**  
**For**  
**STAR Phospho-p53 (Ser15) ELISA Kit**

**Catalog # 17-475**

Sufficient reagents for 96 assays per kit

<b>Contents</b>	<b>Page</b>
<b>I. TEST PRINCIPLE</b>	2
<b>II. BACKGROUND</b>	2
<b>III. ASSAY SENSITIVITY, DETECTION LIMITS, and SPECIES REACTIVITY</b>	3
<b>IV. STORAGE OF KIT COMPONENTS</b>	3
<b>V. KIT COMPONENTS, PRECAUTIONS and TECHNICAL NOTES</b>	3
<b>VI. PREPARATION OF SAMPLE</b>	4
<b>VII. REAGENT PREPARATION</b>	5
<b>VIII. ASSAY PROTOCOL</b>	6
<b>IX. CALCULATION OF RESULTS</b>	7

Sales Orders and Tech Support: 800-MILLIPORE  
Call collect from outside the U.S. 434 975 4300  
email Support:  
<http://www.millipore.com/reply/form/techservice>  
Fax Orders: 866 831 3991  
Online Orders: [www.millipore.com](http://www.millipore.com)

**FOR RESEARCH USE ONLY.**  
**NOT RECOMMENDED OR**  
**INTENDED FOR DIAGNOSIS OF**  
**DISEASE IN HUMANS.**  
**DO NOT USE IN HUMANS.**

This page left blank intentionally.

## **I. TEST PRINCIPLE**

The colorimetric STAR (Signal Transduction Assay Reaction) ELISA kit from Millipore is a solid phase sandwich enzyme linked immunosorbent assay that provides a fast, sensitive method to detect specific levels of signaling targets in whole cell extracts. The p53 plate is coated with a specific mouse monoclonal p53 capture antibody on the microwells of the 96-well clear plate. Sample lysate or the standard included in the kit are incubated in the microwells allowing p53 antigen to be captured in the plate wells. The plate is then washed to remove any unbound non-specific material. The wells are then incubated with a specific rabbit anti-phospho-p53 (Ser15) antibody to detect the captured p53 on the plate well that is phosphorylated on Ser15. The unbound detection antibody is washed away followed by incubation with an HRP-conjugated anti-rabbit antibody. After the addition of TMB substrate and stop solution the absorbance is measured at 450 nm using a plate reader. This allows for a sensitive enzymatic detection of the sample.

The entire assay takes less than 5 hours to complete with minimal hands-on time. Many of the reagents are supplied in ready-to-use formulations for ease of use. The kit also includes a standard that is run as both a positive control and to generate a standard curve for phosphorylated p53 (Ser15) measurement.

## **II. p53 BACKGROUND**

p53, a gene that is mutated in approximately half of all human cancers, has long been regarded as the guardian of the genome by regulating genes controlling cell cycle progression, DNA repair and apoptosis. In response to cellular stress, such as DNA damage, hypoxia, or radiation, p53 is activated and in turn it transcriptionally activates the expression of particular genes, including the cyclin-dependent kinase inhibitor p21, and together with p19ARF, induces expression of p21Cip1, to cause cell cycle arrest. Alternatively, p53 can work via apoptosis as a way of eliminating irreparably damaged cells.

Inactivation or loss of p53 has been associated with deregulation of the cell cycle and DNA replication, inefficient DNA repair, loss of cellular apoptotic responses and ultimately the development of various human cancers. The p53 polypeptide contains three distinct regions. The amino-terminal 83 amino acids of p53 contains the transactivation domain, as well as the region involved in transcription-independent growth suppression, the central sequence-specific DNA binding region, and the carboxy-terminal region contains the DNA-binding domain. Activation and stabilization of p53 is regulated by phosphorylation and possibly acetylation

### III. ASSAY SENSITIVITY, DETECTION LIMITS, and SPECIES REACTIVITY

Sensitivity:	1 units/mL.
Range of Detection:	1.6 to 100 units/mL
Species Reactivity:	Human

### IV. STORAGE OF KIT COMPONENTS

Maintain the unopened kit at 2-8°C until expiration date.

### V. KIT COMPONENTS

1. Capture Plate pre-coated with anti-p53 antibody: (Part No. 17-475A) One pre-coated 96-stripwell immunoplate sealed in a foil pouch.
2. Anti-phospho-p53 (Ser15) detection antibody: (Part No. 17-475B) One bottle (11 mL) of anti-phospho-p53 (Ser15) detection antibody containing sodium azide, ready to use.
3. ELISA Diluent: (Part No. 17-475C) One bottle (25 mL) of ELISA Diluent containing sodium azide, ready to use.
4. 25X ELISA Wash Buffer: (Part No. 17-475D) One bottle (50 mL) of 25X ELISA Wash Buffer.
5. Anti-Rabbit IgG HRP conjugate: (Part No. 17-475E) One vial (125 µL) of 100X anti-rabbit HRP conjugate.
6. HRP Diluent: (Part No. 17-475F) One bottle (25 mL) of HRP Diluent.
7. TMB Solution: (Part No. 17-475G) One bottle (25 mL) of stabilized tetramethylbenzidine (TMB), ready to use.
8. Stop Solution: (Part No. 17-475H) One bottle (25 mL) of stop solution, ready to use.
9. Phospho-p53 (Ser15) Standard: (Part No. 17-475I) Two vials of phosphorylated p53 (Ser15) standard, lyophilized.
10. Plate Covers: Two plate covers.

---

### *Materials Not Supplied*

1. Multi-channel or repeating pipettes
2. Plate shaker (optional)
3. Pipettors & tips capable of accurately measuring 1-1000 µL
4. Graduated serological pipettes
5. 96-well microtiter Plate Reader with 450 nm filter
6. Graphing software for plotting data or graph paper for manual plotting of data
7. Microfuge tubes for standard and sample dilutions
8. Mechanical vortex
9. 1 liter container
10. Distilled or deionized water

---

## ***Precautions***

- The instructions provided have been designed to optimize the kit's performance. Deviation from the instructions may result in suboptimal performance of the kit and the failure to produce accurate data.
- Caustic Material: Stop Solution. **Caution: Eye, hand, face, and clothing protection should be worn when handling this material.**
- **Safety Warnings and Precautions:** This kit is designed for research use only and not recommended for internal use in humans or animals. All chemicals should be considered potentially hazardous and principles of good laboratory practice should be followed.
- The Detection Antibody and ELISA Diluent contain sodium azide. Sodium azide may react with copper and lead plumbing to form highly explosive metal azides. Upon disposal, flush with large amounts of water to prevent azide build-up. Avoid contact with skin.

---

## ***Technical Notes***

- All kit reagents should be at room temperature (20°C to 25°C) just prior to use.
- Do not use reagents beyond the expiration date of the kit.
- Do not mix or interchange reagent from various kit lots.
- Manual Plate Washing: Vigorous washing and complete removal of all liquid by aspiration at the end of each washing step is very important to obtain low background values. Gentle agitation during the wash steps or a 2-3 minute soak may reduce background values.
- The desiccant enclosed in the 96-well capture plate pouch will keep the plate stable when stored at 2° to 8°C should the plate lose its seal during shipping.

## **VI. PREPARATION OF SAMPLE**

1. Culture cells and stimulate p53 activation as desired.
2. Remove culture media and wash cells twice with ice-cold 1X TBS (Tris Buffered Saline) or PBS (Phosphate Buffered Saline). Discard supernatant.
3. Add 5-10 mL of cold 1X RIPA containing protease inhibitors per 150 mm tissue culture plate.  
**Note:** 10 mL of 1X RIPA containing protease inhibitors can be prepared by adding 10 µL of 1 µg/µL Leupeptin, 10 µL of 1 µg/µL Aprotinin, 10 µL of 1 µg/µL Pepstatin, 100 µL of 100mM PMSF, 1 mL 10X RIPA (Cat. No. 20-188) to 8.87 mL of distilled or deionized water.
4. Scrape cells from plate with a rubber policeman.
5. Transfer cells in RIPA buffer to a microcentrifuge tube and incubate on ice for 15 minutes.
6. Vortex tube for 10 seconds or sonicate briefly for 10 seconds.
7. Clarify lysate by centrifugation at 12,000 rpm for 10 minutes at 4°C in a microcentrifuge prior to use.
8. The assay tolerates a maximum of 20 µL per well of lysate prepared in 1X RIPA diluted in ELISA Diluent.
9. Cell extract containing SDS must be diluted to 0.01% SDS using ELISA Diluent prior to use.
10. Collect the supernatant and calculate protein concentration using a Bradford Assay or by densitometry.
11. It is suggested that the cell lysate be used immediately following preparation. However, samples can be frozen and stored at -80° C for later use. Frozen samples should be used within 6 months if storing at -80° C. Avoid repeated freeze thaws.

Further information regarding lysate preparation protocols can be obtained at <http://www.upstate.com> Cell Lysate Extracts-General Protocols.

## VII. REAGENT PREPARATION

### 1. 1X Wash Buffer

Warm the 25X ELISA Wash Buffer to room temperature and mix to ensure that any precipitated salts have re-dissolved. For 500 mL of Wash Buffer, combine 20 mL of 25X ELISA Wash Buffer and 480 mL distilled or deionized water. Stir to homogeneity. Wash Buffer can be stored for up to 4 weeks at 2-8°C. Discard the Wash Buffer if it becomes turbid or if a precipitate develops.

### 2. Anti-Rabbit IgG HRP Conjugate


Dilute the anti-Rabbit IgG HRP Conjugate 100-fold with HRP Diluent immediately before use. Prepare 1 mL for each strip used.

### 3. Standard

**Note:** When opening lyophilized Standard, remove rubber stopper gently as the lyophilizate may have become dislodged during shipping.

Reconstitute the standard with the volume of ELISA Diluent specified on the vial label to give a concentration of 100 Units/mL. Gently swirl the vial and allow the vial to sit for 10 minutes to ensure the material is completely reconstituted. The standard should be reconstituted immediately before the assay. This stock material (tube #1) is then used to generate a standard curve. Any remaining standard can be stored at -80°C. A suggested 2-fold dilution scheme is as follows:

- Label 7 test tubes #2-7 and "0 dose". Add 250  $\mu$ L of the ELISA Diluent to tubes #2-7 and "0 dose".
- Add 250  $\mu$ L of the stock Standard solution [100 Units/mL] to tube #2 and vortex. This is Standard tube #2 with a concentration of 50 Units/mL.
- Standards #3-7 are then prepared by performing a 2-fold serial dilution of the preceding standard. Refer to Fig. 1. For example, to make Standard #3, remove 250  $\mu$ L of Standard #2 and add it to tube #3 and vortex and so on. Do not add any Standard to the "0 Dose" Standard tube.



**Figure 1: Serial Dilution of Standard**

**Note:** The Standard curve can be set up with a different serial dilution scheme by making appropriate adjustments to the dilution pattern.

## VIII. ASSAY PROTOCOL

1. Prepare the reagents as described in the Reagent Preparation section.
2. Place the desired number of strips in the strip well plate holder. (Re-bag the extra strips and return unused strips to refrigerator for future use.)
3. Add either 50  $\mu\text{L}$  of Standards 1 through 7 or the samples to wells of the plate. Add 50  $\mu\text{L}$  of the zero dose to the control wells. It is recommended that standards and samples be run in at least duplicate.

**Note:** Do not add standard or sample lysate to wells reserved for TMB blanks.

**Note:** A standard curve must be generated with each assay.

4. Add 50  $\mu\text{L}$  of the detection antibody to each well. Seal the plate and incubate at room temperature for 3 hours at room temperature (on shaker if possible).
5. **IMPORTANT WASH STEP:**

**Gently remove the plate sealer and wash the plate at least 4 times. A thorough washing of the plate is extremely important to reduce background. We recommend using a multi-channel pipette to fill each well with 250  $\mu\text{L}$  of diluted Wash Buffer. Fluid removal from the wells is best accomplished by inverting the plate over a sink and flicking the fluid out of the wells and then blotting the plate on clean paper towels. Using the multichannel pipet add 250  $\mu\text{L}$  of Wash Buffer to each well; flick and blot the plate. Repeat this procedure for a total of 4 times.**


*For users of automatic plate washers:* It is important to ensure that the wash apparatus is properly maintained and operating correctly. Tubing and tips can easily become clogged, leading to incomplete washing and inadequate aspiration of wells. The result may be poor precision and an unsuitable standard curve. For best results, we recommend at least 4 wash cycles.

6. Add 100  $\mu\text{L}$  of a 1:100 dilution of the anti-Rabbit IgG HRP Conjugate to each well. Cover the plate and incubate at room temperature for 30-45 minutes (on shaker with mild agitation if possible).
7. Wash as described in Step 5. Remove all fluid from the wells and blot the wells dry.
8. Add 100  $\mu\text{L}$  of the TMB Solution to each well. Incubate at room temperature in the dark for 10 to 45 minutes, monitor the color development. Stop the reaction by adding 100  $\mu\text{L}$  of Stop Solution to each well. Immediately read the plate at 450 nm. Plate should be read within 1 hour of adding the stop solution.
9. The plate reader may be blanked against a TMB blank prepared by adding 100  $\mu\text{L}$  of stop solution to 100  $\mu\text{L}$  of the TMB solution.

**CAUTION:** Bubbles in the wells will cause inaccurate readings. Ensure that all bubbles are removed prior to taking the absorbance reading.

**NOTE:** For very low starting protein levels, samples can be placed at 37°C during the final incubation to obtain greater sensitivity.

## IX. CALCULATION OF RESULTS



**Figure 2. Typical phospho-p53 (Ser15) Standard Curve**

**100  $\mu$ L of progressive 2 fold dilutions of the p53 standard included in the kit and run as described in the assay instructions.**

**NOTE:** This data is presented for reference use only and should not be used to interpret actual assay results. A standard curve must be generated for each assay.