



**ANTI-JAK1 (649-747)**  
**Developed in Rabbit, IgG Fraction of Antiserum**

Product Number **J3502**

**Product Description**

Anti-JAK1 is developed in rabbit using a GST fusion protein containing amino acids 649-747 of human JAK1 as immunogen. The antibody is purified using protein A chromatography.

Anti-JAK1 reacts specifically with human JAK1 (approximately 130 kD) and a protein of approximately 80 kD. Other species reactivity is unknown.

Anti-JAK1 may be used for the detection of JAK1 by immunoblotting and immunoprecipitation.

The Janus Kinase (JAK) family is a protein tyrosine kinase (PTK) family involved in cytokine signaling, activated by type I and type II cytokine receptors. It plays a pivotal role in the signal transduction process mediated by cytokines. These kinases appear to transduce signals via their substrates, which modulate programs of gene expression specific to the respective signals. The activation of JAKs is associated with rapid tyrosine phosphorylation of the Signal Transducers and Activators of Transcription (STAT) proteins. At present, the JAK family includes JAK1, JAK2, JAK3 and Tyk2.

The JAKs are 130-kDa proteins that lack SH2/SH3 domains and contain two kinase domains, an active domain and a second kinase-like domain. JAK1, JAK2 and TYK2 are ubiquitous, whereas JAK3 is predominantly expressed in T lymphocytes.

Activation of the JAK/STAT pathway begins with ligand (such as Interferon- $\alpha$ ) binding to receptor on the plasma membrane and activation of certain members of the JAK tyrosine kinase family. Receptors to which JAKs are bound are often referred to as cytokine receptors. JAKs are associated with the intracellular tail of many cytokine receptors. Their ligands include interferon- $\alpha$ ,  $\beta$ , and  $\lambda$ ; interleukins (IL) 2-7, 10-13, and 15; and erythropoietin, growth hormone, prolactin, thrombopoietin, and other polypeptides. Ligand-induced dimerization of the receptor results in the reciprocal tyrosine phosphorylation (activation) of the associated JAK. JAK then phosphorylates tyrosine residues on the cytoplasmic tail of the receptor. These phosphorylated tyrosines function as docking sites for the SH2 domains

## Product Information

of the STAT proteins. Thus, STATs are recruited to the receptor. JAK then catalyzes the tyrosine phosphorylation of the receptor-bound STAT. The phosphorylated STAT molecules then rapidly form homo- or heterodimers. Dimers or heterodimers, but not monomers are competent to bind DNA.<sup>1,2</sup>

SOCS (suppressor of cytokine signaling) proteins are induced in response to cytokine<sup>3,4</sup> and suppress signal transduction in two ways. SOCS-1 appears to bind directly to JAKs and inhibit their catalytic activity,<sup>3,5,6</sup> and CIS, a member of the SOCS family (cytokine-inducible SH2), appears to bind directly to activated receptors and prevent docking of signaling intermediates.<sup>7,8</sup> The phosphatase SHP-1 can also suppresses the signal by dephosphorylating either JAKs or the activated receptor subunits, depending on the specific pathway that is activated.

Besides activating STATs, activated JAKs can bind Shc proteins that recruit Grb-2-SOS complexes, thereby initiating the Ras-MAP kinase pathway. Activated JAKs can also bind insulin receptor substrate (IRS) proteins that are thought to regulate metabolic events in the cell.<sup>9</sup>

**Reagents**

The product is supplied as IgG fraction in 0.07 M tris-glycine buffer, pH 7.4, containing 0.105 M NaCl, 30% glycerol and 0.035% sodium azide.

Protein concentration is approximately 0.7 mg/ml by Bradford.

**Storage/Stability**

Store at 0°C to -20°C. If slight turbidity occurs upon prolonged storage, clarify the solution by centrifugation before use.

**Procedure**

1. Dilute the cell lysate before beginning the immunoprecipitation to roughly 1  $\mu$ g/ $\mu$ l total cell protein in a microcentrifuge tube with PBS (Product No. P3813).
2. Add 5  $\mu$ g of anti-JAK1 to 500  $\mu$ g - 1mg cell lysate.
3. Gently rock the reaction mixture at 4°C overnight.

4. Capture the immunocomplex by adding 100  $\mu$ l of a washed (in PBS) 1:1 slurry of Protein A-Agarose beads (50  $\mu$ l packed beads) (Product No. P2545).
5. Gently rock reaction mixture at 4°C for 2 hours.
6. Collect the agarose beads by pulsing (5 seconds in the microcentrifuge at 14,000 x g), and drain off the supernatant. Wash the beads 3 times with either ice cold cell lysis buffer or PBS.
7. Resuspend the agarose beads in 50  $\mu$ l 2X Laemmli sample buffer. The agarose beads can be frozen for later use.
8. Suspend the agarose beads in Laemmli sample buffer and boil for 5 minutes. Pellet the beads by a microcentrifuge pulse. SDS-PAGE and subsequent immunoblotting analysis may be performed on a sample of the supernatant.

**Lysis Buffer:**

50 mM Tris-HCl, pH 7.4, containing 1% NP-40, 0.25% sodium deoxycholate, 150 mM NaCl, 1 mM EGTA, 1 mM PMSF, 1  $\mu$ g/ml each aprotinin, leupeptin, pepstatin, 1 mM Na<sub>3</sub>VO<sub>4</sub>, and 1 mM NaF.

**Product Profile**

Working concentration is 4  $\mu$ g/ml by immunoblotting using immunoprecipitated JAK1 from human TF1 cells,

anti-rabbit IgG conjugated to peroxidase and enhanced chemiluminescence.

For immunoprecipitation, 5  $\mu$ g will immunoprecipitate JAK1 from 0.5 – 1 mg of a human TF1 cell lysate.

Note: In order to obtain best results and assay sensitivity in different techniques and preparations we recommend determining optimal working dilutions by titration test.

**References**

1. Darnell Jr., J.E., Science, **277**, 1630 (1997)
2. Pellegrini, S., and Dusanter-Fourt, I., Eur. J. Biochem., **248**, 615 (1997).
3. 20. Star, et al., Nature, **387**, 917 (1997).
4. Adams, T.E., et al., J. Biol. Chem., **273**, 1285 (1998).
5. Endo, T.A., et al., Nature, **387**, 921 (1997).
6. Naka, T., et al., Nature, **387**, 924 (1997).
7. 26. Yoshimura, A., et al., EMBO J., **14**, 2816 (1995).
8. Matsumoto, A., et al., Blood, **89**, 3148 (1997).
9. Giorgetti-Peraldi, S., et al., Eur J Biochem, **1;234(2)**, 656 (1995).

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.