

Spectroquant® Move 100



Legend:

red = new test kit or measuring range on Move 100 (upgrade 2014)

red and bold = new Spectroquant® test kit

Overview of preprogrammed methods

Meth. No.	Parameter	Cat. No.	Measuring range	Blank	Type of test	Type of cell
10	Acid cap. 01758	1.01758.0001	0.40 – 8.00 mmol/l	OH	RB	Cell test 16 mm
20	Aluminium 14825	1.14825.0001*	20 – 700 µg/l	Al	RB	Cell test 16 mm
21	Aluminium 00594	1.00594.0001	0.05 – 0.50 mg/l	Al	RB	Test 24 mm
30	Ammonium 14739	1.14739.0001	10 – 2,000 µg/l	NH ₄ -N	RB	Cell test 16 mm
31	Ammonium 14558	1.14558.0001	0.20 – 8.00 mg/l	NH ₄ -N	RB	Cell test 16 mm
32	Ammonium 14559	1.14559.0001	4.0 – 80.0 mg/l	NH ₄ -N	RB	Cell test 16 mm
33	Ammonium 14752	1.14752.0001*	0.02 – 1.30 mg/l	NH ₄ -N	RB	Test 24 mm
34	Ammonium 00683	1.00683.0001	1.0 – 50.0 mg/l	NH ₄ -N	RB	Test 16 mm
40	AOX 00675	1.00675.0001	0.05 – 2.50 mg/l	AOX	RB	Cell test 16 mm
50	Arsenic 01747	1.01747.0001	5 – 100 µg/l	As	RB	Test 16 mm
70	BOD 00687	1.00687.0001	0.5 – 3,000 mg/l	BOD	H ₂ O	Cell test 16 mm
80	Boron 00826	1.00826.0001	0.05 – 2.00 mg/l	B	RB	Cell test 16 mm
90	Bromine 00605	1.00605.0001	0.10 – 5.00 mg/l	Br ₂	H ₂ O	Test 24 mm
100	Cadmium 14834	1.14834.0001	25 – 1,000 µg/l	Cd	RB	Cell test 16 mm
101	Cadmium 01745	1.01745.0001	5 – 500 µg/l	Cd	RB	Test 24 mm
110	Calcium 00858	1.00858.0001	10 – 250 mg/l	Ca	RB	Cell test 16 mm
111	Calcium 14815	1.14815.0001	5 – 160 mg/l	Ca	RB	Test 16 mm
120	Chloride 14730	1.14730.0001	5 – 125 mg/l	Cl	RB	Cell test 16 mm
121	Chloride 14897	1.14897.0001	10 – 250 mg/l	Cl	RB	Test 16 mm
122	Chloride 01804	1.01804.0001	0.5 – 15.0 mg/l	Cl	RB	Cell Test 16 mm
123	Chloride 01807	1.01807.0001	0.50 – 5.00 mg/l	Cl	RB	Test 24 mm
130	Cl₂ CT 0.05–5.00	1.00595.0001 (free) 1.00597.0001 (free + total)	0.05 – 5.00 mg/l	Cl₂	H₂O	Cell test 16 mm
131	Cl₂ 0.02–4.50	1.00598.0002 (free) 1.00598.0001 (free) 1.00602.0001 (total) 1.00602.0002 (total) 1.00599.0001 (free + total)	0.02 – 4.50 mg/l	Cl₂	H₂O	Test 24 mm

* in contrast to the instructions given in the package insert the sample volume as well as the reagent volume must be doubled
RB = own reagent blank value



www.merckmillipore.com/move100

Meth. No.	Parameter	Cat. No.	Measuring range	Blank	Type of test	Type of cell
134	Cl ₂ 0.10–6.00	1.00598.0002 (free) 1.00598.0001 (free) 1.00602.0001 (total) 1.00602.0002 (total) 1.00599.0001 (free + total)	0.10 – 6.00 mg/l	Cl ₂	H ₂ O	Test 16 mm
132	Cl ₂ LR 0.10–6.00	1.00086.0001 + 1.00087.0001 (free)	0.10 – 6.00 mg/l	Cl ₂	H ₂ O	Cell test 16 mm
133	Cl ₂ LR 0.02–4.50	1.00086.0001 + 1.00087.0001 (free)				
140	ClO ₂ 0.05–8.50	1.00608.0001	0.05 – 8.50 mg/l	ClO ₂	H ₂ O	Test 24 mm
141	ClO ₂ 0.20–10.00	1.00608.0001	0.20 – 10.00 mg/l	ClO ₂	H ₂ O	Test 16 mm
150	Chromate 14552	1.14552.0001	0.05 – 2.00 mg/l	Cr	H ₂ O	Cell test 16 mm
151	Chromate 14758	1.14758.0001*	10 – 1,400 µg/l	Cr	H ₂ O	Test 24 mm
168	COD 01796	1.01796.0001	5.0 – 80.0 mg/l	COD	RB	Cell test 16 mm
160	COD 14540	1.14540.0001	10 – 150 mg/l	COD	RB	Cell test 16 mm
161	COD 14895	1.14895.0001	15 – 300 mg/l	COD	RB	Cell test 16 mm
162	COD 14690	1.14690.0001	50 – 500 mg/l	COD	RB	Cell test 16 mm
163	COD 14541	1.14541.0001	25 – 1,500 mg/l	COD	RB	Cell test 16 mm
164	COD 14691	1.14691.0001	300 – 3500 mg/l	COD	RB	Cell test 16 mm
165	COD 14555	1.14555.0001	0.50 – 10.00 g/l	COD	RB	Cell test 16 mm
169	COD 01797	1.01797.0001	5.00 – 90.00 g/l	COD	RB	Cell test 16 mm
166	COD 09772	1.09772.0001	10 – 150 mg/l	COD	RB	Cell test 16 mm
167	COD 09773	1.09773.0001	100 – 1,500 mg/l	COD	RB	Cell test 16 mm
570	COD 17058	1.17058.0001	5.0 – 60.0 mg/l	COD	RB	Cell test 16 mm
571	COD 17059	1.17059.0001	50 – 3,000 mg/l	COD	RB	Cell test 16 mm
170	Color	–	25 – 1,000 mg/l Pt/Co (Hazen)	H ₂ O	Method	24 mm
180	Copper 14553	1.14553.0001	0.05 – 8.00 mg/l	Cu	H ₂ O	Cell test 16 mm
181	Copper 14767	1.14767.0001	0.10 – 6.00 mg/l	Cu	H ₂ O	Test 16 mm
192	Cyanide 02531	1.02531.0001	10 – 350 µg/l	CN	H ₂ O	Cell test 16 mm
190	Cyanide 14561	1.14561.0001	10 – 350 µg/l	CN	H ₂ O	Cell test 16 mm
191	Cyanide 09701	1.09701.0001*	5 – 200 µg/l	CN	H ₂ O	Test 24 mm
201	Cyan. acid 19253	1.19253.0001	2 – 160 mg/l	CyA	SB	Test 24 mm
220	Fluoride 14557	1.14557.0001	0.10 – 1.50 mg/l	F	RB	Cell test 16 mm
222	Fluoride 00809	1.00809.0001	0.10 – 1.80 mg/l	F	RB	Cell test 16 mm
221	Fluoride 14598	1.14598.0001	0.10 – 2.00 mg/l	F	RB	Test 16 mm
223	Fluoride 00822	1.00822.0001	0.08 – 2.00 mg/l	F	RB	Test 24 mm
230	Hydrazine 09711	1.09711.0001*	10 – 1,200 µg/l	N ₂ H ₄	RB	Test 24 mm
560	HydroPerox 18789	1.18789.0001	0.02 – 5.50 mg/l	H ₂ O ₂	RB	Test 16 mm
240	Iodine 00606	1.00606.0001	0.10 – 5.00 mg/l	I ₂	H ₂ O	Test 24 mm
250	Iron 14549	1.14549.0001	0.05 – 4.00 mg/l	Fe	H ₂ O	Cell test 16 mm
251	Iron 14761	1.14761.0001* 1.14761.0002*	0.01 – 2.00 mg/l	Fe	H ₂ O	Test 24 mm
252	Iron 00796	1.00796.0001	0.10 – 5.00 mg/l	Fe	H ₂ O	Test 16 mm
260	Lead 14833	1.14833.0001	0.10 – 5.00 mg/l	Pb	RB	Cell test 16 mm
261	Lead 09717	1.09717.0001	0.05 – 5.00 mg/l	Pb	RB	Test 24 mm
270	Magnesium 00815	1.00815.0001	5.0 – 75.0 mg/l	Mg	RB	Cell test 16 mm
280	Manganese 00816	1.00816.0001	0.10 – 5.00 mg/l	Mn	H ₂ O	Cell test 16 mm
281	Manganese 01739	1.01739.0001	0.05 – 1.80 mg/l	Mn	RB	Test 24 mm
282	Manganese 14770	1.14770.0001*	0.05 – 6.00 mg/l	Mn	H ₂ O	Test 24 mm

* in contrast to the instructions given in the package insert the sample volume as well as the reagent volume must be doubled
RB = own reagent blank value; SB = sample blank value



Meth. No.	Parameter	Cat. No.	Measuring range	Blank	Type of test	Type of cell
283	Manganese 01846	1.01846.0001	0.05 – 1.80 mg/l	Mn	RB	Test 24 mm
290	Molybdenum 00860	1.00860.0001	0.02 – 1.00 mg/l	Mo	H ₂ O	Cell test 16 mm
291	Molybdenum 19252	1.19252.0001	0.5 – 45.0 mg/l	Mo	H ₂ O	Test 24 mm
300	Monochloramine	1.01632.0001	0.10 – 5.00 mg/l	Cl ₂	H ₂ O	Test 24 mm
310	Nickel 14554	1.14554.0001	0.10 – 6.00 mg/l	Ni	H ₂ O	Cell test 16 mm
311	Nickel 14785	1.14785.0001*	0.05 – 5.00 mg/l	Ni	RB	Test 24 mm
320	Nitrate 14542	1.14542.0001	0.5 – 15.0 mg/l	NO ₃ -N	RB	Cell test 16 mm
321	Nitrate 14773	1.14773.0001	0.5 – 15.0 mg/l	NO ₃ -N	RB	Test 16 mm
322	Nitrate 14556	1.14556.0001	0.10 – 3.00 mg/l	NO ₃ -N	RB	Cell test 16 mm
323	Nitrate 01842	1.01842.0001	0.3 – 30.0 mg/l	NO ₃ -N	RB	Test 24 mm
330	Nitrite 14547	1.14547.0001	10 – 700 µg/l	NO ₂ -N	H ₂ O	Cell test 16 mm
331	Nitrite 14776	1.14776.0001* 1.14776.0002*	5 – 400 µg/l	NO ₂ -N	H ₂ O	Test 24 mm
332	Nitrite 00609	1.00609.0001	1.0 – 90.0 mg/l	NO ₂ -N	H ₂ O	Cell test 16 mm
340	Nitrogen 14537	1.14537.0001	0.5 – 15.0 mg/l	N	RB	Cell test 16 mm
550	Oxygen 14694	1.14694.0001	0.5 – 12.0 mg/l	O ₂	H ₂ O	Cell test 16 mm
555	Oxyg. scavengers	1.19251.0001	20 – 500 µg/l	DEHA	RB	Test 24 mm
350	Ozone 0.02–3.00	1.00607.0001 1.00607.0002	0.02 – 3.00 mg/l	O ₃	H ₂ O	Test 24 mm
351	Ozone 0.10–4.00	1.00607.0001 1.00607.0002	0.10 – 4.00 mg/l	O ₃	H ₂ O	Test 16 mm
360	pH 01744	1.01744.0001	6.4 – 8.8		H ₂ O	Cell test 16 mm
370	Phenol 14551	1.14551.0001	0.10 – 2.50 mg/l	C ₆ H ₅ OH	RB	Cell test 16 mm
371	Phenol 00856	1.00856.0001	0.10 – 5.00 mg/l	C ₆ H ₅ OH	RB	Test 24 mm
387	Phosphate 00474	1.00474.0001	0.05 – 4.00 mg/l	PO ₄ -P	H ₂ O	Cell test 16 mm
380	Phosphate 14543	1.14543.0001	0.05 – 4.00 mg/l	PO ₄ -P	H ₂ O	Cell test 16 mm
388	Phosphate 00475	1.00475.0001	0.5 – 20.0 mg/l	PO ₄ -P	H ₂ O	Cell test 16 mm
381	Phosphate 14729	1.14729.0001	0.5 – 20.0 mg/l	PO ₄ -P	H ₂ O	Cell test 16 mm
382	Phosphate 00616	1.00616.0001	3.0 – 100.0 mg/l	PO ₄ -P	H ₂ O	Cell test 16 mm
389	Phosphate 00673	1.00673.0001	3.0 – 100.0 mg/l	PO ₄ -P	H ₂ O	Cell test 16 mm
383	Phosphate 14848	1.14848.0001*	0.01 – 2.50 mg/l	PO ₄ -P	H ₂ O	Test 24 mm
384	Phosphate 00798	1.00798.0001	1.0 – 60.0 mg/l	PO ₄ -P	H ₂ O	Test 16 mm
385	Phosphate 14842	1.14842.0001	0.5 – 30.0 mg/l	PO ₄ -P	RB	Test 16 mm
386	Phosphate 14546	1.14546.0001	0.5 – 25.0 mg/l	PO ₄ -P	RB	Cell test 16 mm
400	Potassium 14562	1.14562.0001	5.0 – 50.0 mg/l	K	H ₂ O	Cell test 16 mm
401	Potassium 00615	1.00615.0001	30 – 300 mg/l	K	H ₂ O	Cell test 16 mm
410	Residual hardness 14683	1.14683.0001	0.50 – 5.00 mg/l	Ca	RB	Cell test 16 mm
420	Silicate 14794	1.14794.0001*	0.11 – 8.56 mg/l	SiO ₂	H ₂ O	Test 24 mm
421	Silicate 00857	1.00857.0001	11 – 1,070 mg/l	SiO ₂	H ₂ O	Test 16 mm
422	Silicate 01813	1.01813.0001	0.004 – 0.500 mg/l	SiO ₂	RB	Test 24 mm
430	Sodium 00885	1.00885.0001	10 – 300 mg/l	Na	RB	Cell test 16 mm
444	Sulfate 02532	1.02532.0001	2.0 – 50.0 mg/l	SO ₄	RB	Cell test 16 mm
440	Sulfate 14548	1.14548.0001	5 – 250 mg/l	SO ₄	H ₂ O	Cell test 16 mm
441	Sulfate 00617	1.00617.0001	50 – 500 mg/l	SO ₄	H ₂ O	Cell test 16 mm
442	Sulfate 14564	1.14564.0001	100 – 1,000 mg/l	SO ₄	H ₂ O	Cell test 16 mm
443	Sulfate 01812	1.01812.0001	1.0 – 25.0 mg/l	SO ₄	RB	Test 24 mm
445	Sulfate 02537	1.02537.0001 1.02537.0002	10 – 300 mg/l	SO ₄	H ₂ O	Test 16 mm
450	Sulfide 14779	1.14779.0001	0.10 – 1.50 mg/l	S	H ₂ O	Test 16 mm
460	Sulfite 14394	1.14394.0001	1.0 – 20.0 mg/l	SO ₃	RB	Cell test 16 mm

* in contrast to the instructions given in the package insert the sample volume as well as the reagent volume must be doubled
RB = own reagent blank value



Meth. No.	Parameter	Cat. No.	Measuring range	Blank	Type of test	Type of cell
461	Sulfite 01746	1.01746.0001	1.0 – 60.0 mg/l	SO ₃	RB	Test 16 mm
470	Surfact-a 14697	1.14697.0001	0.05 – 2.00 mg/l	MBAS	RB	Cell test 16 mm
473	Surfact-a 02552	1.02552.0001	0.10 – 2.00 mg/l	MBAS	RB	Cell test 16 mm
472	Surfact-n 01787	1.01787.0001	0.10 – 7.50 mg/l		RB	Cell test 16 mm
480	Susp. solids	–	50 – 750 mg/l		H ₂ O	Method 24 mm
490	Tin 14622	1.14622.0001	0.10 – 2.50 mg/l	Sn	H ₂ O	Cell test 16 mm
510	Total hardness 00961	1.00961.0001	5 – 215 mg/l	Ca	RB	Cell test 16 mm
520	Turbidity	–	1 – 100 FAU		H ₂ O	Method 24 mm
531	Volatile org. acids	1.01749.0001 1.01809.0001	50 – 3,000 mg/l 50 – 3,000 mg/l		RB RB	Cell test Test 16 mm 16 mm
540	Zinc 00861	1.00861.0001	25 – 1,000 µg/l	Zn	RB	Cell test 16 mm
541	Zinc 14566	1.14566.0001	0.20 – 5.00 mg/l	Zn	RB	Cell test 16 mm
600	A 430 nm					Absorbance
610	A 530 nm					Absorbance
620	A 560 nm					Absorbance
630	A 580 nm					Absorbance
640	A 610 nm					Absorbance
650	A 660 nm					Absorbance

* in contrast to the instructions given in the package insert the sample volume as well as the reagent volume must be doubled
RB = own reagent blank value



For further information on Merck Millipore and our products contact:

Merck KGaA
64271 Darmstadt, Germany
www.merckmillipore.com/move-disinfection-control
© 2014 Merck KGaA, Darmstadt, Germany. All rights reserved.



www.merckmillipore.com/move100

We provide information and advice to our customers on application technologies and regulatory matters to the best of our knowledge and ability, but without obligation or liability. Existing laws and regulations are to be observed in all cases by our customers. This also applies in respect to any rights of third parties. Our information and advice do not relieve our customers of their own responsibility for checking the suitability of our products for the envisaged purpose. Spectroquant® is a trademark of Merck KGaA, Darmstadt, Germany.