

Product Information

RIFAMPICIN

Sigma Prod. No. R3501

CAS NUMBER: 13292-46-1

SYNONYMS: Tubocin; Sinerdol; Rimactan; L-5103; Dione-21 Acetate; Archidyn; Arficin; 3-(4-Methylpiperazinyliminomethyl)-rifamycin SV; NSC 113926; Rifampin¹; Rifaldazine; Rifamycin AMP²

PHYSICAL PROPERTIES:

Appearance: Orange-brown to red-brown powder.³

Molecular formula: C₄₃H₅₈N₄O₁₂

Molecular weight: 823.0


E_{mM} (max absorbance, phosphate buffer, pH 7.38): 33.20 (237 nm); 32.10 (255 nm); 27.00 (334 nm); 15.40 (475 nm)^{2,4}

pK_a (in water): 1.7 (4-hydroxyl group), 7.9 (4-piperazine nitrogen); in methylcellosolve-water (4:1): 3.6 (4-hydroxyl group), 6.7 (3-piperazine nitrogen)⁴

pI (in water): 4.8⁴

Optical rotation: [α]_D^{25°} = +10.6° (c=0.5% in CDCl₃)⁴

Melting point: 183-188°C (dec.)^{2,4}



METHOD OF PREPARATION:

Methods of preparation have been reported.^{4,5} The NMR, UV, IR, Mass spectra, Thin-Layer chromatography and HPLC methods of detection have been reported.^{4,5,6} A colorimetric test for identification was reported.⁴

STABILITY / STORAGE:

Rifampicin (Rif) should be stable for at least two years when stored desiccated at -20°C and protected from light.³ Rif is stable as a solid at temperatures up to 70°C.⁴

SOLUBILITY / SOLUTION STABILITY:

Rif is soluble in dimethylsulfoxide (~100mg/mL), dimethylformamide, methanol (16 mg/ml, 25°C), chloroform (349 mg/ml, 25°C), ethyl acetate (108 mg/ml, 25°C), and acetone (14 mg/ml, 25°C).^{4,6,7,8,9} Rif is slightly soluble in water at 25°C: 2.5 mg/ml, pH 7.3; 1.3 mg/ml, pH 4.3; and in 95% ethanol (~10 mg/mL).⁴ Rif is soluble at 37°C: in 0.1 N HCl, 200 mg/ml and in phosphate buffer pH 7.4, 9.9 mg/ml.⁴

RIFAMPICIN
Sigma Prod. No. R3501

SOLUBILITY / SOLUTION STABILITY:

A 1% suspension in water has a pH of 4.5-6.5.^{4,7} Stock solutions in DMSO were diluted in 0.20 M potassium phosphate buffer to prepare working solutions of 10 µg/ml.⁸ Solution stabilities of Rif: DMSO, 10 mg/ml, about 8 months at 15°C⁸; water-ethanol (8:2), 1 mg/ml, 8 weeks at 4°C or 20°C.^{2,4} In mildly basic aqueous solutions (pH 8.2, 20-22°C) in the presence of air, Rif is converted to rifampin quinone. Addition of sodium ascorbate can prevent its oxidation. Under basic conditions Rif undergoes desacetylation at 22°C forming the 25-desacetyl rifampin (most of antibacterial activity is maintained).⁴ Rif decomposes rapidly in acidic or alkaline conditions at 25°C but slowly in neutral conditions, i.e. at 200 µg/ml, at pH 2.3 Rif is hydrolyzed to 3-formylrifampicin.^{4,5} It is best to prepare aqueous solutions with oxygen-free solvent and at neutral pH.

USAGE / APPLICATIONS:

Rif inactivates bacterial RNA polymerase (RNAP) at about 0.01-0.02 µg/ml (50% effective dose).^{10,11} Rif has activity against a wide range of microorganisms such as mycobacteria including *Mycobacterium tuberculosis*⁹ and *M. leprae*.¹² Rif is highly active against Gram-positive bacteria, such as staphylococci, streptococci, pneumococci but is less active against Gram-negative organisms.^{13,14} The minimum inhibitory concentrations (MIC) for the most sensitive microorganisms (chlamydia, staphylococci) are in the range of about 0.01-0.02 µg/ml; and for the most sensitive mycobacteria, from about 0.1-2 µg/ml.⁷ Additional MIC values for different bacterial strains have been reported.^{14,15} The inhibitory activity of Rif remained practically unchanged between pH 5.5-8.0.¹⁴ Rif inhibits bacterial DNA-dependent RNA polymerase (the enzyme responsible for DNA transcription) by forming a stable enzyme-drug complex with the β-subunit of RNA polymerase (RNAP-Rif), *rpoB* gene (binding constant of 10⁻⁹ M at 37°C).^{10,16,17} Rif suppresses the initiation of chain formation (but not chain elongation) in RNA synthesis.¹⁸ The RNAP-Rif complex is locked on the promoter in the abortive initiation reaction, producing short oligoribonucleotides which diffuse out of the active site.¹⁹ There is some inhibition of mammalian RNA polymerases at much higher concentrations of Rif than that for bacterial RNA polymerases.²⁰ Nuclear RNA polymerases from different eukaryotic cells are not inhibited by Rif.^{18,21}

Bacterial resistance to Rif is due to mutations which result in changes in the structure of the β subunit of RNA polymerase, i.e. studies of Rif resistance in *Mycobacterium tuberculosis* (*M. tuberculosis*) indicated that resistance is mostly, but not necessarily, associated with mutations on the *rpoB* gene in *Mycobacterium tuberculosis*.^{10,16} Rif (100 µg/ml) completely inhibited RNA synthesis in chloroplasts.²² Rif can penetrate into polymorphonuclear leucocytes and kill intracellular pathogens.^{18,23} Rif (100 µg/ml) is active against some viruses.^{12,15,24,25} Rif has antifungal activity probably due to some other mechanism of action than inhibition of a fungal RNA polymerase.²⁶

RIFAMPICIN
Sigma Prod. No. R3501

USAGE / APPLICATIONS: (continued)

Rif inhibited A β 1-40 (Amyloid β -peptide which deposits in the brains of Alzheimer's disease patients) aggregation and neurotoxicity in rat PC12 cells in a concentration-dependent manner.²⁷ Rif (25 μ M) strongly induced the genes CYP3A4 and CYP3A7 mRNAs in adult human hepatocytes in culture.²⁸ Rif strongly induced cytochrome P-450 3A-dependent enzyme and UDP-glucosyltransferase activities in female rat liver microsomes at dosage \geq 250 mg/kg/day.²⁹ Rif inhibited protein synthesis in rat thymocytes at $>$ 20 μ g/ml.³⁰

GENERAL NOTES:

Rif is a semisynthetic derivative of rifamycin B and belongs to the rifamycin group of antibiotics.¹⁸ It functions as a bacteriostatic agent by interfering with the synthesis of nucleic acids by inhibiting microorganisms.⁷ The chemical, biological properties, activity studies (including microbiological assays methods), pharmacology, metabolism and mechanisms of action have been reported.^{4,10,15}

REFERENCES:

1. Sigma's Material Safety Data Sheet
2. The *Merck Index* 12:8382.
3. Sigma Quality Control data
4. Gallo, G.G. and Radaelli, P., *Anal. Profiles of Drug Subs.*, K. Florey, ed. Academic Press, NY, 5, 467, 1976.
5. Maggi, N. et al., *Chemotherapia* 11, 285, 1966.
6. *Clarke's Isolation and Identification of Drugs*, 2nd ed., eds. Moffat, A.C. et al., p 960, The Pharmaceutical Press, London, 1986.
7. Martindale, The Extra Pharmacopoeia, 31st ed., p. 268, 1996.
8. Karlson, A.G. and Ulrich, J.A., *Appl. Microbiol.*, 18, 692, 1969.
9. Pallanza, R. et al., *Arzneimittelforschung*, 17, 529, 1967.
10. Wehrli, W., *Rev. of Infect. Dis.*, 5, Supplement 3, S407, July-August 1983.
11. Hartmann, G. et al., *Biochim. Biophys. Acta* 145, 843, 1967.
12. Lester, W., *Annu. Rev. of Microbiol.*, 26, 85, 1972.
13. Dans, P.E. et al., *Am. J. Med. Sci.*, 259, 120, 1970.
14. Arioli, V. et al., *Arzneimittelforschung*, 17, 523, 1967.
15. Binda, G. et al., *Arzneimittelforschung*, 21, 1907, 1971 (review).
16. Taniguchi, H. et al., *FEMS Microbiol. Lett.* 144, 103, 1996.
17. Wehrli, W. et al., *Proc. Natl Acad. Sci. USA* 61, 668, 1968.
18. *Goodman and Gilman's The Pharmacological Basis of Therapeutics*, p. 1149, 8th ed., eds. Gilman, A.G. et al., Pergamon Press, 1990.
19. Severinov, K. et al., *J. Biol. Chem.* 268, 14820, 1993.
20. Wehrli, W. et al., *Biochim. Biophys. Acta*, 157, 215, 1968.
21. Data for Biochemical Research, 274, 3rd ed. eds Dawson, R.M.C. et al. Oxford University Press, Oxford, England, 1986.
22. Surzycki, S.J., *Proc. Natl. Acad. Sci. USA* 63, 1327, 1969.

RIFAMPICIN
Sigma Prod. No. R3501

REFERENCES:

23. Prokesch, R.C., *Antimicrob. Agents Chemother.* 21, 373, 1982.
24. Moss, B. et al., *Nature*, 224, 1280, 1969.
25. Moss, B. et al., *Biochem. Biophys. Res. Commun.* 36, 858, 1969.
26. Medoff, G. *Rev. Infect. Dis.* 5 (Suppl 3), S614, 1983.
27. Tomiyama, T. et al., *J. Biol. Chem.* 271, 6839, 1996.
28. Greuet, J. et al., *Biochem. Biophys. Res. Commun.* 225, 689, 1996.
29. Oesch, F. et al., *J. Antimicrob. Chemother.*, 37, 1111, 1996.
30. Buss, W.C. et al., *Science*, 200, 432, 1978.