

## Technical Data Sheet

# Buffered NaCl-Peptone Solution + Neutralizers

Ordering number: 1.46482.0006

Buffered NaCl-Peptone Solution is designed for the microbial examination of non-sterile pharmaceutical products in the presence of disinfectant residues.

The solution is used for the microbial examination of non-sterile pharmaceutical products, e.g. as solution for sample preparation or as dilution or washing solution.

The formulation of the basic medium (Buffered NaCl-Peptone Solution) is prepared according to the recommendations of the current European Pharmacopoeia (EP, 2.6.13.).

Buffered NaCl-Peptone Solution is available with different neutralizers in different filling volumes and with various locking mechanisms:

- Buffered NaCl-Peptone Solution + LT (article number 146570): 125 ml-bottle with **screw cap**, filling volume 90 ml
- Buffered NaCl-Peptone Solution + LTH (article number 146175): 17 ml-**tube**, filling volume 9 ml
- Buffered NaCl-Peptone Solution + LTH (article number 146522): 275 ml-bottle with **wide mouth**, filling volume 90 ml
- Buffered NaCl-Peptone Solution + LTH (article number 146507): 250 ml-bottle with **flip cap**, filling volume 200 ml
- Buffered NaCl-Peptone Solution + LTH (article number 146482): 500 ml-bottle with **screw cap**, filling volume 450 ml
- Buffered NaCl-Peptone Solution + LTH (article number 146595): 1000 ml-bottle with **screw cap**, filling volume 1000 ml
- Buffered NaCl-Peptone Solution + TLH (article number 146481): 1000 ml-bottle with **screw cap**, filling volume 1000 ml
- Buffered NaCl-Peptone Solution + LTHTh (article number 146471): 275 ml-bottle with **wide mouth**, filling volume 90 ml
- Buffered NaCl-Peptone Solution + LTHTh (article number 146557): 500 ml-bottle with **screw cap**, filling volume 400 ml

## Mode of Action

The low content of peptone as well as the content of phosphate buffer and sodium chloride in the solution maintains the viability of present microorganisms without supporting growth.

The neutralizing additives lecithin, Polysorbate (Tween®) 80, Na-thiosulfate and histidine reverse the growth inhibitory effect of most disinfectants and antiseptics. Neutralizing efficiency of histidine could be shown against formaldehyde and formaldehyde releasing agents. Na-thiosulfate inactivates sodium hypochlorite and acidified sodium chlorite. Lecithin, particularly in combination with Tween® 80, is effective against quaternary ammonium compounds, amphoteric surfactants, benzamidines, chlorhexidines and dequadin. Tween® 80 inactivates benzyl alcohol, carbanilides, dichlorobenzyl alcohols, benzoic acid, p-hydroxybenzoic acid and its esters, phenols, phenylethyl alcohols and Solbrols (PHB esters).

## Typical Composition

Additive	NaCl-Peptone Solution + LT	NaCl-Peptone Solution + LTH	NaCl-Peptone Solution + LTHTh
Peptone	1 g/l	1 g/l	1 g/l
NaCl	4.3 g/l	4.3 g/l	4.3 g/l
KH <sub>2</sub> PO <sub>4</sub>	3.6 g/l	3.6 g/l	3.6 g/l
Na <sub>2</sub> HPO <sub>4</sub> · 2 H <sub>2</sub> O	7.2 g/l	7.2 g/l	7.2 g/l
Lecithin	3 g/l	3 g/l	3 g/l
Polysorbate (Tween®) 80	30 ml/l	30 ml/l*	30 ml/l
Histidine	-	1 g/l	1 g/l
Sodium Thiosulfate	-	-	5 g/l
<b>Appearance</b>	clear, colorless to slightly yellowish	clear to slightly turbid, colorless to yellowish	clear, light to dark yellow

\* 10 ml/l in Buffered NaCl-Peptone Solution + LTH (article number 146595)

The pH value is in the range of 6.8-7.2. The medium can be adjusted and/or supplemented according to the performance criteria required.

## Application and Interpretation

For quality control a stability test is performed in order to test the ability of the solution to maintain viability of microorganisms. Therefore the buffer solution to be tested is inoculated with 100-1,000 CFU/ml. Directly after inoculation as well as after an incubation time of 1 hour at 20 to 25 °C for each test strain 100 µl are subcultured on Columbia Blood Agar (article number 146559). The viable count should not change from the beginning to the end of incubation. A typical stability test is shown under "Quality Control".

## Storage and Shelf Life

The product can be used for tests until the expiry date if protected from light and properly sealed at +2 °C to +25 °C.

The testing procedures as described on the CoA can be started up to the expiry date printed on the label.



We provide information and advice to our customers on application technologies and regulatory matters to the best of our knowledge and ability, but without obligation or liability. Existing laws and regulations are to be observed in all cases by our customers. This also applies in respect to any rights of third parties. Our information and advice do not relieve our customers of their own responsibility for checking the suitability of our products for the envisaged purpose.

EMD Millipore and the M logo are registered trademarks of Merck KGaA, Darmstadt, Germany. Lit. No. TN1806ENUS

## Disposal

Please mind the respective regulations for the disposal of used culture medium (e.g. autoclave for 20 min at 121 °C, disinfect, incinerate etc.).

## Quality Control

Control Strains	ATCC #	Inoculum CFU	Incubation	Expected Results
<i>Staphylococcus aureus</i>	6538	2,000-20,000	1 h ± 5 min at 20-25 °C	No change in the number of CFU
<i>Pseudomonas aeruginosa</i>	9027	2,000-20,000	1 h ± 5 min at 20-25 °C	No change in the number of CFU
<i>Escherichia coli</i>	8739	2,000-20,000	1 h ± 5 min at 20-25 °C	No change in the number of CFU
<i>Bacillus subtilis</i>	6633	2,000-20,000	1 h ± 5 min at 20-25 °C	No change in the number of CFU
<i>Candida albicans</i>	10231	2,000-20,000	1 h ± 5 min at 20-25 °C	No change in the number of CFU
<i>Escherichia coli</i> + 200 µl Aerodesin 2000	8739	2,000-20,000	1 h ± 5 min at 20-25 °C	No change in the number of CFU

Please refer to the actual batch related Certificate of Analysis.

## Literature

European Pharmacopoeia 8.0 (2014): 2.6.13. Microbial examination of non-sterile products (test for specified microorganisms).

Russel, A.D., Ahonkhai, I. and Rogers, D.T. (1979) Microbiological applications of the inactivation of antibiotics and other antimicrobial agents. *Journal of Applied Bacteriology* 46:207-245



We provide information and advice to our customers on application technologies and regulatory matters to the best of our knowledge and ability, but without obligation or liability. Existing laws and regulations are to be observed in all cases by our customers. This also applies in respect to any rights of third parties. Our information and advice do not relieve our customers of their own responsibility for checking the suitability of our products for the envisaged purpose.

EMD Millipore and the M logo are registered trademarks of Merck KGaA, Darmstadt, Germany. Lit. No. TN1806ENUS

## Ordering Information

Product	Cat. No.	Pack size
Buffered NaCl-Peptone Solution + LT	1.46570.0010	10 x 90 ml bottle
Buffered NaCl-Peptone Solution + LTH	1.46175.0020	20 x 9 ml tube
Buffered NaCl-Peptone Solution + LTH	1.46175.0100	100 x 9 ml tube
Buffered NaCl-Peptone Solution + LTH	1.46522.0006	6 x 90 ml bottle
Buffered NaCl-Peptone Solution + LTH	1.46507.0006	6 x 200 ml bottle
Buffered NaCl-Peptone Solution + LTH	1.46482.0006	6 x 450 ml bottle
Buffered NaCl-Peptone Solution + LTH	1.46595.0006	6 x 1000 ml bottle
Buffered NaCl-Peptone Solution + TLH	1.46481.0006	6 x 1000 ml bottle
Buffered NaCl-Peptone Solution + LTHTh	1.46471.0006	6 x 90 ml bottle
Buffered NaCl-Peptone Solution	1.46557.0006	6 x 400 ml bottle
Columbia Blood Agar Pharm.	1.46559.0020	20 x 90 mm plates
Columbia Blood Agar Pharm.	1.46559.0100	100 x 90 mm plates

EMD Millipore Corporation  
290 Concord Road  
Billerica, MA 01821, U.S.A.  
mibio@emdmillipore.com  
[www.emdmillipore.com/biomonitoring](http://www.emdmillipore.com/biomonitoring)

Find contact information for your country at:  
[www.emdmillipore.com/offices](http://www.emdmillipore.com/offices)  
For Technical Service, please visit:  
[www.emdmillipore.com/techservice](http://www.emdmillipore.com/techservice)



We provide information and advice to our customers on application technologies and regulatory matters to the best of our knowledge and ability, but without obligation or liability. Existing laws and regulations are to be observed in all cases by our customers. This also applies in respect to any rights of third parties. Our information and advice do not relieve our customers of their own responsibility for checking the suitability of our products for the envisaged purpose.

EMD Millipore and the M logo are registered trademarks of Merck KGaA, Darmstadt, Germany. Lit. No. TN1806ENUS