

Product Information

Anti-Goat IgG (whole molecule)-Alkaline Phosphatase produced in rabbit, affinity isolated antibody

Catalog Number **A4187**

Product Description

Antiserum is produced in rabbit using purified goat IgG as the immunogen. Affinity isolated antibody is obtained from Anti-Goat IgG antiserum by immunospecific purification which removes essentially all rabbit serum proteins, including immunoglobulins, which do not specifically bind to goat IgG. Anti-Goat IgG is conjugated to alkaline phosphatase by protein cross-linking with 0.2% glutaraldehyde.¹

Specificity of the antiserum is determined by immunoelectrophoresis (IEP) prior to conjugation. By IEP, the antiserum reacts specifically with normal goat serum and goat IgG.

Identity and purity of the antibody is established by immunoelectrophoresis prior to conjugation. Electrophoresis of the product followed by diffusion versus anti-rabbit IgG and anti-rabbit whole serum results in single arcs of precipitation.

Reagent

Supplied as a solution in 0.05 M Tris buffer, pH 8.0, containing 1% BSA, 1 mM MgCl₂, 50% glycerol, and 15 mM sodium azide as a preservative.

Precautions

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

Storage

Store at 2-8 °C.

Product Profile

ELISA: a minimum titer of 1:30,000 is determined by Direct ELISA. Titer is defined as the dilution of conjugate sufficient to give a change in absorbance of 1.0 at 405 nm after 30 minutes of substrate conversion at 25 °C.² Microtiter plates are coated with purified goat IgG at a concentration of 5 µg/ml in 0.05 M carbonate-bicarbonate buffer, pH 9.6

Carbonate-Bicarbonate Buffer capsules are available as Catalog Number C3041.

Substrate: *p*-Nitrophenyl phosphate (pNPP), Catalog Number N2765, 1.0 mg/ml in 10% diethanolamine buffer, pH 9.8, containing 0.5 mM MgCl₂.

Immunohistology: a minimum titer of 1:50 is determined by an indirect assay using formalin-fixed, paraffin-embedded sections of human tonsil and Anti-Human IgG, Catalog Number I3382, as the primary antibody.

Substrate: Fast Red TR/AS-MX Naphthol Phosphate³ SIGMA FAST Tablets, Catalog Nos. F4523 or F4648.

Immunoblotting: a minimum titer of 1:30,000 is determined. Goat IgG was detected directly using 10 µg protein per lane. Reducing conditions on an SDS-PAGE gradient (4-20%) gel were used. The protein was transferred to nitrocellulose, blocked with 5% BSA in 0.05 M Tris, transferred and then incubated with the conjugate.

Substrate: 5-Bromo-4-chloro-3-indolyl Phosphate/Nitroblue Tetrazolium (BCIP/NBT) SIGMA FAST Tablets, Catalog Number B5655.

Note: Working dilutions should be determined by titration assays. Due to differences in assay systems, these titers may not reflect the user's actual working dilution.

References

1. Avrameas, V., *Immunochemistry*, **6**, 43, (1969).
2. Voller, A., et al., *Bull. World Health Organ.* **53**, 55 (1976).
3. Pluzek, K. and Ramlau, R., Alkaline Phosphatase Labeled Reagents, in CRC Handbook of Immunoblotting of Proteins, Bjerrum O., and Heegaard, N. (Eds.), CRC Press Inc., Boca Raton, FL, **1**, p. 177, (1988).

SIGMAFAST is a trademark of Sigma-Aldrich Co. LLC

DS,KAA,PHC 10/12-1