


For life science research only.  
Not for use in diagnostic procedures.



# Restriction Endonuclease

## Sfi I

from *Streptomyces fimbriatus*



**Version: 21**

Content Version: March 2020

**Cat. No. 11 288 059 001**    5,000 U  
                                  40 U/ $\mu$ l

**Store product at  $-15$  to  $-25^{\circ}\text{C}$ .**

<b>1.</b>	<b>General Information .....</b>	<b>3</b>
1.1.	Contents.....	3
1.2.	Storage and Stability.....	3
	Storage Conditions (Product) .....	3
1.3.	Application.....	3
<b>2.</b>	<b>How to Use this Product .....</b>	<b>4</b>
2.1.	Protocols .....	4
2.2.	Parameters .....	4
	Activity in PCR Buffer .....	4
	Buffers.....	4
	Activity in SuRE/Cut Buffer System .....	4
	Cleavage Sites.....	4
	Number of cleavage sites on different DNAs.....	4
	Compatible Ends.....	5
	Inactivation .....	5
	Isoschizomers.....	5
	Methylation Sensitivity.....	5
	Recognition Sites .....	5
	Temperature Optimum.....	5
	Unit Definition.....	5
<b>3.</b>	<b>Troubleshooting .....</b>	<b>6</b>
<b>4.</b>	<b>Additional Information on this Product .....</b>	<b>7</b>
4.1.	Test Principle .....	7
	Commonly used bacterial strains .....	7
4.2.	References .....	7
4.3.	Quality Control.....	7
<b>5.</b>	<b>Supplementary Information .....</b>	<b>8</b>
5.1.	Conventions .....	8
5.2.	Changes to previous version.....	8
5.3.	Ordering Information.....	8
5.4.	Trademarks.....	9
5.5.	License Disclaimer.....	9
5.6.	Regulatory Disclaimer.....	9
5.7.	Safety Data Sheet.....	9
5.8.	Contact and Support.....	9

# 1. General Information

## 1.1. Contents

Vial / Bottle	Cap	Label	Function / Description	Content
Sfi I conc.	green	Sfi I, high conc.	Contains 10 mM Tris-HCl, 300 mM KCl, 5 mM MgCl <sub>2</sub> , 0.1 mM EDTA, 7 mM 2-mercaptoethanol, 500 mg/ml bovine serum albumin, 0.2% Triton X-100 (v/v), 50% glycerol (v/v), pH approximately 8.0 (+4°C).	1 vial, 5,000 U (40 U/μl)
M	green	SuRE/Cut Buffer M for Restriction Enzymes, 10x conc.	Contains 100 mM Tris-HCl, 500 mM NaCl, 100 mM MgCl <sub>2</sub> , 10 mM dithioerythritol, pH 7.5 (+37°C).	1 vial, 1 ml

## 1.2. Storage and Stability

### Storage Conditions (Product)

The product is shipped on dry ice.

When stored at -15 to -25°C, the product is stable through the expiration date printed on the label.

Vial / Bottle	Cap	Label	Storage
Sfi I conc.	green	Sfi I, high conc.	Store at -15 to -25°C. <b>⚠ Do not store below -25°C.</b>
M	green	SuRE/Cut Buffer M, 10x conc.	Store at -15 to -25°C.

## 1.3. Application

Sfi I recognizes the sequence GGCCNNNN/NGGCC and generates fragments with 3'-cohesive termini (Qiang BQ, Schildkraut I, 1984). Sfi I sites are a subset to Bgl I sites. The cleavage position in the N<sub>5</sub> region is identical. The octameric recognition sequence of Sfi I occurs rarely in the genomes of many organisms, especially those with low G+C content. Sfi I is useful for the analysis and cloning of large DNA fragments.

## 2. How to Use this Product

# 2. How to Use this Product

## 2.1. Protocols

The following steps describe a typical experiment.

- 1 Prepare the restriction digest according to the following table.

Reagent	Final conc.
DNA	1 µg
10x SuRE/Cut Buffer M	2.5 µl
Water, PCR Grade*	Up to total volume of 25 µl
Sfi I	1 U

- 2 Incubate at +50°C for 1 hour.

## 2.2. Parameters

### Activity in PCR Buffer

10%

Relative activity in PCR mix (Taq DNA Polymerase buffer) is 10%. The PCR mix contained λ target DNA, primers, 10 mM Tris-HCl (pH 8.3, +20°C), 50 mM KCl, 1.5 mM MgCl<sub>2</sub>, 200 µM dNTPs, 2.5 U Taq DNA polymerase. The mix was subjected to 25 amplification cycles.

### Buffers

### Activity in SuRE/Cut Buffer System

A	H	M <sup>(1)</sup>
25 to 50%	25 to 50%	<b>100%<sup>(2)</sup></b>

<sup>(1)</sup> Supplied Buffer

<sup>(2)</sup> Indicates recommended buffer for optimal activity.

### Cleavage Sites

### Number of cleavage sites on different DNAs

λ	Ad2	SV40	ΦX174	M13mp7	pBR322	pBR328	pUC18
0	3	1	0	0	0	0	0

## Compatible Ends

Compatible ends are only generated if the sequence of the three internal N's is identical.

## Inactivation

Sfi I cannot be heat inactivated by incubation at +65°C for 15 minutes.

## Isoschizomers

The enzyme is not known to have isoschizomers.

## Methylation Sensitivity

Sfi I is inhibited by the presence of 5-methylcytosine at the most central C-residue, as indicated (\*). 5-methylcytosine at the other C-positions is not inhibiting (^).

## Recognition Sites

GG<sup>°</sup>C\*CNNNNNNGG<sup>°</sup>C<sup>°</sup>C

 \* indicates methylation sensitivity.

## Temperature Optimum

+50°C

 Sfi I has a special incubation temperature.

## Unit Definition

One unit is the enzyme activity that completely cleaves 1 µg pTRE57 DNA in 1 hour at +50°C in a total volume of 25 µl SuRE/Cut Buffer M.

### 3. Troubleshooting

## 3. Troubleshooting

Observation	Possible cause	Recommendation
Inhibition or alteration of recognition specificity of restriction enzyme.	Compounds were used in the isolation of the DNA substrate, such as phenol, chloroform, ethanol, SDS, high levels of NaCl, and metal ions, such as Hg <sup>2+</sup> and Mn <sup>2+</sup> .	Remove compounds by ethanol precipitation followed by drying, before adding DNA to the restriction digest reaction. Mix vial of restriction enzyme gently but completely prior to use.

## 4. Additional Information on this Product

### 4.1. Test Principle

#### Commonly used bacterial strains

Strain	Genotype
BL21	<i>E. coli</i> B <i>F</i> <sup>-</sup> <i>dcm</i> <i>ompT</i> <i>hsdS</i> ( <i>r</i> <sub>B</sub> - <i>m</i> <sub>B</sub> -) <i>gal</i> (Studier FW, et al, 1986).
C600 <sup>e</sup>	<i>supE44</i> <i>hsdR2</i> <i>thi-1</i> <i>thr-1</i> <i>leuB6</i> <i>lacY1</i> <i>tonA21</i> (Hanahan D, 1983).
DH5α	<i>supE44</i> Δ( <i>lacU169</i> ( $\Phi$ 80d/ <i>lacZΔM15</i> ) <i>hsdR17</i> <i>recA1</i> <i>endA1</i> <i>gyrA96</i> <i>thi-1</i> <i>relA1</i> (Hanahan D, 1983).
HB101	<i>supE44</i> <i>hsdS20</i> <i>recA13</i> <i>ara-14</i> <i>proA2</i> <i>lacY1</i> <i>galK2</i> <i>rpsL20</i> <i>xyl-5</i> <i>mtl-1</i> (Hanahan D, 1983).
JM108	<i>recA1</i> <i>supE44</i> <i>endA1</i> <i>hsdR17</i> <i>gyrA96</i> <i>relA1</i> <i>thi</i> Δ( <i>lac-proAB</i> ) (Yanisch-Perron C, et al, 1985).
JM109	<i>recA1</i> <i>supE44</i> <i>endA1</i> <i>hsdR17</i> <i>gyrA96</i> <i>relA1</i> <i>thi</i> Δ( <i>lac-proAB</i> ) F'[ <i>traD36proAB</i> <sup>+</sup> , <i>lacI</i> <sup>q</sup> <i>lacZΔM15</i> ] (Yanisch-Perron C, et al, 1985).
JM110	<i>rpsL</i> ( <i>Str</i> ) <i>thr</i> <i>leu</i> <i>thi-I</i> <i>lacY</i> <i>galK</i> <i>galT</i> <i>ara</i> <i>tonA</i> <i>tsx</i> <i>dam</i> <i>dcm</i> <i>supE44</i> Δ( <i>lac-proAB</i> ) F'[ <i>traD36proAB</i> <sup>+</sup> , <i>lacI</i> <sup>q</sup> <i>lacZΔM15</i> ] (Yanisch-Perron C, et al, 1985).
K802	<i>supE</i> <i>hsdR</i> <i>gal</i> <i>metB</i> (Raleigh E, et al, 1986; Wood WB, 1966).
SURE <sup>r</sup>	<i>recB</i> <i>recJ</i> <i>sbcC201</i> <i>uvrC</i> <i>umuC::Tn5(kan')</i> <i>lac</i> , Δ( <i>hsdRMS</i> ) <i>endA1</i> <i>gyrA96</i> <i>thi</i> <i>relA1</i> <i>supE44</i> F'[ <i>proAB</i> <sup>+</sup> , <i>lacI</i> <sup>q</sup> <i>lacZΔM15</i> Tn10 ( <i>tet</i> <sup>r</sup> ) (Greener A, 1990).
TG1	<i>supE</i> <i>hsd</i> Δ5 <i>thi</i> Δ( <i>lac-proAB</i> ) F'[ <i>traD36proAB</i> <sup>+</sup> , <i>lacI</i> <sup>q</sup> <i>lacZΔM15</i> ] (Gibson TJ, 1984).
XL1-Blue <sup>r</sup>	<i>supE44</i> <i>hsdR17</i> <i>recA1</i> <i>endA1</i> <i>gyrA46</i> <i>thi</i> <i>relA1</i> <i>lac</i> F'[ <i>proAB</i> <sup>+</sup> , <i>lacI</i> <sup>q</sup> <i>lacZΔM15</i> Tn10 ( <i>tet</i> <sup>r</sup> )] (Bullock WO, et al, 1987).

### 4.2. References

- Bullock WO, Fernandez JM, Short JM. XL1-Blue- a high-efficiency plasmid transforming recA Escherichia coli strain with β-galactosidase selection. BioTechniques. 1987;5:376-379.
- Gibson, TJ. PhD Theses. Cambridge University, U.K 1984.
- Greener, A. Strategies 1990;3:5.
- Hanahan D. Studies on transformation of Escherichia coli with plasmids. J Mol Biol.1983;166:557-580.
- Raleigh EA, Wilson G. Escherichia coli K-12 restricts DNA containing 5-methylcytosine. Proc Natl Acad Sci USA.1986;83:9070-9074.
- Wood WB. Host specificity of DNA produced by Escherichia coli: bacterial mutations affecting the restriction and modification of DNA. J Mol Biol.1966;16:118-133.
- Studier FW, Moffatt BA. Use of bacteriophage T7 RNA polymerase to direct selective high-level expression of cloned genes. J Mol Biol.1986;189:113-130.
- Yanisch-Perron C, Vieira J, Messing J. Improved M13 phage cloning vectors and host strains: nucleotide sequences of the M13mp18 and pUC19 vectors. Gene.1985;33:103-19.
- Qiang BQ, Schildkraut I. A type II restriction endonuclease with an eight nucleotide specificity from Streptomyces fimbriatus. Nucleic Acids Res.1984;12:4507-4516.

### 4.3. Quality Control

For lot-specific certificates of analysis, see section **Contact and Support**.

## 5. Supplementary Information

# 5. Supplementary Information

## 5.1. Conventions

To make information consistent and easier to read, the following text conventions and symbols are used in this document to highlight important information:

Text convention and symbols	
 <b>i</b>	Information Note: Additional information about the current topic or procedure.
 <b>⚠ Important Note:</b> Information critical to the success of the current procedure or use of the product.	
(1) (2) (3) etc.	Stages in a process that usually occur in the order listed.
1 2 3 etc.	Steps in a procedure that must be performed in the order listed.
* (Asterisk)	The Asterisk denotes a product available from Roche Diagnostics.

## 5.2. Changes to previous version

Editorial changes.

## 5.3. Ordering Information

Product	Pack Size	Cat. No.
Reagents, kits		
T4 DNA Ligase	100 U, 1 U/µl	10 481 220 001
	500 U, 1 U/µl	10 716 359 001
	500 U, 5 U/µl	10 799 009 001
Water, PCR Grade	25 ml, 25 x 1 ml	03 315 932 001
	25 ml, 1 x 25 ml	03 315 959 001
	100 ml, 4 x 25 ml	03 315 843 001
SuRE/Cut Buffers	SuRE/Cut Buffer A, 5 x 1 ml	11 417 959 001
	SuRE/Cut Buffer M, 5 x 1 ml	11 417 983 001
	SuRE/Cut Buffer H, 5 x 1 ml	11 417 991 001
1,4-Dithiothreitol	2 g	10 197 777 001
	10 g	10 708 984 001
	25 g	11 583 786 001

## **5.4. Trademarks**

All product names and trademarks are the property of their respective owners.

## **5.5. License Disclaimer**

For patent license limitations for individual products please refer to:

**List of biochemical reagent products.**

## **5.6. Regulatory Disclaimer**

For life science research only. Not for use in diagnostic procedures.

## **5.7. Safety Data Sheet**

Please follow the instructions in the Safety Data Sheet (SDS).

## **5.8. Contact and Support**

To ask questions, solve problems, suggest enhancements or report new applications, please visit our **Online Technical Support Site**.

To call, write, fax, or email us, visit **sigma-aldrich.com**, and select your home country. Country-specific contact information will be displayed.