


61743 N-Lauroylsarcosine sodium salt

Synonyms: Sarkosyl NL
N-Dodecanoyl-N-methylglycine sodium salt

CAS number: 137-16-6

Product Description:

Molecular Formula: $C_{15}H_{28}NNaO_3$
Molecular Weight: 293.4 g/mol
pH: pH 7.0-9.0 (25°C, 1 M in H₂O)¹
 A_{260nm} (1 M in H₂O): 0.2¹
 A_{280nm} (1 M in H₂O): 0.06¹
 λ_{max} : 220 nm, 265 nm²
Critical Micelle Concentration (CMC) 14.57 mM (30 °C)³



61743 BioUltra for molecular biology

Trace elemental analyses have been performed on this Bio Ultra quality. BioUltra N-lauroylsarcosine sodium salt is for applications which require tight control of elemental content. The molecular biology quality is tested on the absence of Dnases, Rnases, Phosphatases and Proteases.

This product is an anionic detergent.² It aids in the solubilization and separation of membrane proteins, glycoproteins, isolation of RNA and plasmids.^{4, 5, 6, 7, 8, 9} This detergent can also be used as an antifoaming supplement⁵ or as a component of a lysing buffer of bacteria⁸ or other cells.

It has been used to indicate paramagnetic anisotropy sign change in micelle mesophage.¹⁰ It inhibits hexokinase.¹¹ Inhibition of bacterial flora of human saliva/gut at 0.25% as well as fungistatic activity in aqueous dispersion (1%) have been reported.¹²

The IR spectrum has been reported.¹³ A method for determination of sodium laurate content in N-lauroylsarcosine has been reported.¹⁴

Solubility:

The product is soluble in water (100 mg/ml), yielding a clear to slightly hazy, colorless solution.

References:

1. Sigma-Aldrich quality control
2. Data for Biochemical Research, 3rd ed., Dawson, R. M. C., et al., Oxford University Press (New York, NY: 1986), pp. 284-285.
3. Venkataraman, N. I., and Subrahmanyam, V. V. R., Effect of Structure on Surfactance of Sodium Salts of N-acylamino Acids in Aqueous Solutions. *J. Indian Chem. Soc.*, 62, 507-512 (1985).
4. P. Gariglio, Useful for rupturing eukaryote cells in transcription studies *FEBS Lett.* **44**, 330 (1974)
5. R.J. MacDonald, In the guanidine hydrochloride method for the isolation of RNA. Improves purity of the initial RNA precipitate and avoids excessive foaming *Meth. Enzymol.* **152**, 219 (1987)
6. Wroblewski, W., Solubilization of *Spiroplasma citri* cell membrane proteins with the anionic detergent sodium lauroyl-sarcosinate (Sarkosyl). *Biochimie* **60**, 389 (1978)



-
7. Schموokler, R. J., Properties of the polyoma virus transcription complex obtained from mouse nuclei. *Virology* **57**, 122 (1974)
 8. D.E. Mahoney, Lysis of *Clostridium perfringens* for the rapid extraction of plasmids, *Appl. Environ. Microbiol.* **51**, 521 (1986)
 9. *Methodol. Dev. Biochem.*, 3, 121 (1973).
 10. *J. Phys. Chem.*, 85, 3244 (1981).
 11. *Arch. Biochem. Biophys.*, 55, 356 (1955).
 12. Geigy Industrial Chemicals book, pp. 9-10.
 13. *J. Assoc. Off. Agr. Chemists*, 38, 638 (1955).
 14. *J. Assoc. Off. Agr. Chemists*, 37, 534 (1954).

Precautions and Disclaimer:

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

The vibrant M and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. Detailed information on trademarks is available via publicly accessible resources.
© 2018 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved.

The life science business of Merck KGaA, Darmstadt, Germany operates as MilliporeSigma in the US and Canada.

